


Spring-Loaded Probes


Industrial Process Styles



Available as
See page A-43
to A-48.

Cut-away of NB2 style to show detail of spring mechanism and terminal block.

- ✓ Non-Sealed for Use in Thermowells
- ✓ NB1 Cast Iron or NB2 Miniature Aluminum Protection Head
- ✓ Approx. 13 mm (1/2") of Travel Length
- ✓ 300 mm (12") Standard Length†
- ✓ Spring-Loading Provides Tip Contact for Faster Response When Used with Thermowells



 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| Thermocouple Alloy | Sheath Dia. mm (in) | Cast Iron Head | Aluminum Head | Price | | |
|--|---------------------|-------------------------|-------------------------|---------------------|------------|-----------------|
| | | | | Grounded or Exposed | Ungrounded | Price/Add'l 12" |
| IRON-CONSTANTAN Inconel Sheath J | 1.5 (1/16) | NB1-ICIN-116(*)-12-TBSL | NB2-ICIN-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-ICIN-18(*)-12-TBSL | NB2-ICIN-18(*)-12-TBSL | 57 | 59 | 3.15 |
| | 4.5 (9/16) | NB1-ICIN-316(*)-12-TBSL | NB2-ICIN-316(*)-12-TBSL | 58 | 60 | 4.35 |
| | 6.0 (3/4) | NB1-ICIN-14(*)-12-TBSL | NB2-ICIN-14(*)-12-TBSL | 62 | 64 | 7.50 |
| IRON-CONSTANTAN 304 SS Sheath J | 1.5 (1/16) | NB1-ICSS-116(*)-12-TBSL | NB2-ICSS-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-ICSS-18(*)-12-TBSL | NB2-ICSS-18(*)-12-TBSL | 57 | 59 | 1.85 |
| | 4.5 (9/16) | NB1-ICSS-316(*)-12-TBSL | NB2-ICSS-316(*)-12-TBSL | 58 | 60 | 3.15 |
| | 6.0 (3/4) | NB1-ICSS-14(*)-12-TBSL | NB2-ICSS-14(*)-12-TBSL | 62 | 64 | 5.00 |
| CHROMEGLA®-** ALOMEGA® Inconel Sheath K | 1.5 (1/16) | NB1-CAIN-116(*)-12-TBSL | NB2-CAIN-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-CAIN-18(*)-12-TBSL | NB2-CAIN-18(*)-12-TBSL | 57 | 59 | 3.15 |
| | 4.5 (9/16) | NB1-CAIN-316(*)-12-TBSL | NB2-CAIN-316(*)-12-TBSL | 58 | 60 | 4.35 |
| | 6.0 (3/4) | NB1-CAIN-14(*)-12-TBSL | NB2-CAIN-14(*)-12-TBSL | 62 | 64 | 7.50 |
| CHROMEGLA®-** ALOMEGA® 304 SS Sheath K | 1.5 (1/16) | NB1-CASS-116(*)-12-TBSL | NB2-CASS-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-CASS-18(*)-12-TBSL | NB2-CASS-18(*)-12-TBSL | 57 | 59 | 1.85 |
| | 4.5 (9/16) | NB1-CASS-316(*)-12-TBSL | NB2-CASS-316(*)-12-TBSL | 58 | 60 | 3.15 |
| | 6.0 (3/4) | NB1-CASS-14(*)-12-TBSL | NB2-CASS-14(*)-12-TBSL | 62 | 64 | 5.00 |
| CHROMEGLA®- CONSTANTAN Inconel Sheath E | 1.5 (1/16) | NB1-CXIN-116(*)-12-TBSL | NB2-CXIN-116(*)-12-TBSL | \$57 | \$59 | \$1.85 |
| | 3.0 (3/8) | NB1-CXIN-18(*)-12-TBSL | NB2-CXIN-18(*)-12-TBSL | 57 | 59 | 3.75 |
| | 4.5 (9/16) | NB1-CXIN-316(*)-12-TBSL | NB2-CXIN-316(*)-12-TBSL | 58 | 60 | 5.00 |
| | 6.0 (3/4) | NB1-CXIN-14(*)-12-TBSL | NB2-CXIN-14(*)-12-TBSL | 65 | 67 | 7.50 |
| CHROMEGLA®- CONSTANTAN 304 SS Sheath E | 1.5 (1/16) | NB1-CXSS-116(*)-12-TBSL | NB2-CXSS-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-CXSS-18(*)-12-TBSL | NB2-CXSS-18(*)-12-TBSL | 57 | 59 | 2.50 |
| | 4.5 (9/16) | NB1-CXSS-316(*)-12-TBSL | NB2-CXSS-316(*)-12-TBSL | 58 | 60 | 3.15 |
| | 6.0 (3/4) | NB1-CXSS-14(*)-12-TBSL | NB2-CXSS-14(*)-12-TBSL | 62 | 64 | 5.00 |
| COPPER-CONSTANTAN Inconel Sheath T | 1.5 (1/16) | NB1-CPIN-116(*)-12-TBSL | NB2-CPIN-116(*)-12-TBSL | \$57 | \$59 | \$1.85 |
| | 3.0 (3/8) | NB1-CPIN-18(*)-12-TBSL | NB2-CPIN-18(*)-12-TBSL | 57 | 59 | 3.75 |
| | 4.5 (9/16) | NB1-CPIN-316(*)-12-TBSL | NB2-CPIN-316(*)-12-TBSL | 58 | 60 | 5.00 |
| | 6.0 (3/4) | NB1-CPIN-14(*)-12-TBSL | NB2-CPIN-14(*)-12-TBSL | 65 | 67 | 7.50 |
| COPPER-CONSTANTAN 304 SS Sheath T | 1.5 (1/16) | NB1-CPSS-116(*)-12-TBSL | NB2-CPSS-116(*)-12-TBSL | \$57 | \$59 | \$1.55 |
| | 3.0 (3/8) | NB1-CPSS-18(*)-12-TBSL | NB2-CPSS-18(*)-12-TBSL | 57 | 59 | 2.50 |
| | 4.5 (9/16) | NB1-CPSS-316(*)-12-TBSL | NB2-CPSS-316(*)-12-TBSL | 58 | 60 | 3.15 |
| | 6.0 (3/4) | NB1-CPSS-14(*)-12-TBSL | NB2-CPSS-14(*)-12-TBSL | 62 | 64 | 5.00 |

* Specify junction type: **G** (Grounded), **U** (Ungrounded) or **E** (Exposed)

** For highest temperature and stability rating, change "SS" or "IN" to "XL" and add \$3 to price.

Note: Probe length includes approx. 1/2" allowance for threads.

† To order probes with lengths other than 12", change the "12" in the model number to the desired length in inches, and add the appropriate price per add'l foot from the last column.

To order with 310 SS, 316 SS or 321 SS sheath, change "SS" in model number to "310SS", "316SS" or "321SS" respectively; no additional charge.

Ordering Example: **NB1-ICSS-14U-12-TBSL**, spring-loaded probe with NB1-type cast iron head, Type J calibration, 6.0 mm (3/4") OD, ungrounded 304 SS sheath, 300 mm (12") L, \$64.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters