



Temperature Transmitter with Display and RTD Sensor

PRTXD Series
\$389
 All Models



- ✓ 2-Wire Transmitter
- ✓ 4 to 20 mA Output
- ✓ 4½ Digit Display
- ✓ RTD Probe Included
- ✓ NEMA-4X (IP66) Housing



The PRTXD Series are 2-wire transmitters that provide a 4 to 20 mA signal representing temperature. The units include a 4½ digit display and the RTD sensor. The NEMA 4X (IP66) housing protects the electronics. Units are available with spring-loaded probes for use with thermowells.

Specifications

Sensor: 100 W RTD element, 0.00385 alpha coefficient IEC-751 class B:

±0.3°C at 0°C, ±1.1°C at 150°C

Display: 4½ digit LCD, ½" digit height, 4 readings per second, nominal display update rate

Out of Range Indication:

ALARM 1: On display above 200°C (392°F)

ALARM 2: On display below -50°C (-58°F)

Loop Supply Voltage: Any DC supply/loop resistance that maintains 8 to 32 Vdc at gauge terminals (reverse polarity protected)

Loop Output Characteristics:

4 to 20 mA output (see chart for loop voltage characteristics), minimum 8 V required at gauge terminals at all times for proper operation

Test Function: Front panel TEST button when held, sets loop current and display to test calibration level, independent of temperature input to allow testing of system operation

Wiring Connections

(see drawing): 0.9 m (3') long, 2-conductor 22 AWG cable

Material and Color: NEMA 4X (IP66) ABS/Polycarbonate housing, light gray gasketed rear cover connection and probe material: ½" NPT male hex nipple, 316 stainless steel probe sheath

Operating Temperature (Electronics): -20 to 85°C (-4 to 185°F)

Storage Temperature: -40 to 95°C (-40 to 203°F)

Weight:

Transmitter:

Approx 340 g (12 oz)


Shipping weight:

Approx 450 g (1 lb)

Range: -50 to 200°C (-58 to 392°F)

Resolution: 0.1 degree

Accuracy: ±0.1% of span plus max sensor error of ±0.3°C at 0°C or ±1.1°C at 150°C



PRTXD-4, \$389, shown smaller than actual size.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
PRTXD-4	\$389	RTD transmitter with display and 4" sensor
PRTXD-4-SL	389	RTD transmitter with display and 4" spring-loaded [†] sensor
PRTXD-12	389	RTD transmitter with display and 12" sensor
PRTXD-12-SL	389	RTD transmitter with display and 12" spring-loaded [†] sensor
PE-1005	50	Reference Book: Introduction to Fuzzy Logic

Comes with complete operator's manual.

[†]Thermowell required for spring-loaded versions.

Ordering Example: PRTXD-12, RTD transmitter with display and 12" sensor, \$389.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters