



# High-Performance Infrared Thermometer With Patented Circle/Dot Laser Sighting and Wireless USB Interface

OS-DT8855W

# \$279



TM  
**PATENTED**

- ✓ **Measurement Range:**  
IR: -50 to 1050°C (-58 to 1922°F)  
T/C: -50 to 1370°C (-58 to 2498°F)
- ✓ **Data Logger with Built-In Memory Storing up to 20 Readings**
- ✓ **Wireless USB Interface (RF 915 MHz for USA, Canada and Mexico)**
- ✓ **Wireless Transmission Distance 15 m (49.2')**
- ✓ **Type K Thermocouple Input**



OS-DT8855W, shown smaller than actual size with included accessories, \$279.

The high performance, handheld OS-DT8855W infrared thermometer is a non-contact temperature measurement instrument that features a laser circle/dot sight. The patented laser sighting system defines the target for point and shoot measurement of temperatures from -50 to 1050°C (-58 to 1922°F) and reads surface temperature in less than a second.

## Specifications

**IR Temperature Range:**  
-50 to 1050°C (-58 to 1922°F)

**Accuracy:**  
-50 to 20°C (-58 to -4°F): ±5°C (9°F)  
-20 to 200°C (-4 to 392°F): ±1.5% rdg ±2°C (±3.6°F)  
200 to 538°C (392 to 1000°F): ±2.0% rdg ±2°C (±3.6°F)  
538 to 1050°C (1000 to 1922°F): ±3.5% rdg ±5°C (±9°F)

**Response Time:** Less than 1 second

**Spectral Response:** 8-14 microns

**Emissivity:** Digitally adjustable from 0.10 to 1.0

**CAUTION!** – This product is not intended for medical use or use on humans

**T/C Temperature Range:**  
-50 to 1370°C (-58 to 2498°F)

**Accuracy:**  
-50 to 1000°C (-58 to 212°F): ±1.5% rdg ±3°C (±5°F)  
1000 to 1370°C (1832 to 2498°F): ±1.5% rdg ±2°C (±3.6°F)

**Power Requirements:**  
9V battery or supplied AC adaptor

**Laser Power Output:** <1 mW

**Wavelength:** 630 to 670 nm

**Laser Classification:** Class 2

**Ambient Operating Temperature:**  
0 to 50°C (32 to 122°F)

**Storage Temperature:**  
-20 to 60°C (-4 to 140°F)

**Weight:** 290 g (10.2 oz)

**Distance to Spot Ratio:** 30:1

**Dimensions:** 175 H x 38 W x 95 mm D (6.87 x 1.5 x 3.75")

**Temperature Monitoring:**  
Max/Min/Diff/Avg



**Field of View:** 30:1

**Power:** Auto power-off

**Display:** Backlit for night use

**°C/°F:** Selectable

**Thermocouple:** Type K input

**Lock:** Trigger


**Alarm:** High and low

**Analog Output:** 1 mV/degree

**AVAILABLE FOR FAST DELIVERY!**



**Free Thermocouple Included!**



Model OS-DT8855W includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy. Order a Spare! Model No. SC-GG-K-30-36, \$15

## To Order (Specify Model Number)

Model No	Price	Description
OS-DT8855W	\$279	Handheld infrared thermometer 30:1 field of view

Comes complete with hard carrying case, mini-tripod, AC power supply, 9V battery, one Type K thermocouple, USB wireless data receiver, PC software, probe lead adaptors, and operator's manual.

**Ordering Example:** OS-DT8855W, handheld infrared thermometer with patented laser circle sighting, backlit LCD, 30:1 field of view, \$279. OCW-3, OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 4 years (\$69), \$279 + 69 = \$348.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters