




Series S Sanitary Thermowells Standard Threaded Well for 1/4 or 3/8" Diameter Elements

Application: 1/4 or 3/8" diameter stem, bimetal thermometers; temperature sensing elements having 0.252" (S-260 models) and 0.377" (S-385 models) maximum diameters, #20-gage thermocouple elements. Applications: food and beverage, pharmaceuticals, research.

Connection Size: 1 1/2, 2 and 2 1/2" Tri-Grip (Tri-Clamp® compatible) flange size are standard, 3 and 4" Tri-Grip models also available upon request.

Materials: 316 stainless steel. Custom wells are also available in special materials; prices on request.



1 1/2-S-260-U7 1/2-316SS, \$170, shown smaller than actual size.

Other Flange Diameters From 1 1/2 to 4"




1 1/2-S-385-U1 5/8-316SS, \$110, shown smaller than actual size.



Visit omega.com/s-260_s-385 for details.

MOST POPULAR MODELS HIGHLIGHTED!



Material	Pressure-Temperature Rating—lb per square inch						
	Temperature — °F						
	70°	200°	400°	600°	800°	1000°	1200°
A.I.S.I.-316	7000	7000	6400	6200	6100	5100	2500

To Order (Specify Model Number)

Model No.	Price	Flange Size	Shank Style	Stem Length, A	Insertion Length, U	Shank Dia. Q
S-260 Series* 0.260 Bore Diameter						
1 1/2-S-260-U1 5/8-316SS	\$110	1" and 1 1/2"	No Step Down	2 1/2"	1 5/8"	1/2"
1 1/2-S-260-U2 1/2-316SS	125	1" and 1 1/2"	No Step Down	4"	2 1/2"	1/2"
1 1/2-S-260-U4 1/2-316SS	145	1" and 1 1/2"	Step Down	6"	4 1/2"	3/4"
1 1/2-S-260-U7 1/2-316SS	170	1" and 1 1/2"	Step Down	9"	7 1/2"	3/4"
1 1/2-S-260-U10 1/2-316SS	190	1" and 1 1/2"	Step Down	12"	10 1/2"	3/4"
2-S-260-U1 5/8-316SS	125	2"	No Step Down	2 1/2"	1 5/8"	1/2"
2-S-260-U2 1/2-316SS	140	2"	No Step Down	4"	2 1/2"	1/2"
2-S-260-U4 1/2-316SS	160	2"	Step Down	6"	4 1/2"	3/4"
2-S-260-U7 1/2-316SS	185	2"	Step Down	9"	7 1/2"	3/4"
2-S-260-U10 1/2-316SS	205	2"	Step Down	12"	10 1/2"	3/4"
2 1/2-S-260-U1 5/8-316SS	135	2 1/2"	No Step Down	2 1/2"	1 5/8"	1/2"
2 1/2-S-260-U2 1/2-316SS	150	2 1/2"	No Step Down	4"	2 1/2"	1/2"
2 1/2-S-260-U4 1/2-316SS	170	2 1/2"	Step Down	6"	4 1/2"	3/4"
2 1/2-S-260-U7 1/2-316SS	195	2 1/2"	Step Down	9"	7 1/2"	3/4"
2 1/2-S-260-U10 1/2-316SS	215	2 1/2"	Step Down	12"	10 1/2"	3/4"
S-385 Series* 0.385 Bore Diameter						
1 1/2-S-385-U1 5/8-316SS	\$110	1" and 1 1/2"	No Step Down	2 1/2"	1 5/8"	1/2"
1 1/2-S-385-U2 1/2-316SS	125	1" and 1 1/2"	No Step Down	4"	2 1/2"	1/2"

Ordering Examples: 1 1/2-S-260-U2 1/2-316SS, 1 1/2" Tri-Grip™ 316 SS sanitary well with 2 1/2" insertion length and 0.260" internal diameter, \$125.
1 1/2-S-260-U4 1/2-316SS, 1 1/2" Tri-Grip™ 316 SS step down sanitary well with 4 1/2" insertion length and 0.260" internal diameter, \$145.
1 1/2-S-260-U7 1/2-316SS, 1 1/2" Tri-Grip™ 316 SS sanitary well with 7 1/2" insertion length and 0.260" internal diameter, \$170.

*The above thermowells are also available with 3 and 4" Tri-Grip flanges, contact sales for ordering information.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters