

Tungsten-Rhenium Thermocouples

Butt-Welded and Unsheathed

Tungsten-rhenium thermocouples were developed to meet the requirements for measuring ultra-high temperatures in the 2760°C (5000°F) range.

OMEGA sells 3 widely used tungsten-rhenium thermocouple calibrations: tungsten versus tungsten-26% rhenium, tungsten-5% rhenium versus tungsten-26% rhenium, and tungsten-3% rhenium versus tungsten-25% rhenium.


OMEGA® tungsten-rhenium thermocouples conform to the limits of error listed in the table below.

Because of the inherent brittleness of unalloyed tungsten, the tungsten versus tungsten-26% rhenium thermocouples are more difficult to handle than the tungsten-5% rhenium versus tungsten-26% rhenium combination.

The average emf of the W-3% Re/W-25% Re is slightly less than that of W/W-26% Re and slightly more than that of W-5% Re/W-26% Re. The ductility of W-3% Re is about equal to that of W-5% Re, but superior to that of unalloyed tungsten.

All 3 thermocouple calibrations can be used to 2760°C (5000°F) in hydrogen or inert gas atmospheres and in a vacuum. They deteriorate rapidly under oxidizing conditions and should not be used in air or atmospheres containing oxygen.

OMEGA® tungsten-rhenium thermocouples come in 300 mm (12") lengths, which corresponds to each for a 600 mm (24") total length. Longer lead lengths are available; consult sales.



Limits of Error for Tungsten-Rhenium Thermocouple Wire Combinations

Wire Diameter mm (in)	Temperature Range (†)	Maximum Error or Departure
0.075 (0.003)	0 to 425°C (32 to 800°F) 426 to 1750°C (800 to 3200°F)	±4.5°C (±8°F) ±1%
0.125 (0.005)	0 to 425°C (32 to 800°F) 426 to 1975°C (800 to 3600°F)	±4.5°C (±8°F) ±1%
0.25 to 0.50 (0.010 to 0.020)	0 to 425°C (32 to 800°F) 426 to 2325°C (800 to 4200°F)	±4.5°C (±8°F) ±1%

† Up to 2760°C (5000°F) for short-term exposure.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)							
Materials	Wire Dia. mm (in)	Unsheathed Model No.**	Price per TC	Price per Add'l Dbl In	Butt-Welded Model No.**	Price per TC	Price per Add'l Dbl In
G Tungsten- Tungsten 26% Re	0.075 (0.003)	TOR-003-12	\$35	\$0.50	—	—	—
	0.125 (0.005)	TOR-005-12	40	0.75	—	—	—
	0.250 (0.010)	TOR-010-12	60	2.00	TOR-010-12-BW	\$70	\$4
	0.381 (0.015)	TOR-015-12	85	3.00	TOR-015-12-BW	95	6
	0.500 (0.020)	TOR-020-12	110	4.00	TOR-020-12-BW	95	6
C* Tungsten 5% Re- Tungsten 26% Re	0.075 (0.003)	T5R-003-12	\$35	\$2.00	—	—	—
	0.125 (0.005)	T5R-005-12	40	2.25	—	—	—
	0.250 (0.010)	T5R-010-12	60	4.00	T5R-010-12-BW	\$70	\$4
	0.381 (0.015)	T5R-015-12	85	6.00	T5R-015-12-BW	95	6
	0.500 (0.020)	T5R-020-12	110	8.00	T5R-020-12-BW	95	6
D Tungsten 3% Re- Tungsten 25% Re	0.127 (0.005)	T3R-005-12	\$40	\$2.25	—	—	—
	0.250 (0.010)	T3R-010-12	60	4.00	T3R-010-12-BW	\$70	\$4
	0.381 (0.015)	T3R-015-12	85	6.00	T3R-015-12-BW	95	6
	0.500 (0.020)	T3R-020-12	110	8.00	T3R-020-12-BW	125	8

* Most popular of the 3 tungsten-rhenium thermocouples; a large selection of instrumentation is available.

** Tungsten-rhenium alloy thermocouples are supplied in standard 300 mm (12") lengths (600 mm [24"] loops). Change suffix "-12" in model number to indicate additional length (in inches) required. Consult Sales for other sizes.

Ordering Examples: T5R-005-12, 300 mm (12"), Type C thermocouple, 0.125 mm (0.005") diameter, \$40. T5R-010-12-BW, butt-welded Type C thermocouple, 300 mm (12") long with a 0.25 mm (0.010") diameter, \$70.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters