

SANITARY TEMPERATURE SENSORS



Sanitary RTD Assemblies Spring Loaded Design with Sanitary Thermowell

PRS-TW-NB9W Series
Starts at

\$180



- ✓ Removable Spring Loaded Probe in Well for Good Thermal Response
- ✓ 1½" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting
- ✓ Standard Insertion Lengths of 1½", 2½", 4½", 7½", 10½"
- ✓ White Polypropylene Head with Screw Cap Standard, Other Polypropylene and SS Heads Available
- ✓ 316L SS Thermowell with 32 µin or Better Finish on Wetted Parts
- ✓ 4-Wire Pt100 Class A Element Standard
- ✓ -50 to 200°C (-58 to 392°F) Temperature Range

Options

- ✓ Fitting Styles
- ✓ RTD Elements
- ✓ Protection Heads

Sensor Flange Size Range ¾" to 4" Tri-Grip™ Process Flange. See Page 5 or Visit omega.com/tri-grip for Details


The OMEGA® PRS-TW-NB9W series RTD probes are spring loaded into a sanitary thermowell, with a ½ x ½ NPT fitting for easy removal. These probes feature a 4-wire Pt100 Class A element (100 ±0.06 Ω at 0°C) that is compatible with 2-, 3-, and 4-wire RTD instrumentation.

Please consult sales for available options, including element types and curves, probe lengths, protection heads and sanitary fitting styles.

¾ NPT conduit connection.

Allows Sensor Removal/Calibration Without Disturbing Your Clean-In-Place System

½ x ½ NPT fitting spring loads sensor in thermowell.



White polypropylene screw cover connection head.

316L SS 1½" 16 AMP Tri-Grip™ cap standard.

32 µin Finish

Insertion length

PRS-3-100-A-TW-0250-D1-NB9W, \$195, shown smaller than actual size.

Standard well features include a 0.5" dia. stem (0.75" stepped down for insertion lengths over 2.5") with a 0.260" bore diameter. See the S-260 series thermowells on page 67 or visit omega.com/s-260_s-385 for complete well dimensions.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Lead Wire Style	Ω at 0°C	Well Stem Length	Insertion Length	Shank Diameter
PRS-3-100-A-TW-0163-D1-NB9W	\$180	4-wire	100	2½"	1½"	½"
PRS-3-100-A-TW-0250-D1-NB9W	195	4-wire	100	4"	2½"	½"
PRS-3-100-A-TW-0450-D1-NB9W	215	4-wire	100	6"	4½"	¾" step to ½"
PRS-3-100-A-TW-0750-D1-NB9W	240	4-wire	100	9"	7½"	¾" step to ½"
PRS-3-100-A-TW-1050-D1-NB9W	260	4-wire	100	12"	10½"	¾" step to ½"

Optional protection heads: To order with NB16W white polypropylene flip-top head, change model number suffix from "-NB9W" to "-NB16W" and \$7 to price.

To order with NB15 large 316 SS head, change model number suffix from "-NB9W" to "-NB15" and \$37 to price.

To order with NB13 medium size 316 SS head, change model number suffix from "-NB9W" to "-NB13" and \$55 to price.

Note: Please consult sales for available options, including element types and curves, probe lengths, and sanitary fitting styles.

Ordering Examples: PRS-3-100-A-TW-0450-D1-NB9W, 4-wire Pt100 RTD sensor (100 Ω @ 0°C, Class A accuracy), spring loaded in a 1½" 16 AMP fitting thermowell with 6" stem length/4½" insertion length, \$215.

PRS-3-100-A-TW-0750-D1-NB9W, 4-wire Pt100 RTD sensor (100 Ω @ 0°C, Class A accuracy), spring loaded in a 1½" 16 AMP fitting thermowell with 9" stem length/7½" insertion length, \$240.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters