

# Linear Power Supply



PSU505  
\$2100



- ✓ 0 to 30 Vdc
- ✓ Standard RS232, USB Interface
- ✓ Liquid Crystal Display
- ✓ Programmable Triple Outputs (Auto-Ranging Function on Channel 3)
- ✓ Low Ripple, Low Noise
- ✓ Number and Function Keys
- ✓ 100 Store and Recall Settings
- ✓ Timer (1 second to 100 hours)
- ✓ Precise Voltage and Current Measurement
- ✓ Dual Tracking Mode
- ✓ Average Measurement Time: 50 ms

The PSU505 is a DC power supply with 3 programmable outputs and 12-bit resolution. The total output power is 210 W: channels 1 and 2, 30V/3 A, provide 90 W each; channel 3, 10V/ 5 A, puts out 30 W at a constant rate. Channel 1 provides outputs in serial and parallel modes; channel 2, in serial mode only. On channel 3, the

PSU505, \$2100, shown smaller than actual size.

user can perform auto-ranging, a feature not found on traditional power supplies.

The user can monitor OVP (overvoltage protection) and OCP (overcurrent protection) on the front-panel LCD. Because of its 0.01% load-and-line regulation and 50 ms max response time, the PSU505 remains stable even when the voltage source and loads change. The PSU505 is also highly efficient, with an average measurement time of 50 ms.

The PSU505 is easy to use, featuring an adjustable tracking function, a rotary selection dial, and

an alphanumeric keypad. With the timer function, the user can control when each output is switched off (1 second to 100 hours); this feature is particularly useful in burn-in-room and electroplating applications. Up to 100 configurations can be stored in memory. A key-lock function prevents users from changing the original settings.



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
PSU505	\$2100	Linear power supply

Comes complete with 1.5 m (5') power cord, fuse and operator's manual.

Ordering Examples: PSU505, linear power supply, \$2100. OCW-3, OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 4 years (\$350), \$2100 + 350 = \$2450.

PSU505, \$2100,  
shown smaller than actual size.



## Specifications

<b>Channel Number</b>	CH1 and CH2	CH3
<b>Output Voltage</b>	0 to 30 V	0 to 15 V
<b>Output Current</b>	0 to 3 A	0 to 5 A
<b>Output Power (CH3 Auto-Ranging)</b>	90 W	30 W
<b>Line Regulation ±(% of Output + Offset)</b>		
<b>Voltage</b>	0.01% + 2 mV	
<b>Current</b>	0.01% + 300 µA	
<b>Load Regulation ±(% of Output + Offset)</b>		
<b>Voltage</b>	≤3 mV	≤5 mV
<b>Current</b>	0.01% + 300 µA	
<b>Ripple and Noise (20 Hz to 20 MHz)</b>		
<b>Normal Mode Voltage</b>	300 µVrms/3 mVpp	1 mVrms/20 mVpp
<b>Normal Mode Current</b>	<1 mA	<5 mA
<b>Resolution</b>		
<b>Programming</b>	10 mV/1 mA	10 mV/2 mA
<b>Readback</b>	10 mV/1 mA	3 mV/2 mA
<b>Programming Accuracy ±(% Output + Offset)</b>		
<b>Voltage</b>	0.05% + 20 mV	0.05% + 6 mV
<b>Current</b>	0.05% + 3 mA	0.05% + 4 mA
<b>Readback Accuracy ±(% Output + Offset)</b>		
<b>Voltage</b>	0.05% + 20 mV	0.05% + 6 mV
<b>Current</b>	0.05% + 3 mA	0.05% + 4 mA
<b>Temperature Coefficient per ±(% Output + Offset)</b>		
<b>Voltage</b>	<0.1% + 3 mV	
<b>Current</b>	<0.2% + 2 mA	
<b>Tracking Accuracy ±(% of Output + Offset)</b>		
<b>Voltage</b>	<0.1% + 40 mV	
<b>Transient Response Time</b>	<50 µs	
<b>Stability, Constant Output and Temperature ±(% of Output + Offset), 8 hrs</b>		
<b>Voltage</b>	<0.2% + 2 mV	
<b>Current</b>	<0.1% + 1 mA	
<b>Voltage Programming Speed</b>		
<b>Rising Time at Full Load</b>	1 ms	
<b>Rising Time at No Load</b>	1 ms	
<b>Falling Time at Full Load</b>	2.5 ms	
<b>Falling Time at No Load</b>	250 ms	
<b>General</b>		
<b>AC Line Input Voltage Ranges</b>	115/220 Vac ±10% (47 to 63 Hz)	
<b>Temperature Ranges</b>	<b>Operating:</b> 0 to 40°C (32 to 104°F); <b>Storage:</b> -10 to 70°C (14 to 158°F)	
<b>Common-Mode Voltage</b>	±240 Vdc	
<b>Dimensions (W x H x D)</b>	216 x 135 x 432 mm (8.5 x 5.3 x 17")	
<b>Weight</b>	6.5 kg (14 lb)	
<b>Communications</b>	RS232/USB interface	



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters