

Mix-and-Match Series Digital Stem Thermometers

Deluxe Digital Pocket Thermometer

Model HH65

\$20



- ✓ Data Hold
- ✓ °C/°F Switch
- ✓ On/Off Switch
- ✓ Auto Power-Off: 10 min

- ✓ 65 L x 4 mm Dia. (2.5 x 0.16") Probe
- ✓ -40 to 150°C (-40 to 300°F)
- ✓ 15 s Response Time
- ✓ Pocket Clip
- ✓ Protective Cover
- ✓ Drop Resistant
- ✓ Water Resistant
- ✓ ±2% Accuracy
- ✓ 1° Resolution



Battery: 15 V x 1 pc LR-43
Dimensions: 160 L x 25 W x 13 mm H (6 1/4 x 1 x 1/2")

Protective Case Included

Cheaper by the Dozen!
Purchase Any Combination of 12 Units and Save 20%.

ALL MODELS AVAILABLE FOR FAST DELIVERY!



Case Included

Digital Min/Max Thermometer

Model TPD40

\$21



- ✓ °C/°F Switch
- ✓ On/Off Switch
- ✓ Min/Max Function
- ✓ Plastic Sheath
- ✓ Pocket Clip
- ✓ -26 to 200°C (-14 to 392°F)
- ✓ 100 mm L (4") Stainless Steel Probe
- ✓ 47 mm (1.9") Dia. Head
- ✓ Accuracy: ±1°C (1.8°F) from -10 to 82°C (14 to 180°F)

Easy-to-Read 50 mm (2.1") Dia. Thermometer

Model TPD42 **\$35**

Shown close to actual size.

Specifications	TPD42
Measurement Range	-50 to 150°C (-58 to 302°F)
Accuracy	±1°C from -30 to 150°C (±1.8 °F from -22 to 302°F)
Probe Size	4 Dia. x 125 mm L (0.16 x 5")
Sampling Time	1 s
Unit Weight	20 g (0.7 oz) with probe cover
Unit Size	50 Dia. x 31 mm L (2.1 x 1.3")
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges
Display Digit Size	10 H x 5 mm W (0.4 x 0.2")
Auto Power-Off	After 1 hour
Battery	1.5 V x 1 pc, model MN-TPD
Ambient Temperature	-10 to 50°C (14 to 122°F)
Button Functions	ON/OFF and °C/°F



Case Included

Pocket Thermometer



Model TPD41

\$18



Case Included



- ✓ Low Cost
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

Applications: Air conditioning, food processing, heating and ventilating, agriculture, automobile, brewing, photography, food storage, refrigeration, pharmaceutical and laboratory uses

Specifications	TPD41
Measurement Range	-40 to 150°C (-40 to 302°F)
Accuracy	±1°C between -20 and 120°C, otherwise, ±2°C (±2°F between -4 and 248°F, otherwise, ±4°F)
Probe Size	3.5 Dia. x 125 mm L (0.14 x 5")
Sampling Time	1 second or 10 seconds, selectable
Unit Weight	20 g (0.7 oz) with probe cover
Unit Size	35 L x 35 H x 20 mm Dia. (1.4 x 1.4 x 0.8")
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges
Display Digit Size	6 H x 3 mm W (0.24 x 0.12")
Battery	1.5 V x 1 pc, model MN-TPD
Ambient Temperature	-10 to 50°C (14 to 122°F)

Mix-and-Match Series Digital Stem Thermometers

- ✓ On/Off Switch
- ✓ °C or °F Switchable
- ✓ Auto Power-Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover



Case Included

Model TPD32/33
\$21/23



Model TPD34/35
\$18/22

- ✓ On/Off Switch
- ✓ °C or °F Switchable
- ✓ Auto Power-Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover



ALL MODELS AVAILABLE FOR FAST DELIVERY!

Case Included




Cheaper by the Dozen!
Purchase Any Combination of 12 Units and Save 20%

Specifications	TPD32	TPD33
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	3.5 Dia. x 200 mm L (0.14 x 8")	3.5 Dia. x 200 mm L (0.14 x 8")
Sampling Time	1 s	0.5 s
Unit Weight	23 g (0.7 oz) with probe cover	28 g (0.9 oz) with probe cover
Unit Size	20 Dia. x 58 mm L (0.8 x 2.3")	
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges	
Display Digit Size	6 H x 3 mm W (0.24 x 0.12")	
Auto Power-Off	After 10 minutes	
Battery	1.5 V x 1 pc, model PH-BATT-3	
Ambient Temp	-10 to 50°C (14 to 122°F)	
Button Functions	On/off and °C/°F	

Specifications	TPD34	TPD35
Measurement Range	-40 to 150°C (-40 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4 to -58°F and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	3.5 Dia. x 200 mm L (0.14 x 8")	3.5 Dia. x 200 mm L (0.14 x 8")
Sampling Time	1 s	0.5 s
Unit Weight	21 g (0.7 oz) with probe cover	26 g (0.9 oz) with probe cover
Unit Size	35 L x 35 H x 20 mm D (1.4 x 1.4 x 0.8")	
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges	
Display Digit Size	6 H x 3 mm W (0.24 x 0.12")	
Auto Power-Off	After 10 minutes	
Battery	1.5 V x 1 pc, model no. MN-TPD	
Ambient Temp	-10 to 50°C (14 to 122°F)	
Button Functions	On/off and °C/°F	

Case Included



- ✓ On/Off Switch
- ✓ °C or °F Switchable
- ✓ Auto Power-Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

Model TPD38/39
\$23/24

Specifications	TPD38	TPD39
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	3.5 Dia. x 200 mm L (0.14 x 8")	3.5 Dia. x 200 mm L (0.14 x 8")
Sampling Time	1 s	0.5 s
Unit Weight	23 g (0.8 oz) with probe cover	28 g (0.99 oz) with probe cover
Unit Size	20 Dia. x 72 mm L (0.8 x 2.8")	
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges	
Display Digit Size	6 H x 3 mm W (0.24 x 0.12")	
Auto Power-Off	After 10 minutes	
Battery	1.5 V x 1 pc, model PH-BATT-3	
Ambient Temp	-10 to 50°C/14 to 122°F	
Button Functions	On/off and °C/°F	

Model TPD36/37
\$17/21

- Temperature Tester
- ✓ On/Off Switch
- ✓ °C or °F Switchable
- ✓ Auto Power-Off
- ✓ Stainless Steel Probe
- ✓ Protective Probe Cover

Specifications	TPD36	TPD37
Measurement Range	-50 to 150°C (-58 to 302°F)	-50 to 280°C (-58 to 536°F)
Accuracy	±1°C from -20 to 120°C otherwise, ±2°C ±2°F from -4 to 248°F otherwise, ±4°F	±1°C from -20 to 120°C ±2°C from -20 to -50°C and 120 to 150°C ±4°C from 150 to 200°C ±6°C from 200 to 280°C ±2°F from -4 to 248°F ±4°F from -4°F to -58 and 248 to 302°F ±8°F from 302 to 392°F ±11°F from 392 to 536°F
Probe Size	3.5 Dia. x 125 mm L (0.14 x 5")	3.5 Dia. x 125 mm L (0.14 x 5")
Sampling Time	1 s	0.5 s
Unit Weight	21 g (0.7 oz) with probe cover	26 g (0.9 oz) with probe cover
Unit Size	36 L x 17 H x 33 mm D (1.4 x 0.7 x 1.3")	
Display Resolution	0.1° from -19.9 to 199.9°; 1° other ranges	
Display Digit Size	6 H x 3 mm W (0.24 x 0.12")	
Auto Power-Off	After 10 minutes	
Battery	1.5 V x 1 pc, model No. PH-BATT-3	
Ambient Temp	-10 to 50°C/14 to 122°F	
Button Functions	On/off and °C/°F	

Case Included





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters