

Compact Flatbed Recorder

100 mm Chart Width


Model RD-1101

\$1656



RD-1101
Flatbed Recorder

DISCONTINUED PRODUCT



- ✓ 100 mm (4") Chart Width
- ✓ 1 mV to 5 V Full Scale
- ✓ 16 Chart Speeds
- ✓ 0.4 sec, Full Scale Response
- ✓ Override Event Marker

Compact in size, this recorder utilizes all of the most common features of recorders today. Its twelve calibrated full scale ranges from 1 mV to 5 V accommodate most input signals. The patented Pulse Modulated Servo system provides reliable and repeatable recording and is protected from large signal variances by a simple electronic servo power shutdown. Many features are offered with this model such as the override event marker, our long-life pen system and more.

Specifications

Number of Channels: one
Full Scale Ranges: 1, 2, 5, 10, 20, 50 millivolts; 0.1, 0.2, 0.5, 1.2, 5 volts (switch selectable)
Input Type: floating, single ended
Input Impedance: 2.5 MΩ, fixed
Chart Width: 100 mm (4")
Chart Speeds: 1, 2, 3, 6, 10, 15, 20, and 30 cm/min and cm/hr, switch selectable (1 cm = 0.3937")
Writing Method: ink, fiber tipped disposable cartridge
Accuracy: Better than 0.5% full scale

DISCONTINUED PRODUCT

PX602 Series pressure sensors, \$198 (basic unit), sold separately. See Section B of the OMEGA Complete Pressure, Strain and Force Measurement Handbook and Encyclopedia®, or online at omega.com

Response Time: 0.4 sec, full scale

Zero Adjustment:
-100 to 100% of full scale

Power: 115/230 Vac ±10%; 50/60 Hz

Dimensions:

114 x 216 x 267 mm
(4.5 H x 8.5 D x 10.5" W)

Weight: 2.95 kg (6.8 lb)

DISCONTINUED PRODUCT

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
RD-1101	\$1656	Flatbed recorder 100 mm (4")

Each recorder comes complete with one roll of paper, disposable felt-tip pen, and operator's manual.

OMEGACARESM extended warranty program is available for models shown on this page. OMEGACARESM covers parts, labor, and equivalent loaners. Ask your sales representative for full details when placing an order.

Ordering Example: RD-1101 flatbed recorder plus 0100-0011, 100 mm (4") chart paper, plus 0100-0105, 6 blue pens, \$1656 + 77 + 24 = \$1757. OCW-3 OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$350), \$1656 + 350 = \$2006.

Accessories

Model No.	Price	Description
0100-0011	\$77	chart paper, 100 mm x 30 m (4" x 98'), pkg of six
0100-0105	24	6 blue pens
0100-0106	24	6 red pens
0100-0107	24	6 black pens
0100-0108	24	6 green pens



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters