


Reversible Liquid Crystal Temperature Labels


RLC-80 Series
Starts at
\$15

- ✓ 11-Point Temperature Range
- ✓ Unique Temperature Bar Design
- ✓ Size: 12.7 W x 101.6 L x 0.25 mm Thick (0.5 x 4 x 0.01")


RLC-80-0/100



RLC-80-50/150



RLC-80-100/220



RLC-80-100/220 Series Turns Black up to the Next Level of Reading. Example: 175°F will Start to Show Black at 170°F.

Green, Brown, Blue Indicating Systems

All models shown actual size.

BROWN	Bar is just above the actual reading
GREEN	Bar is the actual reading
BLUE	Bar is just below the actual reading

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)								Price/Pkg of 10	Price/Pkg of 30
Model No.	Temperature Range								
RLC-80-0/100(*)	°F	0	10	20	30	40		\$15	\$45
		50	60	70	80	90	100		
RLC-80-50/150(*)	°F	50	60	70	80	90	100		
		100	110	120	130	140	150		
RLC-80-100/220(*)	°F	100	110	120	130	140			
		150	160	170	180	200	220		

* Insert "-10" for package of 10 or "-30" for package of 30.

Ordering Example: RLC-80-0/100-30, 11-point temperature label (0 to 100°F), package of 30, \$45.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters