

omega.com[®]

Ω OMEGA[®]

OMEGABOND[®] OB-600

HIGH TEMPERATURE CHEMICAL SET CEMENT



INSTRUCTION
SHEET

M1239-0311

Shop online at: omega.com e-mail: info@omega.com
For latest product manuals: omegamanual.info

GENERAL DESCRIPTION

The OMEGABOND[®] OB-600 High Temperature Chemical Set Cement is a magnesium phosphate base, one-part ceramic cement which has many exceptional characteristics including:

- Resists temperatures to 1427°C (2600°F)
- Resists oil, solvents and most acids (except hydrofluoric)
- Heat conductive and thermal shock resistant
- Excellent electrical insulator
- Adheres to metals, ceramics, glass, porcelain and most other surfaces
- Excellent mechanical bonding characteristics
- Ceramic-like body

OMEGABOND[®] OB-600 cement is an electrical refractory cement used where high levels of electrical insulation and thermal conductivity are needed. It is ideal for potting applications that are subject to high temperature and/or thermal shock. The cement provides heavy duty electrical insulation for appliances, nickel chromium resistance heating elements, pyrometers and resistors.

HANDLING INFORMATION

CAUTION

- Avoid prolonged breathing of vapors - work in well-ventilated area
- Protect skin against contamination
- Protect eyes against contamination
- Do not take internally

OMEGABOND[®] 600 Cement Powder is a harmful dust. Avoid breathing dust by using respirators. Avoid contact with eyes or skin by wearing gloves and goggles or a face shield. Wash thoroughly with soap and water after handling. Keep containers closed.

SHELF LIFE

OMEGABOND[®] 600 Cement Powder has a shelf life of (6) months when stored in unopened, tightly sealed containers in a dry location at 70°F.

SOLVENT

A 10% caustic or alkaline solution such as 10% NaOH (Sodium Hydroxide) will break down the OB-600 cement after it has cured. However, care should be exercised as far as the compatibility of the caustic solution with any other components involved in the application, such as the material or surface that the cured cement has been applied to.

DIRECTIONS FOR USE

OMEGABOND[®] OB-600 cement is a one-part cement and is supplied as a powder. Weigh out 100 parts of OMEGABOND[®] 600 powder and 13 parts of water. First place the powder into a clean mixing container. Then add water to the powder all at one time while mixing - DO NOT

ADD WATER GRADUALLY! Continue mixing with a slow-speed mixer or with a hand spatula until smooth, uniform consistency is obtained. Avoid using excess amounts of water. Excess water reduces the mechanical strength, increases the amount of shrinkage and delays the setting time of the cement. Failure of the cement to adhere indicates setting has begun - in this case discard the cement (do not attempt to retemper by adding more water).

Porous substrates should be dampened with OMEGABOND[®] Cement Thinning Liquid (Part No. OB-TL), prior to application of the mixed cement.

CURING

OMEGABOND[®] 600 cement cures with an internal chemical-setting action in 18-24 hours at ambient temperature. Since it is a chemical set cement, it can be used in thick applications (i. e., it can be applied in thicknesses greater than 1/4"). Cure time can be accelerated by low temperature oven drying at 180°F. If the cement is to be exposed to elevated temperatures, cure for 18-24 hours at ambient temperature, then oven dry for 4 hours at 180°F and for an additional 4 hours at 220°F. This helps to prevent flaking and chipping. The working time of mixed OMEGABOND[®] 600 cement is approximately 30 minutes when the powder is mixed with water at 70°F.

PHYSICAL PROPERTIES*

Maximum Service Temperature:	1427°C (2600°F)
Thermal Conductivity:	10-12 Btu-in/sq.ft./-hr-°F
Color:	Off white
Coefficient of Thermal Expansion:	2.6 x 10 ⁻⁶ in/in°F
Density:	160 lbs/cu. ft.
Dielectric Constant:	3.0-4.0
Compressive Strength:	4500-5500 PSI
Tensile Strength:	250 PSI
Dielectric Strength:	
At 70°F (21°C):	76.0 to 101.5 volts/mil
At 750°F (399°C):	25.0 to 38.0 volts/mil
At 1475°F (801°C):	12.5 to 25.0 volts/mil
Modulus of Rupture:	450 PSI
Volume Resistivity:	
At 70°F (21°C):	10 ¹⁰ to 10 ¹¹ ohm-cm
At 750°F (399°C):	10 ⁹ to 10 ¹⁰ ohm-cm
At 1475°F (801°C):	10 ⁸ to 10 ⁹ ohm-cm

*Determined under laboratory conditions using applicable ASTM procedures. Actual field data may vary. Do not use Physical Properties for specifications.

NOTE

The Material Safety Data Sheet (MSDS) for the OMEGA[®] OB-600 cement is shipped with the product. Additional copies can be obtained by contacting OMEGA Engineering and asking for MSDS-0138.



OMEGAnet® Online Service
omega.com

Internet e-mail
info@omega.com

Servicing North America:

U.S.A.:
ISO 9001 Certified
Omega Engineering, Inc., One Omega Drive, P.O. Box 4047
Stamford, CT 06907-0047
Toll-Free: 1-800-826-6342 Tel: (203) 359-1660
FAX: (203) 359-7700 e-mail: info@omega.com

Canada:
976 Bergar
Laval (Quebec), H7L 5A1 Canada
Toll-Free: 1-800-826-6342 TEL: (514) 856-6928
FAX: (514) 856-6886 e-mail: info@omega.ca

For immediate technical or application assistance:

U.S.A. and Canada: Sales Service: 1-800-826-6342/1-800-TC-OMEGA®
Customer Service: 1-800-622-2378/1-800-622-BEST®
Engineering Service: 1-800-872-9436/1-800-USA-WHEN®

**Mexico/
Latin America** En Español: 001 (203) 359-7803 FAX: 000 (203) 359-7807
info@omega.com.mx e-mail: espanol@omega.com

Servicing Europe:

Benelux: Managed by the United Kingdom Office
Toll-Free: 0800 099 3344 TEL: +31 20 347 21 21
FAX: +31 20 643 46 43 e-mail: sales@omegaeng.nl

Czech Republic: Frystatska 184
733 01 Karviná, Czech Republic
Toll-Free: 0800-1-66342 TEL: +420-59-6311899
FAX: +420-59-6311114 e-mail: info@omegashop.cz

France: Managed by the United Kingdom Office
Toll-Free: 0800 466 342 TEL: +33 (0) 161 37 29 00
FAX: +33 (0) 130 57 54 27 e-mail: sales@omega.fr

Germany/Austria: Daimlerstrasse 26, D-75392 Deckenpfronn, Germany
Toll-Free: 0800 6397678 TEL: +49 (0) 7056 9398-0
FAX: +49 (0) 7056 9398-29 e-mail: info@omega.de

United Kingdom: OMEGA Engineering Ltd.
ISO 9001 Certified One Omega Drive, River Bend Technology Centre, Northbank
Irlam, Manchester M44 5BD United Kingdom
Toll-Free: 0800-488-488 TEL: +44 (0) 161 777-6611
FAX: +44 (0) 161 777-6622 e-mail: sales@omega.co.uk

It is the policy of OMEGA Engineering, Inc. to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification.

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.
WARNING: These products are not designed for use in, and should not be used for, human applications.



WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

1. Purchase Order number under which the product was PURCHASED,
2. Model and serial number of the product under warranty, and
3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

1. Purchase Order number to cover the COST of the repair,
2. Model and serial number of the product, and
3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2011 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.