

Insulators

Ceramic Bead, PFA, and Fiberglass Sleeving



MOST POPULAR MODELS HIGHLIGHTED!

Single Hole Round (SH)

Starts at
\$45/100



To Order (Specify Model Number)

Insulator Model No.	Price	Material/ Max Temp	Used With Wire Size AWG/Inch	Dimension*	
				Length mm (in)	OD mm (in)
SH-1-8-100	\$50	Mullite 1600°C (2910°F)	8/0.128	25 (1)	6.0 (1/4)
SH-1-14-100	45		14/0.064	25 (1)	4.5 (5/16)
SH-1-20-100	45		20/0.032	25 (1)	3.0 (1/8)
SH-1-24-100	45		24/0.020	25 (1)	1.5 (1/16)

Double Hole Round (DH)

Starts at
\$45/100




To Order (Specify Model Number)

Insulator Model No.	Price	Material/ Max Temp	Used With Wire Size AWG/Inch	Dimension*	
				Length mm (in)	OD mm (in)
DH-1-8-100	\$50	Mullite 1600°C (2910°F)	8/0.128	25 (1)	11.1 (7/16)
DH-1-14-100	45		14/0.064	25 (1)	7.0 (5/8)
DH-1-20-100	45		20/0.032	25 (1)	4.0 (5/32)
DH-1-24-100	45		24/0.020	25 (1)	3.0 (1/8)

Single Hole Fish Spine (FS)

\$25/500
\$45/1000



To Order (Specify Model Number)

Material/ Max Temp	Insulator Model No.	Used With Wire Size AWG/Inch	Dimension*	
			Length mm (in)	OD mm (in)
Steatite 1200°C (2190°F)	FS-400-8-(+)	8/0.128	10.2 (0.40)	10.2 (0.40)
	FS-330-10-(+)	10/0.102	8.38 (0.33)	8.38 (0.33)
	FS-260-8-(+)	8/0.128	6.60 (0.26)	6.60 (0.26)
	FS-260-12-(+)	12/0.081	6.60 (0.26)	6.60 (0.26)
	FS-200-14-(+)	14/0.064	5.08 (0.20)	5.08 (0.20)
	FS-170-18-(+)	18/0.040	4.32 (0.17)	4.32 (0.17)
	FS-125-20-(+)	20/0.032	3.18 (0.13)	3.18 (0.13)
	FS-110-20-(+)	20/0.032	2.79 (0.11)	2.79 (0.11)

† Specify quantity: 500 or 1000 pieces.

Double Hole Oval (OV)

Starts at
\$45/100



To Order (Specify Model Number)

Insulator Model No.	Price	Material/ Max Temp	Used With Wire Size AWG/Inch	Dimension*		
				Length mm (in)	OD mm (in)	Thickness mm (in)
OV-1-8-100	\$50	Mullite 1600°C (2910°F)	8/0.128	25 (1)	11.1 (7/16)	6.99 (0.275)
OV-1-14-100	45		14/0.064	25 (1)	8.0 (5/16)	5.16 (0.203)
OV-1-20-100	45		20/0.032	25 (1)	4.4 (11/64)	3.0 (0.118)

* All dimensions given are nominal figures only.

Fiberglass Sleeving

Fiberglass sleeving is ideal for insulating bare wire in applications not exceeding 480°C (900°F).



Gage	20	24	26	28	30
Color					
Black	FBGS BK 20	FBGS BK 24	FBGS BK 26	FBGS BK 28	FBGS BK 30
Yellow	FBGS Y 20	FBGS Y 24	FBGS Y 26	FBGS Y 28	FBGS Y 30
Blue	FBGS B 20	FBGS B 24	FBGS B 26	FBGS B 28	FBGS B 30
Purple	FBGS P 20	FBGS P 24	FBGS P 26	FBGS P 28	FBGS P 30
Red	FBGS R 20	FBGS R 24	FBGS R 26	FBGS R 28	FBGS R 30
Natural	FBGS N 20	FBGS N 24	FBGS N 26	FBGS N 28	FBGS N 30

\$0.25/ft >49 ft -20%, >99 ft -30%, >199 ft -40%
Ordering Example: FBGS-BK-20-200, black 20 gage fiberglass sleeving, (200 x \$0.25) - 20 = \$30.



PFA Tubing

PFA tubing is used for insulating wires in moist or corrosive environments where temperatures do not exceed 230°C (450°F).



Gage	20	24	26	28	30
Color					
Black	TF-BK 20	TF-BK 24	TF-BK 26	TF-BK 28	TF-BK 30
Blue	TF-B 20	TF-B 24	TF-B 26	TF-B 28	TF-B 30
Purple	TF-P 20	TF-P 24	TF-P 26	TF-P 28	TF-P 30
Red	TF-R 20	TF-R 24	TF-R 26	TF-R 28	TF-R 30
White	TF-W 20	TF-W 24	TF-W 26	TF-W 28	TF-W 30
Yellow	TF-Y 20	TF-Y 24	TF-Y 26	TF-Y 28	TF-Y 30

\$0.35/ft >49 ft -20%, >99 ft -30%, >199 ft -40%
Ordering Example: TF-R-20-200, red 20 gage PFA tubing, (200 x \$0.35) - 28 = \$42.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters