



Sanitary Thermocouple Assemblies

Standard Duty With Protection Head

TCS-S-NB9W Series

\$95

All Models




- ✓ Standard Duty 1/4" Probe Diameter
- ✓ 1 1/2" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
- ✓ White Polypropylene Head with Screw Cap Standard
- ✓ 316L SS Wetted Surfaces with 32 μin or Better Finish
- ✓ Ungrounded J, K, T or E Thermocouple, Special Limits of Error
- ✓ -50 to 200°C (-58 to 392°F) Temperature Range

Options

- ✓ Fitting Styles
- ✓ Protection Heads
- ✓ Probe Lengths

See A-156 For Additional Flange Sizes

The OMEGA® TCS-S-NB9W Series thermocouple probe assemblies are available in standard lengths from 3 to 6", with an ungrounded thermocouple probe with special limits of error. Standard probes are available in J, K, T and E calibrations. Standard features include a 1 1/2" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including probe lengths, protection heads and sanitary fitting styles.



3/4 NPT conduit connection.

Head Mounted Transmitters Available, See Page A-149

White polypropylene screw cover connection head.

316L SS 1 1/2" 16 AMP Tri-Grip™ cap standard.

For Complete Product Line Visit omega.com/sanitary

For Use in CIP and Sanitary Processes

TCS-TU-S-0300-D1-NB9W, \$95, shown smaller than actual size.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)				
Model No.	Price	Thermocouple Calibration	Sheath Diameter	Probe Length
TCS-(*)U-S-0300-D1-NB9W	\$95	J, K, T or E	1/4"	3"
TCS-(*)U-S-0400-D1-NB9W	95	J, K, T or E	1/4"	4"
TCS-(*)U-S-0500-D1-NB9W	95	J, K, T or E	1/4"	5"
TCS-(*)U-S-0600-D1-NB9W	95	J, K, T or E	1/4"	6"

* Specify calibration: J, K, T or E

To order with NB15 large stainless steel screw top head, change suffix "NB9W" in model number to "NB15" and add \$37 to price.

Note: Connection heads provided with nickel plated brass terminal blocks.

For lengths longer than 6", change "0300" in model number to the required length (12" = 1200, 9 1/4" = 0925) and add \$1 per additional inch to price.

Ordering Example: TCS-TU-S-0600-D1-NB9W, Type "T" ungrounded thermocouple, 1/4" diameter, 6" length, with 1 1/2" 16 AMP flange and NB9W white polypropylene screw cover head, \$95.



Sanitary Thermocouple Assemblies

Heavy-Duty With Protection Head

TCS-H-NB9W Series

\$125

All Models



- ✓ Heavy-Duty Probe Design with Stepped Probe Stem for Additional Strength
 - ✓ 1½" 16 AMP Tri-Grip™ (Tri-Clamp® Compatible) Fitting Standard
 - ✓ White Polypropylene Head with Screw Cap Standard
 - ✓ 316L SS Wetted Surfaces with 32 µin or Better Finish
 - ✓ Ungrounded J, K, T or E Thermocouple, Special Limits of Error
 - ✓ -50 to 200°C (-58 to 392°F) Temperature Range
- Options**
- ✓ Fitting Styles
 - ✓ Protection Heads
 - ✓ Probe Lengths

The OMEGA® TCS-H-NB9W Series thermocouple probe assemblies are available in standard lengths from 3 to 6", with an ungrounded thermocouple probe with special limits of error. Standard probes are available in J, K, T and E calibrations. These heavy-duty probes have a 3/8" diameter, which steps down to a 3/16" diameter at the probe tip, for fast response and additional strength. Standard features include a 1½" 16 AMP Tri-Grip™ fitting, type NB9W white polypropylene protection head with screw cap. Please consult sales for available options, including probe lengths, protection heads and sanitary fitting styles.



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)				
Model No.	Price	Thermocouple Calibration	Sheath Diameter**	Probe Length
TCS-(*)U-H-0300-D1-NB9W	\$125	J, K, T or E	3/8"	3"
TCS-(*)U-H-0400-D1-NB9W	125	J, K, T or E	3/8"	4"
TCS-(*)U-H-0500-D1-NB9W	125	J, K, T or E	3/8"	5"
TCS-(*)U-H-0600-D1-NB9W	125	J, K, T or E	3/8"	6"

* Specify calibration: J, K, T or E

** 3/8" diameter stepped down to 3/16" at the probe tip.

To order with NB15 large stainless steel screw top head, change suffix "NB9W" in model number to "NB15" and add \$37 to price.

Note: Connection heads provided with nickel plated brass terminal blocks.

For lengths longer than 6", change "0300" in model number to the required length (12" = 1200, 9¼" = 0925) and add \$2.50 per additional inch to price.

Ordering Example: TCS-TU-H-0600-D1-NB9W, Type "T" ungrounded thermocouple, heavy-duty design with 3/8" step-down diameter, 6" length, with 1½" 16 AMP flange and NB9W white polypropylene screw cover head, \$125.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters