

omega.com[®]

Ω OMEGA[®]

PHH-103

pH/mV/TEMPERATURE METER

INSTRUCTION
SHEET

M4318-0606

Shop online at: omega.com e-mail: info@omega.com
For latest product manuals: omegamanual.info



pH/mV/Temperature Meter

The PHH-103 is a Microprocessor based designed. The rugged housing and splash proof keyboard make the PHH-103 ideal for measurements outside of the laboratory. The large LCD displays pH and temperature values simultaneously, or can show millivolts. The PHH-103 has five memorized buffer values for fast, convenient and accurate calibration. User can perform a one-point calibration at any of these values, or a two-point calibration using any of the remaining buffer values, or adjust buffer values as needed under calibration mode and flash status by UP and DOWN key. the LCD display will indicate percentage of slope (PTS) to show the status of electrode after slope calibration. The PHH-103 has low battery consumption indicator and will auto shut off after 10 minutes of non use.

Specifications:

Range: 0.00 to 14.00 pH, +1999 mV, 0 to 100°C

Accuracy: 0.02 pH, 2 mV, 0.3°C

Resolution: 0.01 pH, 1 mV, 0.1°C

ATC: 0 to 100°C

Calibration: pH1.68, 4.00, 7.00, 10.00, 12.45

Battery: 9V

Dimensions: 108 x 75 x 30 mm

Weight: 135 g (with battery)

Accessories:

Upon receiving the shipment, inspect the container and equipment for any signs of damage. Remove the packing list and verify that you have received all equipment: Meter, pH electrode, temperature probe, Buffer solution 4.00 & 7.00, Battery 9V, Operating manual and rubber protective holster

Operating Procedure:

Preparation:

1. Open the battery compartment and connect the 9V battery.
2. Remove the protection cap from the electrode and connect to BNC input.

3. Turn on the power switch.

4. Rinse the electrode with clean water and wipe it dry.

Calibration:

1. Dip and stir the electrode into the buffer solution pH 7.00. Press and hold CAL key 3 second to into calibration mode. The display will appear CAL and flash 7.00. When the display stop flashing then it's end of calibration
2. Dip and stir the electrode into the buffer solution pH 4.00 and same as step 1.
Note: Calibration value can be adjusted as your buffer solution value under CAL mode and flash status by UP and DOWN key. For example, pH 6.86 instead of pH 7.00
3. After slope calibration, the LCD display will indicate percentage of slope (PTS) to show the status of electrode.

Measurement:

1. After calibration, rinse the electrode with clean water and wipe it dry. Dip the electrode into sample solution to be measured. Stir gently and wait until a stable reading can be obtained.
2. Press pH/mV key to change pH or ORP mode as needed.

Others:

1. Degree C and F can be changed by press and hold pH/mV key 3 second.
2. Automatic temperature compensation(ATC) mode by insert temperature probe. Manual temperature compensation mode by up and down key.
3. Auto shut off after 10 minutes of non use.
4. Change a new battery when the battery indicator flashing.

Applications:

Floriculture, Fish farming, Agriculture, Swimming pool & Spa, Waste water, Plating industry Food industry, Pharmaceutical & Medical, Cooling towers and Chemical industry.



OMEGAnet® Online Service
omega.com

Internet e-mail
info@omega.com

Servicing North America:

U.S.A.:
ISO 9001 Certified
One Omega Drive, Box 4047
Stamford, CT 06907-0047
Tel: (203) 359-1660
FAX: (203) 359-7700
e-mail: info@omega.com

Canada:
976 Bergar
Laval (Quebec) H7L 5A1, Canada
Tel: (514) 856-6928
FAX: (514) 856-6886
e-mail: info@omega.ca

For immediate technical or application assistance:

U.S.A. and Canada: Sales Service: 1-800-826-6342/1-800-TC-OMEGA®
Customer Service: 1-800-622-2378/1-800-622-BEST®
Engineering Service: 1-800-872-9436/1-800-USA-WHEN®

Mexico:
En Español: (001) 203-359-7803
FAX: (001) 203-359-7807
e-mail: espanol@omega.com
info@omega.com.mx

Servicing Europe:

Czech Republic: Frystatska 184, 733 01 Karviná, Czech Republic
Tel: +420 (0)59 6311899
FAX: +420 (0)59 6311114
Toll Free: 0800-1-66342
e-mail: info@omegashop.cz

Germany/Austria: Daimlerstrasse 26, D-75392 Deckenpfronn, Germany
Tel: +49 (0)7056 9398-0
FAX: +49 (0)7056 9398-29
Toll Free in Germany: 0800 639 7678
e-mail: info@omega.de

United Kingdom: One Omega Drive, River Bend Technology Centre
ISO 9002 Certified
Northbank, Irlam, Manchester
M44 5BD United Kingdom
Tel: +44 (0)161 777 6611
FAX: +44 (0)161 777 6622
Toll Free in United Kingdom: 0800-488-488
e-mail: sales@omega.co.uk

It is the policy of OMEGA Engineering, Inc. to comply with all worldwide safety and EMC/EMI regulations that apply. OMEGA is constantly pursuing certification of its products to the European New Approach Directives. OMEGA will add the CE mark to every appropriate device upon certification.

The information contained in this document is believed to be correct, but OMEGA accepts no liability for any errors it contains, and reserves the right to alter specifications without notice.
WARNING: These products are not designed for use in, and should not be used for, human applications.



WARRANTY/DISCLAIMER

OMEGA ENGINEERING, INC. warrants this unit to be free of defects in materials and workmanship for a period of **13 months** from date of purchase. OMEGA's WARRANTY adds an additional one (1) month grace period to the normal **one (1) year product warranty** to cover handling and shipping time. This ensures that OMEGA's customers receive maximum coverage on each product.

If the unit malfunctions, it must be returned to the factory for evaluation. OMEGA's Customer Service Department will issue an Authorized Return (AR) number immediately upon phone or written request. Upon examination by OMEGA, if the unit is found to be defective, it will be repaired or replaced at no charge. OMEGA's WARRANTY does not apply to defects resulting from any action of the purchaser, including but not limited to mishandling, improper interfacing, operation outside of design limits, improper repair, or unauthorized modification. This WARRANTY is VOID if the unit shows evidence of having been tampered with or shows evidence of having been damaged as a result of excessive corrosion; or current, heat, moisture or vibration; improper specification; misapplication; misuse or other operating conditions outside of OMEGA's control. Components in which wear is not warranted, include but are not limited to contact points, fuses, and triacs.

OMEGA is pleased to offer suggestions on the use of its various products. However, OMEGA neither assumes responsibility for any omissions or errors nor assumes liability for any damages that result from the use of its products in accordance with information provided by OMEGA, either verbal or written. OMEGA warrants only that the parts manufactured by the company will be as specified and free of defects. OMEGA MAKES NO OTHER WARRANTIES OR REPRESENTATIONS OF ANY KIND WHATSOEVER, EXPRESSED OR IMPLIED, EXCEPT THAT OF TITLE, AND ALL IMPLIED WARRANTIES INCLUDING ANY WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE HEREBY DISCLAIMED. LIMITATION OF LIABILITY: The remedies of purchaser set forth herein are exclusive, and the total liability of OMEGA with respect to this order, whether based on contract, warranty, negligence, indemnification, strict liability or otherwise, shall not exceed the purchase price of the component upon which liability is based. In no event shall OMEGA be liable for consequential, incidental or special damages.

CONDITIONS: Equipment sold by OMEGA is not intended to be used, nor shall it be used: (1) as a "Basic Component" under 10 CFR 21 (NRC), used in or with any nuclear installation or activity; or (2) in medical applications or used on humans. Should any Product(s) be used in or with any nuclear installation or activity, medical application, used on humans, or misused in any way, OMEGA assumes no responsibility as set forth in our basic WARRANTY/DISCLAIMER language, and, additionally, purchaser will indemnify OMEGA and hold OMEGA harmless from any liability or damage whatsoever arising out of the use of the Product(s) in such a manner.

RETURN REQUESTS / INQUIRIES

Direct all warranty and repair requests/inquiries to the OMEGA Customer Service Department. BEFORE RETURNING ANY PRODUCT(S) TO OMEGA, PURCHASER MUST OBTAIN AN AUTHORIZED RETURN (AR) NUMBER FROM OMEGA'S CUSTOMER SERVICE DEPARTMENT (IN ORDER TO AVOID PROCESSING DELAYS). The assigned AR number should then be marked on the outside of the return package and on any correspondence.

The purchaser is responsible for shipping charges, freight, insurance and proper packaging to prevent breakage in transit.

FOR **WARRANTY** RETURNS, please have the following information available BEFORE contacting OMEGA:

1. Purchase Order number under which the product was PURCHASED,
2. Model and serial number of the product under warranty, and
3. Repair instructions and/or specific problems relative to the product.

FOR **NON-WARRANTY** REPAIRS, consult OMEGA for current repair charges. Have the following information available BEFORE contacting OMEGA:

1. Purchase Order number to cover the COST of the repair,
2. Model and serial number of the product, and
3. Repair instructions and/or specific problems relative to the product.

OMEGA's policy is to make running changes, not model changes, whenever an improvement is possible. This affords our customers the latest in technology and engineering. OMEGA is a registered trademark of OMEGA ENGINEERING, INC.

© Copyright 2006 OMEGA ENGINEERING, INC. All rights reserved. This document may not be copied, photocopied, reproduced, translated, or reduced to any electronic medium or machine-readable form, in whole or in part, without the prior written consent of OMEGA ENGINEERING, INC.