



## Benchtop Weight Scale



WSB-8150, \$529, shown smaller than actual size.

WSB-8000 Series  
All Models

**\$529**



- ✓ Auto Calibration
- ✓ Easy-to-Read Black LCD Display with Backlight
- ✓ Overload Protection for Load-Cell
- ✓ Audible Beep Alert Upon Reaching Preset Target Weight
- ✓ Low-Battery and Charging Status Signal
- ✓ RS232 Interface with Windows® Software and Cable

### Specifications

#### Capacity:

- WSB-8015: 1.5 kg (3.3 lb)
- WSB-8030: 3 kg (6.6 lb)
- WSB-8060: 6 kg (13.2 lb)
- WSB-8150: 15 kg (33 lb)

#### Division:

- WSB-8015: 0.1 g (0.004 oz)
- WSB-8030: 0.2 g (0.007 oz)
- WSB-8060: 0.5 g (0.017 oz)
- WSB-8150: 1 g (0.035 oz)

**Platter:** 260 x 205 mm (10 x 8")  
**Display:** LCD 25.4 mm (1") H, 6-digit

**Power:** Rechargeable battery 6 Vdc/4.5 A and 110 Vac power cord (included)

**Battery Life:** 150 hours when fully charged

**MOST POPULAR MODEL HIGHLIGHTED!**

### To Order (Specify Model Number)

Model No.	Price	Description
WSB-8015	\$529	Weigh scale, 1.5 kg (3.3 lb) capacity and 0.1 g (0.004 oz) resolution
WSB-8030	529	Weigh scale, 3 kg (6.6 lb) capacity and 0.2 g (0.007 oz) resolution
WSB-8060	529	Weigh scale, 6 kg (13.2 lb) capacity and 0.5 g (0.017 oz) resolution
WSB-8150	529	Weigh scale, 15 kg (33 lb) capacity and 1 g (0.035 oz) resolution

Comes complete with 1.8 m (6') communication cables and Windows software, 6 Vdc battery, 110 Vac power cord, and operator's manual.

**Ordering Examples:** WSB-8030, benchtop scale 0 to 3 kg (6.6 lb) capacity, 0.2 kg (0.007 oz) resolution and RS232 communications, \$529.

WSB-8015, weigh scale 0 to 1.5 kg (3.3 lb) capacity, 0.1 g (0.004 oz) resolution and RS232 communications, \$529.

Each WSB-8000 Series benchtop scales feature a 6-key programming pad for easy set up. The conversion from kg to lbs, auto tare and auto zero are all easily done with individual buttons. The WSB-8000 is also light weight and durable with a large, stainless steel tray. Other features like overload protection and audible beep at preset target weight make the WSB-8000 a great choice for the classroom or laboratory. Other standard features include an RS232 interface and an easy-to-read backlit display. Low-battery and charging status are indicated on the display to help make sure your scale is always ready to use.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters