

SELECTION OF FLANGED IMMERSION HEATERS

Flanged Immersion Heater Selection Guide

Application	Solution or Heater Type	Alkaline or Acid Content (Est. % by Volume)	Sheath Material	Watt Density (Watts/In ²)	Max. Recommended Sheath Temp. (°F)
Water & Very Mild Solutions	Clean Water	pH 6 to pH 8 Neutral	Copper	45	350
	Process Water or Very Weak Solutions	pH 5 to pH 9 2-3%	Stainless Steel*	45	1200
	Weak Solutions	5-6%	Incoloy	45	1600
	Demineralized Deionized or Pure Water	—	Incoloy with Stainless Flange	45	1600
Corrosive & High Viscous Solution	Mild Corrosive Solution	5-15%	Stainless Steel*	23	1200
	More Severe Corrosive Solution	10-25%	Incoloy	23	1200
	Severe Corrosive Solution	30-60%	Incoloy with Stainless Flange	15	1600
Specialty Water Heating	Steam Boiler	Treated	Incoloy, Copper	—	1600
	Water Storage Tank	Treated	Copper	—	350
Oil Heating	Low Viscosity Oil	—	Steel	23	750
	Medium Viscosity Oil	—	Steel	15	750
	High Viscosity Oil	—	Steel	6.5	750
Oil Reservoir Heating	Lubrication Oil	—	Steel	15	750
Air, Gases & Steam Heating	Low Temperature	To 1100°F	Stainless Steel	23	1200
	High Temperature	To 1600°F	Incoloy	23	1600

*Passivated stainless steel recommended for water

Flanged Immersion Heater Types

Application	Flange Size (cm)	Sheath Material	Flange Material	Heater Type	Page	Application	Flange Size (cm)	Sheath Material	Flange Material	Heater Type	Page				
Clean water heater	3"(8)	Copper	Steel	TM	F-54	Demineralized or deionized water heater	3"(8)	Incoloy	SS	TMIS	F-61				
	5"(13)	Copper	Steel	TM			5"(13)	Incoloy	SS	TMIS					
	6"(15)	Copper	Steel	TM			Boiler & water heater	2½"sq.(6)	Copper	Steel		TTSF	F-68		
	8"(20)	Copper	Steel	TM				2½"sq.(6)	Incoloy	Steel		TTSF			
	10"(25)	Copper	Steel	TM				Storage water heater	3"(8)	Copper		Steel		TM	F-62
	12"(30)	Copper	Steel	TM					5"(13)	Copper		Steel		TM	
14"(36)	Copper	Steel	TM	6"(15)	Copper	Steel	TM								
Process water heater	3"(8)	SS	Steel	TMS	F-55	Light weight oil heater	3"(8)	Steel	Steel	TMO	F-63				
	5"(13)	SS	Steel	TMS			5"(13)	Steel	Steel	TMO					
	6"(15)	SS	Steel	TMS			6"(15)	Steel	Steel	TMO					
	8"(20)	SS	Steel	TMS			8"(8)	Steel	Steel	TMO					
Solution water heaters	3"(8)	Incoloy	Steel	TMI	F-56		10"(25)	Steel	Steel	TMO					
	5"(13)	Incoloy	Steel	TMI			12"(30)	Steel	Steel	TMO					
	6"(15)	Incoloy	Steel	TMI			14"(36)	Steel	Steel	TMO					
	8"(20)	Incoloy	Steel	TMI											
Mild corrosive heaters	3"(8)	SS	Steel	TMS	F-58	Medium weight oil heater	3"(8)	Steel	Steel	TMO	F-65				
	5"(13)	SS	Steel	TMS			5"(13)	Steel	Steel	TMO					
	6"(15)	SS	Steel	TMS			6"(15)	Steel	Steel	TMO					
	8"(20)	SS	Steel	TMS											
Corrosive solution & gas heaters	3"(8)	Incoloy	Steel	TMI	F-59	Heavy weight oil heater	3"(8)	Steel	Steel	TMO	F-66				
	5"(13)	Incoloy	Steel	TMI			5"(13)	Steel	Steel	TMO					
	6"(15)	Incoloy	Steel	TMI			8"(20)	Steel	Steel	TMO					
	8"(20)	Incoloy	Steel	TMI		Sump oil heaters	3"(8)	Steel	Steel	TMO	F-67				
	10"(25)	Incoloy	Steel	TMI											
	12"(30)	Incoloy	Steel	TMI			Food equipment heater		Copper	Brass		TTUH-CO	F-69		
14"(36)	Incoloy	Steel	TMI					TTUH							
Severe corrosive solution heater	3"(8)	Incoloy	SS	TMIS	F-60										
	5"(13)	Incoloy	SS	TMIS											
	6"(15)	Incoloy	SS	TMIS											



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters