

ITS-90 Thermocouple Direct and Inverse Polynomials

Direct Polynomials provide the thermoelectric voltage (μV) from a known temperature ($^{\circ}\text{C}$); Inverse Polynomials provide the temperature ($^{\circ}\text{C}$) from a known thermoelectric voltage (μV).

Type J Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature t_{90} , for the indicated temperature ranges. The equations are of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-210 to 760 $^{\circ}\text{C}$	760 to 1,200 $^{\circ}\text{C}$
$c_0 =$	0.000 000 000 0	2.964 562 568 1 $\times 10^5$
$c_1 =$	5.038 118 781 5 $\times 10^1$	-1.497 612 778 6 $\times 10^3$
$c_2 =$	3.047 583 693 0 $\times 10^{-2}$	3.178 710 392 4
$c_3 =$	-8.568 106 572 0 $\times 10^{-5}$	-3.184 768 670 1 $\times 10^{-3}$
$c_4 =$	1.322 819 529 5 $\times 10^{-7}$	1.572 081 900 4 $\times 10^{-6}$
$c_5 =$	-1.705 295 833 7 $\times 10^{-10}$	-3.069 136 905 6 $\times 10^{-10}$
$c_6 =$	2.094 809 069 7 $\times 10^{-13}$	
$c_7 =$	-1.253 839 533 6 $\times 10^{-16}$	
$c_8 =$	1.563 172 569 7 $\times 10^{-20}$	

Type J Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-210 to 0 $^{\circ}\text{C}$	0 to 760 $^{\circ}\text{C}$	760 to 1,200 $^{\circ}\text{C}$
Voltage Range:	-8,095 to 0 μV	0 to 42,919 μV	42,919 to 69,553 μV
$c_0 =$	0.000 000 0	0.000 000	-3.113 581 87 $\times 10^3$
$c_1 =$	1.952 826 8 $\times 10^{-2}$	1.978 425 $\times 10^{-2}$	3.005 436 84 $\times 10^{-1}$
$c_2 =$	-1.228 618 5 $\times 10^{-6}$	-2.001 204 $\times 10^{-7}$	-9.947 732 30 $\times 10^{-6}$
$c_3 =$	-1.075 217 8 $\times 10^{-9}$	1.036 969 $\times 10^{-11}$	1.702 766 30 $\times 10^{-10}$
$c_4 =$	-5.908 693 3 $\times 10^{-13}$	-2.549 687 $\times 10^{-16}$	-1.430 334 68 $\times 10^{-15}$
$c_5 =$	-1.725 671 3 $\times 10^{-16}$	3.585 153 $\times 10^{-21}$	4.738 860 84 $\times 10^{-21}$
$c_6 =$	-2.813 151 3 $\times 10^{-20}$	-5.344 285 $\times 10^{-26}$	
$c_7 =$	-2.396 337 0 $\times 10^{-24}$	5.099 890 $\times 10^{-31}$	
$c_8 =$	-8.382 332 1 $\times 10^{-29}$		
Error Range:	0.03 to -0.05 $^{\circ}\text{C}$	0.04 to -0.04 $^{\circ}\text{C}$	0.03 to -0.04 $^{\circ}\text{C}$

Type K Thermocouples - coefficients α_0 , α_1 and α_2 , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equation below 0 $^{\circ}\text{C}$ is of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

the equation above 0 $^{\circ}\text{C}$ is of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i + \alpha_0 e^{\alpha_1 (t_{90} - 126.9686)^2}$$

where e is the natural logarithm constant, E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	Coefficients
-270 to 0 $^{\circ}\text{C}$	$c_0 =$ 0.000 000 000 0
	$c_1 =$ 3.945 012 802 5 $\times 10^1$
	$c_2 =$ 2.362 237 359 8 $\times 10^{-2}$
	$c_3 =$ -3.285 890 678 4 $\times 10^{-4}$
	$c_4 =$ -4.990 482 877 7 $\times 10^{-6}$
	$c_5 =$ -6.750 905 917 3 $\times 10^{-8}$
	$c_6 =$ -5.741 032 742 8 $\times 10^{-10}$
	$c_7 =$ -3.108 887 289 4 $\times 10^{-12}$
	$c_8 =$ -1.045 160 936 5 $\times 10^{-14}$
	$c_9 =$ -1.988 926 687 8 $\times 10^{-17}$
	$c_{10} =$ -1.632 269 748 6 $\times 10^{-20}$
0 to 1372 $^{\circ}\text{C}$	$c_0 =$ -1.760 041 368 6 $\times 10^1$
	$c_1 =$ 3.892 120 497 5 $\times 10^1$
	$c_2 =$ 1.855 877 003 2 $\times 10^{-2}$
	$c_3 =$ -9.945 759 287 4 $\times 10^{-5}$
	$c_4 =$ 3.184 094 571 9 $\times 10^{-7}$
	$c_5 =$ -5.607 284 488 9 $\times 10^{-10}$
	$c_6 =$ 5.607 505 905 9 $\times 10^{-13}$
	$c_7 =$ -3.202 072 000 3 $\times 10^{-16}$
	$c_8 =$ 9.715 114 715 2 $\times 10^{-20}$
	$c_9 =$ -1.210 472 127 5 $\times 10^{-23}$
	$\alpha_0 =$ 1.185 976 $\times 10^2$
$\alpha_1 =$ -1.183 432 $\times 10^{-4}$	

Type K Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-200 to 0 $^{\circ}\text{C}$	0 to 500 $^{\circ}\text{C}$	500 to 1,372 $^{\circ}\text{C}$
Voltage Range:	-5891 to 0 μV	0 to 20,644 μV	20,644 to 54,886 μV
$c_0 =$	0.000 000 0	0.000 000	-1.318 058 $\times 10^2$
$c_1 =$	2.517 346 2 $\times 10^{-2}$	2.508 355 $\times 10^{-2}$	4.830 222 $\times 10^{-2}$
$c_2 =$	-1.166 287 8 $\times 10^{-6}$	7.860 106 $\times 10^{-8}$	-1.646 031 $\times 10^{-6}$
$c_3 =$	-1.083 363 8 $\times 10^{-9}$	-2.503 131 $\times 10^{-10}$	5.464 731 $\times 10^{-11}$
$c_4 =$	-8.977 354 0 $\times 10^{-13}$	8.315 270 $\times 10^{-14}$	-9.650 715 $\times 10^{-16}$
$c_5 =$	-3.734 237 7 $\times 10^{-16}$	-1.228 034 $\times 10^{-17}$	8.802 193 $\times 10^{-21}$
$c_6 =$	-8.663 264 3 $\times 10^{-20}$	9.804 036 $\times 10^{-22}$	-3.110 810 $\times 10^{-26}$
$c_7 =$	-1.045 059 8 $\times 10^{-23}$	-4.413 030 $\times 10^{-26}$	
$c_8 =$	-5.192 057 7 $\times 10^{-28}$	1.057 734 $\times 10^{-30}$	
$c_9 =$		-1.052 755 $\times 10^{-35}$	
Error Range:	0.04 $^{\circ}\text{C}$ to -0.02 $^{\circ}\text{C}$	0.04 $^{\circ}\text{C}$ to -0.05 $^{\circ}\text{C}$	0.06 $^{\circ}\text{C}$ to -0.05 $^{\circ}\text{C}$

Adapted from NIST Monograph 175, *Temperature-Electromotive Force Reference Functions and Tables for the Letter-Designated Thermocouple Types Based on the ITS-90*, by G.W. Burns, M.G. Scroger, G.F. Strouse, M.C. Croarkin, and W.F. Guthrie, 1993. Not copyrightable in the United States.

ITS-90 Thermocouple Direct & Inverse Polynomials cont'd

Type T Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-270 to 0°C	0 to 400°
$C_0 =$	0.000 000 000 0....	0.000 000 000 0....
$C_1 =$	3.874 810 636 4 x10 ¹	3.874 810 636 4 x10 ¹
$C_2 =$	4.419 443 434 7 x 10 ⁻²	3.329 222 788 0 x10 ⁻²
$C_3 =$	1.184 432 310 5 x 10 ⁻⁴	2.061 824 340 4 x 10 ⁻⁴
$C_4 =$	2.003 297 355 4 x 10 ⁻⁵	-2.188 225 684 6 x 10 ⁻⁶
$C_5 =$	9.013 801 955 9 x 10 ⁻⁷	1.099 688 092 8 x 10 ⁻⁸
$C_6 =$	2.265 115 659 3 x 10 ⁻⁹	-3.081 575 877 2 x 10 ⁻¹¹
$C_7 =$	3.607 115 420 5 x 10 ⁻¹⁰	4.547 913 529 0 x 10 ⁻¹⁴
$C_8 =$	3.849 393 988 3 x 10 ⁻¹²	-2.751 290 167 3 x 10 ⁻¹⁷
$C_9 =$	2.821 352 192 5 x 10 ⁻¹⁴	
$C_{10} =$	1.425 159 477 9 x 10 ⁻¹⁶	
$C_{11} =$	4.876 866 228 6 x 10 ⁻¹⁹	
$C_{12} =$	1.079 553 927 0 x 10 ⁻²¹	
$C_{13} =$	1.394 502 706 2 x 10 ⁻²⁴	
$C_{14} =$	7.979 515 392 7 x 10 ⁻²⁸	

Type T Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-200 to 0°C	0 to 400°C
Voltage Range:	-5,603 to 0 μV	0 to 20,872 μV
$C_0 =$	0.000 000 0....	0.000 000
$C_1 =$	2.594 919 2 x 10 ⁻²	2.592 800 x 10 ⁻²
$C_2 =$	-2.131 696 7 x 10 ⁻⁷	-7.602 961 x 10 ⁻⁷
$C_3 =$	7.901 869 2 x 10 ⁻¹⁰	4.637 791 x 10 ⁻¹¹
$C_4 =$	4.252 777 7 x 10 ⁻¹³	-2.165 394 x 10 ⁻¹⁵
$C_5 =$	1.330 447 3 x 10 ⁻¹⁶	6.048 144 x 10 ⁻²⁰
$C_6 =$	2.024 144 6 x 10 ⁻²⁰	-7.293 422 x 10 ⁻²⁵
$C_7 =$	1.266 817 1 x 10 ⁻²⁴	
Error Range:	0.04 to -0.02°C	0.03 to -0.03°C

Type E Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-270 to 0°C	0 to 400°C
$C_0 =$	0.000 000 000 0	0.000 000 000 0
$C_1 =$	5.866 550 870 8 x10 ¹	5.866 550 871 0 x10 ¹
$C_2 =$	4.541 097 712 4 x 10 ⁻²	4.503 227 558 2 x10 ⁻²
$C_3 =$	-7.799 804 868 6 x 10 ⁻⁴	2.890 840 721 2 x 10 ⁻⁵
$C_4 =$	-2.580 016 084 3 x 10 ⁻⁵	-3.305 689 665 2 x 10 ⁻⁷
$C_5 =$	-5.945 258 305 7 x 10 ⁻⁷	6.502 440 327 0 x 10 ⁻¹⁰
$C_6 =$	-9.321 405 866 7 x 10 ⁻⁹	-1.919 749 550 4 x 10 ⁻¹³
$C_7 =$	-1.028 760 553 4 x 10 ⁻¹⁰	-1.253 660 049 7 x 10 ⁻¹⁵
$C_8 =$	-8.037 012 362 1 x 10 ⁻¹³	2.148 921 756 9 x 10 ⁻¹⁸
$C_9 =$	-4.397 949 739 1 x 10 ⁻¹⁵	-1.438 804 178 2 x 10 ⁻²¹
$C_{10} =$	-1.641 477 635 5 x 10 ⁻¹⁷	3.596 089 948 1 x 10 ⁻²⁵
$C_{11} =$	-3.967 361 951 6 x 10 ⁻²⁰	
$C_{12} =$	-5.582 732 872 1 x 10 ⁻²³	
$C_{13} =$	-3.465 784 201 3 x 10 ⁻²⁶	

Type E Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-200 to 0°C	0 to 1,000°C
Voltage Range:	-8,825 to 0 μV	0 to 76,373 μV
$C_0 =$	0.000 000 0	0.000 000 0
$C_1 =$	1.697 728 8 x 10 ⁻²	1.705 703 5 x 10 ⁻²
$C_2 =$	-4.351 497 0 x 10 ⁻⁷	-2.330 175 9 x 10 ⁻⁷
$C_3 =$	-1.585 969 7 x 10 ⁻¹⁰	6.543 558 5 x 10 ⁻¹²
$C_4 =$	-9.250 287 1 x 10 ⁻¹⁴	-7.356 274 9 x 10 ⁻¹⁷
$C_5 =$	-2.608 431 4 x 10 ⁻¹⁷	-1.789 600 1 x 10 ⁻²¹
$C_6 =$	-4.136 019 9 x 10 ⁻²¹	8.403 616 5 x 10 ⁻²⁶
$C_7 =$	-3.403 403 0 x 10 ⁻²⁵	-1.373 587 9 x 10 ⁻³⁰
$C_8 =$	-1.156 489 0 x 10 ⁻²⁹	1.062 982 3 x 10 ⁻³⁵
$C_9 =$		-3.244 708 7 x 10 ⁻⁴¹
Error Range:	0.03 to -0.01°C	0.02 to -0.02°C

Type N Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-270 to 0°C	0 to 1,300°C
$C_0 =$	0.000 000 000 0....	0.000 000 000 0....
$C_1 =$	2.615 910 596 2 x 10 ¹	2.592 939 460 1 x 10 ¹
$C_2 =$	1.095 748 422 8 x 10 ⁻²	1.571 014 188 0 x 10 ⁻²
$C_3 =$	-9.384 111 155 4 x 10 ⁻⁵	4.382 562 723 7 x 10 ⁻⁵
$C_4 =$	-4.641 203 975 9 x 10 ⁻⁸	-2.526 116 979 4 x 10 ⁻⁷
$C_5 =$	-2.630 335 771 6 x 10 ⁻⁹	6.431 181 933 9 x 10 ⁻¹⁰
$C_6 =$	-2.265 343 800 3 x 10 ⁻¹¹	-1.006 347 151 9 x 10 ⁻¹²
$C_7 =$	-7.608 930 079 1 x 10 ⁻¹⁴	9.974 533 899 2 x 10 ⁻¹⁶
$C_8 =$	-9.341 966 783 5 x 10 ⁻¹⁷	-6.086 324 560 7 x 10 ⁻¹⁹
$C_9 =$		2.084 922 933 9 x 10 ⁻²²
$C_{10} =$		-3.068 219 615 1 x 10 ⁻²⁶

Type N Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots + c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-200 to 0°C	0 to 600°C	600 to 1,300°C	0 to 1,300°C
Voltage Range:	-3,990 to 0 μV	0 to 20,613 μV	20,613 to 47,513 μV	0 to 47,513 μV
$C_0 =$	0.000 000 0	0.000 00	1.972 485 x 10 ¹	0.000 000 0
$C_1 =$	3.843 684 7 x 10 ⁻²	3.868 96 x 10 ⁻²	3.300 943 x 10 ⁻²	3.878 327 7 x 10 ⁻²
$C_2 =$	1.101 048 5 x 10 ⁻⁶	-1.082 67 x 10 ⁻⁶	-3.915 159 x 10 ⁻⁷	-1.161 234 4 x 10 ⁻⁶
$C_3 =$	5.222 931 2 x 10 ⁻⁹	4.702 05 x 10 ⁻¹¹	9.855 391 x 10 ⁻¹²	6.952 565 5 x 10 ⁻¹¹
$C_4 =$	7.206 052 5 x 10 ⁻¹²	-2.121 69 x 10 ⁻¹⁸	-1.274 371 x 10 ⁻¹⁶	-3.009 007 7 x 10 ⁻¹⁵
$C_5 =$	5.848 858 6 x 10 ⁻¹⁵	-1.172 72 x 10 ⁻¹⁹	7.767 022 x 10 ⁻²²	8.831 158 4 x 10 ⁻²⁰
$C_6 =$	2.775 491 6 x 10 ⁻¹⁸	5.392 80 x 10 ⁻²⁴		-1.621 383 9 x 10 ⁻²⁴
$C_7 =$	7.707.516 6 x 10 ⁻²²	-7.981 56 x 10 ⁻²⁹		1.669 336 2 x 10 ⁻²⁹
$C_8 =$	1.158 266 5 x 10 ⁻²⁵			-7.311 754 0 x 10 ⁻³⁵
$C_9 =$	7.313 886 8 x 10 ⁻³⁰			
Error Range:	0.03 to -0.02°C	0.03 to -0.02°C	0.02 to -0.04°C	0.06 to -0.06°C

Type B Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the form:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	0 to 630.615°C	630.615 to 1,820°C
$C_0 =$	0.000 000 000 0	-3.893 816 862 1 x 10 ³
$C_1 =$	-2.465 081 834 6 x 10 ⁻¹	2.857 174 747 0 x 10 ¹
$C_2 =$	5.904 042 117 1 x 10 ⁻³	-8.488 510 478 5 x 10 ⁻²
$C_3 =$	-1.325 793 163 6 x 10 ⁻⁶	1.578 528 016 4 x 10 ⁻⁴
$C_4 =$	1.566 829 190 1 x 10 ⁻⁹	-1.683 534 486 4 x 10 ⁻⁷
$C_5 =$	-1.694 452 924 0 x 10 ⁻¹²	1.110 979 401 3 x 10 ⁻¹⁰
$C_6 =$	6.229 034 709 4 x 10 ⁻¹⁶	-4.451 543 103 3 x 10 ⁻¹⁴
$C_7 =$		9.897 564 082 1 x 10 ⁻¹⁸
$C_8 =$		-9.379 133 028 9 x 10 ⁻²²

Type B Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots + c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	250 to 700°C	700 to 1,820°C
Voltage Range:	291 to 2,431 μV	2,431 to 13,820 μV
$C_0 =$	9.842 332 1 x 10 ¹	2.131 507 1 x 10 ²
$C_1 =$	6.997 150 0 x 10 ⁻¹	2.851 050 4 x 10 ⁻¹
$C_2 =$	-8.476 530 4 x 10 ⁻⁴	-5.274 288 7 x 10 ⁻⁵
$C_3 =$	1.005 264 4 x 10 ⁻⁶	9.916 080 4 x 10 ⁻⁹
$C_4 =$	-8.334 595 2 x 10 ⁻¹⁰	-1.296 530 3 x 10 ⁻¹²
$C_5 =$	4.550 854 2 x 10 ⁻¹³	1.119 587 0 x 10 ⁻¹⁶
$C_6 =$	-1.552 303 7 x 10 ⁻¹⁶	-6.062 519 9 x 10 ⁻²¹
$C_7 =$	2.988 675 0 x 10 ⁻²⁰	1.866 169 6 x 10 ⁻²⁵
$C_8 =$	-2.474 286 0 x 10 ⁻²⁴	-2.487 858 5 x 10 ⁻³⁰
Error Range:	0.03 to -0.02°C	0.02 to -0.01°C

ITS-90 Thermocouple Direct & Inverse Polynomials cont'd

Type R Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the for:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-50 to 1,064.18°C	1,064.18 to 1,664.5°C	1,664.5 to 1,768.1°C
$C_0 =$	0.000 000 000 0	2.951 579 253 16 x 10 ³	1.522 321 182 09 x 10 ⁵
$C_1 =$	5.289 617 297 65	-2.520 612 513 32	-2.688 198 885 45 x 10 ²
$C_2 =$	1.391 665 897 82 x 10 ⁻²	1.595 645 018 65 x 10 ⁻²	1.712 802 804 71 x 10 ⁻¹
$C_3 =$	-2.388 556 930 17 x 10 ⁻⁵	-7.640 859 475 76 x 10 ⁻⁶	-3.458 957 064 53 x 10 ⁻⁵
$C_4 =$	3.569 160 010 63 x 10 ⁻⁸	2.053 052 910 24 x 10 ⁻⁹	-9.346 339 710 46 x 10 ⁻¹²
$C_5 =$	-4.623 476 662 98 x 10 ⁻¹¹	-2.933 596 681 73 x 10 ⁻¹³	
$C_6 =$	5.007 774 410 34 x 10 ⁻¹⁴		
$C_7 =$	-3.731 058 861 91 x 10 ⁻¹⁷		
$C_8 =$	1.577 164 823 67 x 10 ⁻²⁰		
$C_9 =$	-2.810 386 252 51 x 10 ⁻²⁴		

Type R Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots + c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-50°C to 250°C	250 to 1,200°C	1,064 to 1,664.5°C	1,664.5 to 1,768.1°C
Voltage Range:	-226 to 1,923 μV	1,923 to 13,228 μV	11,361 to 19,739 μV	19,739 to 21,103 μV
$C_0 =$	0.000 000 0	1.334 584 505 x 10 ¹	-8.199 599 416 x 10 ¹	3.406 177 836 x 10 ⁴
$C_1 =$	1.889 138 0 x 10 ⁻¹	1.472 644 573 x 10 ⁻¹	1.553 962 042 x 10 ⁻¹	-7.023 729 171
$C_2 =$	-9.383 529 0 x 10 ⁻⁵	-1.844 024 844 x 10 ⁻⁵	-8.342 197 663 x 10 ⁻⁶	5.582 903 813 x 10 ⁻⁴
$C_3 =$	1.306 861 9 x 10 ⁻⁷	4.031 129 x 726 10 ⁻⁹	4.279 433 549 x 10 ⁻¹⁰	-1.952 394 635 x 10 ⁻⁸
$C_4 =$	-2.270 358 0 x 10 ⁻¹⁰	-6.249 428 360 x 10 ⁻¹³	-1.191 577 910 x 10 ⁻¹⁴	2.560 740 231 x 10 ⁻¹³
$C_5 =$	3.514 565 9 x 10 ⁻¹³	6.468 412 046 x 10 ⁻¹⁷	1.492 290 091 x 10 ⁻¹⁹	
$C_6 =$	-3.895 390 0 x 10 ⁻¹⁶	-4.458 750 426 x 10 ⁻²¹		
$C_7 =$	2.823.947 1 x 10 ⁻¹⁹	1.994 710 146 x 10 ⁻²⁵		
$C_8 =$	-1.260 728 1 x 10 ⁻²²	-5.313 401 790 x 10 ⁻³⁰		
$C_9 =$	3.135 361 1 x 10 ⁻²⁶	6.481 976 217 x 10 ⁻³⁵		
$C_{10} =$	-3.318 776 9 x 10 ⁻³⁰			
Error Range:	0.02 to -0.02°C	0.005 to -0.005°C	0.001 to -0.0005°C	0.002 to -0.001°C

Type S Thermocouples - coefficients, c_i , of reference equations giving the thermoelectric voltage, E , as a function of temperature, t_{90} , for the indicated temperature ranges. The equations are of the for:

$$E = \sum_{i=0}^n c_i (t_{90})^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-50 to 1,064.18°C	1,064.18 to 1,664.5°C	1,664.5 to 1,768.1°C
$C_0 =$	0.000 000 000 0	1.329 004 450 85 x 10 ³	1.466 282 326 36 x 10 ⁵
$C_1 =$	5.403 133 086 31....	3.345 093 113 44	-2.584 305 167 52 x 10 ²
$C_2 =$	-8.005 040 62 x 10 ⁻⁵	6.548 051 928 18 x 10 ⁻³	1.636 935 746 41 x 10 ⁻¹
$C_3 =$	-2.324 779 686 89 x 10 ⁻⁵	-1.648 562 592 09 x 10 ⁻⁶	-3.304 390 469 87 x 10 ⁻⁵
$C_4 =$	3.220 288 230 36 x 10 ⁻⁸	1.299 896 051 74 x 10 ⁻¹¹	-9.432 236 906 12 x 10 ⁻¹²
$C_5 =$	-3.314 651 963 89 x 10 ⁻¹¹		
$C_6 =$	2.557 442 517 86 x 10 ⁻¹⁴		
$C_7 =$	-1.250 688 713 93 x 10 ⁻¹⁷		
$C_8 =$	2.714 431 761 45 x 10 ⁻²¹		

Type S Thermocouples - coefficients of approximate inverse functions giving temperature, t_{90} , as a function of the thermoelectric voltage, E , in selected temperature and voltage ranges. The functions are of the form:

$$t_{90} = c_0 + c_1 E + c_2 E^2 + \dots + c_i E^i$$

where E is in microvolts and t_{90} is in degrees Celsius.

Temperature Range:	-50 to 250°C	250 to 1,200°C	1,064 to 1,664.5°C	1,664.5 to 1,768.1°C
Voltage Range:	-235 to 1,874 μV	1,874 to 11,950 μV	10,332 to 17,536 μV	17,536 to 18,693 μV
$C_0 =$	0.000 000 0	1.291 507 177 x 10 ¹	-8.087 801 117 x 10 ¹	5.333 875 126 x 10 ⁴
$C_1 =$	1.849 494 60 x 10 ⁻¹	1.466 298 863 x 10 ⁻¹	1.621 573 104 x 10 ⁻¹	-1.235 892 298 x 10 ¹
$C_2 =$	-8.005 040 62 x 10 ⁻⁵	-1.534 713 402 x 10 ⁻⁵	-8.536 869 453 x 10 ⁻⁶	1.092 657 613 x 10 ⁻³
$C_3 =$	1.022 374 30 x 10 ⁻⁷	3.145 945 973 x 10 ⁻⁹	4.719 686 976 x 10 ⁻¹⁰	-4.265 693 686 x 10 ⁻⁸
$C_4 =$	-1.522 485 92 x 10 ⁻¹⁰	-4.163 257 839 x 10 ⁻¹³	-1.441 693 666 x 10 ⁻¹⁴	6.247 205 420 x 10 ⁻¹³
$C_5 =$	1.888 213 43 x 10 ⁻¹³	3.187 963 771 x 10 ⁻¹⁷	2.081 618 890 x 10 ⁻¹⁹	
$C_6 =$	-1.590 859 41 x 10 ⁻¹⁶	-1.291 637 500 x 10 ⁻²¹		
$C_7 =$	8.230 278 80 x 10 ⁻²⁰	2.183 475 087 x 10 ⁻²⁶		
$C_8 =$	-2.341 819 44 x 10 ⁻²³	-1.447 379 511 x 10 ⁻³¹		
$C_9 =$	2.797 862 60 x 10 ⁻²⁷	8.211 272 125 x 10 ⁻³⁶		
Error Range:	0.02 to -0.02°C	0.01 to -0.01°C	0.0002 to -0.0002°C	0.002 to -0.002°C



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters