


OHM'S LAW



VARIATIONS OF OHM'S LAW

VOLTS

$$\text{VOLTS} = \frac{\text{WATTS}}{\text{AMPERES}}$$

$$\text{VOLTS} = \frac{\text{WATTS}}{\text{AMPERES}}$$

$$\text{VOLTS} = \text{AMPERES} \times \text{OHMS}$$

OHMS

$$\text{OHMS} = \frac{\text{VOLTS}}{\text{AMPERES}}$$

$$\text{OHMS} = \frac{\text{VOLTS}^2}{\text{WATTS}}$$

$$\text{OHMS} = \frac{\text{WATTS}^2}{\text{AMPERES}^2}$$

AMPERES

$$\text{AMPERES} = \frac{\text{VOLTS}}{\text{OHMS}}$$

$$\text{AMPERES} = \frac{\text{WATTS}}{\text{VOLTS}}$$

$$\text{AMPERES} = \frac{\text{WATTS}}{\text{OHMS}}$$

WATTS

$$\text{WATTS} = \frac{\text{VOLTS}^2}{\text{OHMS}}$$

$$\text{WATTS} = \text{AMPERES}^2 \times \text{OHMS}$$

$$\text{WATTS} = \text{VOLTS} \times \text{AMPERES}$$

Table 11 Currents for resistance heating loads

kW	Single phase					Three phase balanced load			
	120V	208V	240V	440V	480V	208V	240V	440V	480V
1	8.4	4.8	4.2	2.3	2.1	2.8	2.5	1.4	1.3
2	16.7	9.7	8.4	4.6	4.2	5.6	4.9	2.7	2.5
3	25	14.5	12.5	6.9	6.3	8.4	7.3	4	3.7
4	33.4	19.3	16.7	9.1	8.4	11.2	9.7	5.3	4.9
5	41.7	24.1	20.9	11.4	10.5	13.9	12.1	6.6	6.1
6	50	28.9	25	13.7	12.5	16.7	14.5	7.9	7.3
7.5	62.5	36.1	31.3	17.1	15.7	20.9	18.1	9.9	9.1
10	83.4	48.1	41.7	22.8	20.9	27.8	24.1	13.2	12.1
12	100	57.7	50	27.3	25	33.4	29	15.8	14.5
15	125	72.2	62.5	34.1	31.2	41.7	36.2	19.7	18.1
20	167	96.2	83.4	45.5	41.7	55.6	48.2	26.3	24.1
25	209	121	105	56.9	52.1	69.5	60.3	32.9	30.1
30	250	145	125	68.2	62.5	83.4	72.3	39.4	36.2
50	417	241	209	114	105	139	121	65.7	60.3
75	625	361	313	171	157	209	181	98.6	90.4
100	834	481	417	228	209	278	241	132	121

Currents for resistance heating loads
 Heating elements are frequently used at voltages other than those shown in our catalog. The percentages shown below are used to determine the resulting wattage. Should you wish to use a heater on a voltage not shown above, you may calculate the resultant wattage with this formula:

$$\text{Actual Wattage} = \text{Rated Wattage} \times \frac{\text{Applied Voltage}^2}{\text{Rated Voltage}^2}$$

Percent of rated wattage for various applied voltages

Applied Voltage	Rated Voltage													
	110	115	120	208	220	230	240	277	380	415	440	460	480	550
110	100%	91%	84%	28%	25%	23%	21%	16%	8.4%	7%	6.2%	5.7%	5.2%	4%
115	109%	100%	92%	31%	27%	25%	23%	17%	9.0%	7.6%	6.7%	6.2%	5.7%	4.3%
120	119%	109%	100%	33%	30%	27%	25%	19%	10%	8.4%	7.4%	6.8%	6.3%	4.8%
208			300%	100%	89%	82%	75%	56%	30%	25%	22%	20%	19%	14%
220				112%	100%	91%	84%	63%	34%	28%	25%	23%	21%	16%
230				122%	109%	100%	92%	69%	37%	31%	27%	25%	23%	17%
240				133%	119%	109%	100%	75%	40%	33%	30%	27%	25%	19%
277							133%	100%	53%	45%	40%	37%	33%	25%
380								188%	100%	84%	74%	68%	63%	47%
415									119%	100%	89%	81%	75%	57%
440										112%	100%	91%	84%	64%
460										123%	109%	100%	92%	70%
480											119%	109%	100%	76%
550											156%	143%	131%	100%



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters