

Fast-Response Infrared Fiber Optic Thermometer/ Transmitter

With Local Display and Analog Output

NEMA 4 (IP65)
electronics
housing.

OS1592 Series
Starts at

\$2320



Fiber optic cable, included.

OS1592, \$2320,
shown smaller than
actual size.

Style L1 remote
optical head shown.
Transmitter price includes
sensor head with 1.5 m (5')
fiber optic cable.

- ✓ Fast 25 msec Time Constant (0 to 63% of Final Value)
- ✓ Well-Suited for Both Hard-to-Reach and Polymer Bolt Applications
- ✓ Accuracy: 1% of Reading
- ✓ Models with Temperature Ranges Measuring up to 2482°C (4500°F)
- ✓ Isolated Analog Output, mV, °C or °F, and Either Current, Voltage, Millivolt, or Thermocouple Output
- ✓ °C/°F Keypad Selectable
- ✓ Local Backlit LCD Display Standard
- ✓ Visual Alarm and Built-In Relay
- ✓ Dual Display Indicates Current Plus Min, Max, or Differential Temperatures
- ✓ Emissivity Adjustable from 0.05 to 1.00 in 0.01 Steps Via the Keypad
- ✓ Complete NEMA 4 (IP66) System
- ✓ Dual Analog Outputs Isolated from Power Supply Input

OMEGA's new CE marked low cost OS1590 Series infrared fiber optic thermometer/transmitter system measures temperature ranges up to 2482°C (4500°F) and provides dual analog outputs (4 to 20 mA, 0 to 5 Vdc, 0 to 10 Vdc, 1 mV/Deg, J, K T/C) electrically isolated from the DC power supply input. The main electronics is in a NEMA 4 rated aluminum housing with a local backlit LCD, built-in relay, alarm LED, and a 4-position programmable keypad.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Available Now!

iR2 SUPERMETER[®]
ULTRA HIGH PERFORMANCE
2-COLOR RATIO FIBER OPTIC
INFRARED TEMPERATURE
MEASUREMENT AND
CONTROL SYSTEM

- ✓ Temperature Range from 300 to 3000°C (572 to 5432°F)
- ✓ Ethernet and RS232/485 Options Available

\$2995
Complete!



Patented



Please see page J-125 for additional information.

Specifications

Temperature Range:

- R1: 260 to 538°C (500 to 1000°F)
- R2: 538 to 1093°C (1000 to 2000°F)
- R3: 1093 to 2482°C (2000 to 4500°F)

Accuracy: 1% of rdg

Repeatability: 0.75% of rdg

Response Time: 25 msec (0 to 63% of final value)

Emissivity: 0.05 to 1.00 adjustable, set via keypad

Spectral Response: 0.8 to 1.8 microns

Analog Output: 1 mV/deg, standard

Second Analog Output: 0 to 5 Vdc, 0 to 10 Vdc, 4 to 20 mA, or Type J or K thermocouple

Display: Backlit dual LCD

Keypad: 4 position, tactile feedback membrane switch

Calculated Temperature Values:

Maximum, minimum, differential

High Alarm: Set via keypad with built-in relay

Relay Contact Rating:

5 A @ 28 Vdc

Operating Ambient Temperature:

0 to 50°C (32 to 122°F)

Enclosure: Die-cast aluminum, NEMA 4

Dimensions

Main Housing:

5.6 H x 8.9 W x 11.4 cm L
(2.2 x 3.5 x 4.5")

Optical Assembly:

L1-Lens: 2.5 Dia. x 15.9 cm (1 x 6.25")


L2-Ceramic Tip: 0.47 Dia. x 15.2 cm (0.187 x 6")

L3-Polymer Bolt: 0.95 Dia. x 10 cm (0.375 x 4")


Power: 18 to 36 Vdc

Note: Contact factory if a replacement probe is needed. Probe is calibrated with your transmitter at time of purchase and is not field replaceable.

OS1590 Series backlit display and programmable key pad.



Available Probe Styles



Transmitter price includes 1 probe supplied with 1.5 m (5') fiber optic cable and sensor head.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)				
Model No.	Price	Temperature Range	Optical Assembly, Spot Size	Cable Length
OS1592-L1-R1-1-*	\$2320	260 to 538°C (500 to 1000°F)	Lens probe, 6.35 mm @ 203.2 mm (0.25" @ 8")	1.5 m (5')
OS1592-L2-R1-*	2360	260 to 538°C (500 to 1000°F)	Ceramic tip, 152.4 mm (6") Probe	1.5 m (5')
OS1592-L3-R1-*	2965	260 to 538°C (500 to 1000°F)	Polymer bolt, 101.6 mm (4") Probe	1.5 m (5')
OS1592-L1-R2-1-*	2320	538 to 1093°C (1000 to 2000°F)	Lens probe, 6.35 mm @ 203.2 mm (0.25" @ 8")	1.5 m (5')
OS1592-L1-R2-2-*	2320	538 to 1093°C (1000 to 2000°F)	Lens probe, 4.83 mm @ 508 mm (0.19" @ 20")	1.5 m (5')
OS1592-L1-R2-3-*	2320	538 to 1093°C (1000 to 2000°F)	Lens probe, 1.93 mm @ 152.4 mm (0.076" @ 6")	1.5 m (5')
OS1592-L2-R2-*	2320	538 to 1093°C (1000 to 2000°F)	Ceramic tip, 152.4 mm (6") Probe	1.5 m (5')
OS1592-L3-R2-*	2965	538 to 1093°C (1000 to 2000°F)	Polymer bolt, 101.6 mm (4") Probe	1.5 m (5')
OS1592-L1-R3-2-*	2320	1093 to 2482°C (2000 to 4500°F)	Lens probe, 4.83 mm @ 508 mm (0.19" @ 20")	1.5 m (5')
OS1592-L1-R3-3-*	2320	1093 to 2482°C (2000 to 4500°F)	Lens probe, 1.93 mm @ 152.4 mm (0.076" @ 6")	1.5 m (5')

Accessories	Price	Description
OS1500-BLS	\$495	Backlight source
OS1500-BLF	145	Backlight fiber assembly to use with OS1500-BLS
OS1500-RC	35	Replacement bulb for backlit source
PSR-24S	60	Regulated power supply, US plug, 90 to 264 Vac input, 24 Vdc output, 400 mA, screw terminals, UL
PSR-24L	60	Regulated power supply, US plug, 90 to 264 Vac input, 24 Vdc output, 400 mA, stripped leads, UL
PSR-24L-230	60	Regulated power supply, European plug, 230 Vac input, 24 Vdc output, 400 mA, stripped leads, CE
PSU-93	40	Unregulated power supply, 16 to 23 Vdc, 300 mA max, screw terminal
TX8-100	95	8-conductor shielded cable, 30.5 m (100')

(* Specify second analog output: -J = Thermocouple output, Type J (for R1 temp range only); -K = Thermocouple output, Type K (for R1 and R2 temp range only); -mA = 4 to 20 mA output; -V1 = 0 to 5 Vdc output; -V2 = 0 to 10 Vdc output. This unit provides two separate analog outputs. The first is 1 mV/deg.

Ordering Example: OS1592-L1-R1-1-MA, OS1592 transmitter with lens probe, 260 to 538°C (500 to 1000°F) temperature range, 1 mV/deg and 4 to 20 mA output, \$2320.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$350), \$2320 + 350 = \$2670.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters