

# MECHANICAL HYGROSTAT

**NEW**

MFR012  
\$78



- Adjustable Relative Humidity Range
- High Switching Capacity
- DIN Rail Mountable

The MFR012 is designed to control the relative air humidity inside of enclosures. When connected to an enclosure heater, (de-humidifier), it will turn the heater on at the set humidity level in order to raise the dew point. This helps prevent damage and malfunction of electronic components caused by condensation and corrosion. The MFR012 can also be used to control cooling fans, warning lights or other devices.

## SPECIFICATIONS

**Adjustment Range:** 35 to 95% ( $\pm 3.0\%$ ) relative humidity

**Switching Difference (Hysteresis):** Approx. 4% RH @ 50% relative humidity

**Permissible Air Velocity:** 50 ft/sec (15 m/s)

**Maximum Switching Voltage:** 250 Vac

**Attention:** 250 V should only be switched in a non-condensing environment

**Contact Type:** Change-over contact

**Contact Resistance:** <10 mOhm

**Service Life:** 100,000 cycles

**Minimum Switching Capacity:** 100 mA @ AC/DC 20 V

**Maximum Switching Capacity:**

5 A @ AC 230 V (resistive load)

1.0 A @ AC 230 V (inductive load at  $\cos \phi = 0.8$ ); DC 20 W

**EMI/EMC Compliance:** EN 55014-1-2, EN 61000-3-2, EN 61000-3-3

**Connection:** 3-pole terminal, 3 x AWG 14 max [2.5 mm<sup>2</sup> (0.1 in<sup>2</sup>)]

**Mounting:** Clip for 35 mm (1.4") DIN rail (EN 50022)

**Dimensions:** 67 H x 50 W x 38 mm D (2.64 x 1.97 x 1.5")

**Housing:** Clip for 35 mm DIN rail (EN 50022)

**Weight:** 60 g (2 oz)

**Operating Temperature:** 0 to 60°C (32 to 140°F)


**Storage Temperature:** -20 to 80°C (-4 to 176°F)

**Protection Type:** NEMA 2 (IP20)



MFR01201220000, \$78, shown larger than actual size.

Dimensions:  
mm (in)



## Application Examples:

- Electrical and Electronic Enclosures
- Telecommunication Systems
- Display Panels
- Ticket Dispensers
- Automatic Teller Machines (ATM's)
- Access and Parking Control Systems

**Note:** The critical relative humidity for most components is 65%. Above 65% RH, condensation can cause malfunction of electronic equipment. Long-term, this can lead to corrosion and permanent damage of electronic components and systems.

## To Order (Specify Model Number)

**AVAILABLE FOR FAST DELIVERY!**

MODEL NO.	PRICE	DESCRIPTION
MFR01201220000	\$78	Mechanical humidity control, SPDT, 35 to 100% RH, 20 Vdc to 230 Vac

Comes with complete operator's manual.

Ordering Example: MFR01201220000, mechanical hygrometer, \$78.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters