


EN-EIC-325

Four Axis Encoder Interface Card For The ISA Bus



EN-EIC-325 (ISA Bus), \$575, shown slightly larger than actual size

\$575
Basic Unit



- ✓ Four 24-Bit Up/Down Latch Counters
- ✓ Each Counter has a Programmable Setpoint Value
- ✓ Provides the Excitation to the Encoders

The Model EN-EIC-325 Four Axis Encoder Interface Card for the ISA BUS accommodates most of the popular optical encoders available. The board supports either square-wave or sinusoidal output encoders, both linear and rotary types. It can be directly connected to up to four encoders and will also provide necessary excitation to the encoders.

The card is equipped with four differential inputs for limit or home switches/marker/encoder index and 11 single-ended inputs for general use. Also, there are four opto-isolated outputs that may be used for set-points, carry/overflow or index/marker and three opto-isolated outputs for general use.

The card has four 24-bit up/down latch counters. Each counter can be programmed for a preset value. There is an internal status register for rapid storing and clearing of signals.

Specifications

Number of Encoders:

4 per board

Multiple Encoder Pulses:

1, 2 or 4 (software selectable)
Encoder Outputs: Sinusoidal or square-wave types

Counter Size: 24-bit up/down with latched buffer

Method of Communication with PC Bus: I/O port addressing, 16 jumper selectable address ranges

Encoder Inputs:

4 Wave Signal Inputs
(one per channel)

- single ended or differential for square wave
- differential for sinusoidal wave

4 Wave Index (Marker) Inputs
(one per channel)

- single ended or differential

11 general purpose inputs
TTL/CMOS compatible Schmidt trigger single-ended

Encoder Outputs:

- 4 event signal outputs
 - can be set to respond to following events - setpoint, overflow and index/marker
 - 1 opto-isolated output per channel

3 general purpose opto-isolated outputs

Power

(All supplied from ISA bus):

+5 V, 200 mA max; +12 V, 100 mA max; -12 V, 50 mA max

Encoder Connectors: Mini D-Sub 44 pin (mating connector supplied)

Output Connectors: D-Sub 9 pin

Operating Ambient: 0 to 50°C (32 to 122°F), up to 80% RH non-condensing

Dimensions:

153 L x 107 mm W
(6.0 x 4.2")

Weight: 150 g (5.3 oz)

ENCODER SIGNALS

SQUARE-WAVE SIGNAL

Signals: Square wave A phase and B phase shifted by 90°, single-ended or differential


Compatibility:

HTL 0.5-5V or TTL compatible

Rate: 500 Kpps max

SINUSOIDAL SIGNALS

Signals: Two incremental sinusoidal signals (phase A and B shifted by 90°) differential



EN-EIC-325 (ISA Bus), \$575, shown smaller larger than actual size

Signal Range (Encoder Output)

Impedance: <1 KΩ; current output encoders, >± 100 μA; voltage output encoders, >± 100 mV for phases A, B and for the reference marker/index pulse

Encoder Excitation: 5 Vdc

Light Source Current:

900 mA total max, protected by a polyswitch resettable fuse

Rate: 500 Kpps max

ENCODER COUNTER:

Counter: 24-bit up/down counter +24 bit latched buffer per counter

Setpoint: Independently programmable setpoint for each counter

Buffers: User may freeze the buffers without stopping the counters from counting

Operation: Independent operation mode for each axis

Encoder Pulses:

Single/multiple encoder pulses (1, 2 or 4 - software selectable)

Counter Reset: Counter may be reset when index is reached (software selectable)

Output/Interrupt Options for each Encoder

(Independently Selectable): Set-point reached, counter carry flag, index/marker

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
EN-EIC-325	\$575	Four axis encoder interface card for the ISA bus
EN-EIC-325-CONN	7	Extra mating connector for encoder input port

Each card is supplied with one mating connector for the 44 pin encoder input port. For an extra mating connector for the encoder input port, order part number EN-EIC-325-CONN, \$7. Each card also includes example software and source code illustrating how to communicate with the card under DOS as well as Windows drivers (EN-EIC-325 supports Windows 98) with complete Visual Basic examples.

Ordering Example: EN-EIC-325 four axis encoder interface card for the ISA bus and OMEGACARESM 1-year extended warranty for EN-EIC-325 (adds 1 year to standard 1-year warranty), \$575 + 57 = \$632.

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters