

Portable Low-Cost Temperature Relative Humidity Data Logger

Part of the NOMAD® Family

OM-62
\$109




- ✓ Measure Temperature, Relative Humidity and Dew Point Simultaneously
- ✓ Temperature and Humidity Alarm with Visual Indication on Demand
- ✓ User Selectable Stop on Memory Full or Memory Rollover for Continuous Recording
- ✓ PC or Push Button Recording Control
- ✓ USB Interface
- ✓ Compact, Light Weight, Easy-to-Use

The OM-62 temperature/relative humidity data logger is an easy-to-use, versatile device which can be used for a wide range of logging applications. The OM-62 is capable of sampling as fast as once per second or as slow as every 18 hours.

A total of 43,344 temperature measurements can be stored in the data logger memory if only temperature is measured, or 21,672 measurements for temperature and humidity.

In addition to measuring temperature and relative humidity, the easy-to-use Windows software included with the OM-62 data logger calculates and displays the dew point temperature. The software is a full-featured program that allows you to set up all data logger functions including sampling rate, logging duration, start mode, logging mode, and high and low temperature and relative humidity alarm values.

Once data has been logged, the program then allows you to download data from the logger, plot the data and export the data to an ASCII text or Excel file format for further analysis.



Windows software displays data in graphical or tabular format.



OM-62, \$109.

Specifications

Temperature Measurement Range:
-40 to 70°C (-40 to 158°F)

Temperature Sensor:
Internal digital sensor

Relative Humidity Range:
0 to 99% RH, non-condensing

Relative Humidity Sensor:
Polymer capacitive

Temperature Accuracy:
±0.5°C (±1°F)

Temperature Resolution:
±0.01°C (±0.01°F)

Relative Humidity Accuracy:
±2% RH from 10 to 90% RH

Relative Humidity Resolution:
0.01% RH

Temperature and Relative Humidity Alarms: Programmable high and low alarm thresholds, for both temperature and humidity

Sampling Rate: User selectable, 1 second to 18 hours, in 1 second increments

Data Storage: 43,344 for temperature only; 21,672 for temperature and humidity

Recording Mode: User selectable; stop on memory full or continuous recording with memory rollover

Recording Start: Push button, computer controlled, or up to 6 week delayed start

PC Interface: USB

Calibration: Single point offset calibration available through software for both temperature and humidity

Time Accuracy: ±100 ppm @ 75°F

Power: 3V lithium battery (included)

Battery Life: 6 years typical

Storage Temperature:
-40 to 70°C (-40 to 158°F)

Dimensions: 76 H x 40 W x 15 mm D (3.0 x 1.6 x 0.6")

Compatibility:
Windows 98/2000/XP/VISTA/WIN 7

Weight: 28 g (1 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-62	\$109	Temperature relative humidity data logger

Comes complete with Windows software on CD ROM, 3V lithium battery and USB interface cable.

Ordering Example: OM-62, temperature relative humidity data logger, \$109.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters