

OM-CP-OCTPROCESS 8-Channel Current Data Logger

Part of the NOMAD® Family


\$999
Basic Unit



- ✓ 16-Bit Resolution
- ✓ Programmable Engineering Units, Scale Factor, and Offset Value
- ✓ Memory Wraparound
- ✓ Miniature Size
- ✓ User Calibration Through Software
- ✓ Real-Time Operation

The OM-CP-QUADPROCESS is a 4 channel, battery powered, standalone current data logger. The OM-CP-OCTPROCESS lets the user store user defined units in the device, as well as scale factors and offset values. This allows easy linearization and scaling allows any process meter that provides an analog output to process units. This allows easy automatic linearization and scaling of any process meter that provides an analog output to process units. This portable, easy-to-use device will measure and record up to 16,383 current measurements per channel.

The OM-CP-OCTPROCESS represents a major leap in both size and performance. Its small size allows it to fit almost anywhere. Its real-time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security, even if the battery becomes discharged. Data retrieval is simple. Plug the logger into an available COM port and our easy-to-use software does the rest. The software converts your



OM-CP-OCTPROCESS-100MA, \$999, data logger shown larger than actual size.

PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format. It can also be exported to a text or Microsoft Excel file.

Specifications

Input Channels:

8 non-isolated inputs

Memory: 16,383 readings/channel

Input connection: Screw terminal

ADC Resolution: 16 bits

Analog Conversion Time: 133 ms

Frequency Rejection: 60 Hz

Current Calibration:

Digital calibration is available through software

Calibration Date: Automatically recorded within device to alert user when calibration is required

Recording Interval: 1 second to 12 hours selectable with software

Start Time: Start time and date are programmable through software

Real-Time Recording:

Device can be used with PC to monitor and record data in real time

Memory Wraparound:

Selectable in software

Power: 9 V lithium battery (included); 120 Vac power optional

Battery Life: 1 year typical

Time Accuracy: ±1 minute per month at 20°C

Data Format: Date and time stamped in µA, mA, A and other engineering units programmable through software

Weight: 480 g (17 oz)

Computer Interface:

PC serial, RS-232C COM or USB (interface cable required)

Software: XP SP3/Vista and 7 (32-bit and 64-bit)

Operating Environment:

40 to 60°C (-40 to 140°F)


0 to 95% RH non-condensing

Dimensions:

38 H x 111 W x 89 mm D

(1.5 x 4.4 x 3.5")

Material: Black anodized aluminum



OM-CP-IFC200, \$129,
Windows software displays
data in graphical or tabular
format.



OM-CP-OCTPROCESS-100MA,
\$999, data logger shown larger
than actual size.

INPUT RANGES	OM-CP-OCTPROCESS-1MA	OM-CP-OCTPROCESS-25MA	OM-CP-OCTPROCESS-100MA
Nominal Range	±1 mA	±25 mA	±100 mA
Measurement Range	±1.5 mA	±30 mA	±120 mA
Resolution	0.05 µA	1 µA	5 µA
Calibrated Accuracy	±0.5% FSR	±0.1% FSR	±0.1% FSR
Input Impedance	50 Ω	10 Ω	2 Ω
Overload Protection	±20 mA	±100 mA	±125 mA

Specified accuracy range: nominal range @25°C

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-OCTPROCESS-1MA	\$999	8-channel current data logger, ±1mA range
OM-CP-OCTPROCESS-1MA-CERT	1059	8-channel current data logger, ±1mA range with NIST calibration certificate
OM-CP-OCTPROCESS-25MA	999	8-channel current data logger, ±25 mA range
OM-CP-OCTPROCESS-25MA-CERT	1059	8-channel current data logger, ±25 mA range with NIST calibration certificate
OM-CP-OCTPROCESS-100MA	999	8-channel current data logger, ±100 mA range
OM-CP-OCTPROCESS-100MA-CERT	1059	8-channel current data logger, ±100 mA range with NIST calibration certificate
OM-CP-IFC200	129	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	25	Replacement 9 V lithium battery
OM-CP-CONNECTOR-3	6	Replacement 3 position terminal block connector

Operator's manual and USB cable are included with the **OM-CP-IFC200** Windows software (software is required to operate the data logger and is sold separately). To order data loggers with optional 120 Vac power, add suffix "-AC" to model number and add \$100 to price.
Ordering Example: OM-CP-OCTPROCESS-25MA-CERT 8-channel current data logger with NIST calibration certificate, OM-CP-IFC200 Windows software and USB interface cable, \$1059 + 129 = \$1188.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters