

High Speed Temperature and Process Signal Measurement System



OMB-TEMPSCAN-1100, \$1499, shown smaller than actual size

\$1998
Basic Unit with
OMB-TEMPTC-32B Input
Module and Software

- ✓ Measure Thermocouples at Rates up to 960 Channels per Second
- ✓ Software Support includes:
 - Chartview datalogging application for effortless setup, acquisition, & real-time display
 - PostView, for post-acquisition viewing of large data files
 - Calibration software
- ✓ Accepts Optional Scanning Modules for Measuring Thermocouples or RTDs
- ✓ Expandable to 992 Channels
- ✓ Requires No External Signal Conditioning
- ✓ Built-In IEEE-488 and RS-232/422 Interfaces

- ✓ 32 TTL Digital Alarm Outputs and 8 TTL-Compatible Digital Inputs
- ✓ Programmable Pre-Trigger and Post-Trigger Scan Intervals
- ✓ Memory Expansion to 8 MB
- ✓ Time and Date Stamping for Monitoring Temperature Trends

The OMB-TEMPSCAN-1100 sets a new standard for speed, expansion and economy in data acquisition systems.

The OMB-TEMPSCAN-1100 accepts any one of two scanning modules, for either thermocouple or RTD measurement. The thermocouple module accepts 32 inputs, while the RTD module accepts 16 3-wire or 4-wire RTD sensors.

With optional expansion chassis the OMB-TEMPSCAN-1100 can accept up to 992 inputs. The OMB-EXP-10A two-slot chassis can accept one or two scanning modules. Multiple OMB-EXP-10A units may be daisy chained for expansions to the full input capacity. For systems with more than 96 inputs, the OMB-EXP-11A, 10-slot chassis provides more economical, convenient expansion.

Each OMB-EXP-11A provides up to 320 input channels in a compact and convenient enclosure.

Multiple OMB-EXP-11A chassis can be connected to one OMB-TEMPSCAN-1100 to provide a total system capacity of up to 992 channels.

The OMB-TEMPSCAN-1100's multi-processor architecture provides linearized and compensated thermocouple-based temperature readings at speeds up to 960 channels per second, valuable in monitoring a large number of channels. The OMB-TEMPSCAN-1100 fast reading rate enables the unit to measure a sensor and activate an alarm much faster than alternative solutions. Also, a 16-bit A/D converter ensures measurement integrity. The A/D converter samples and averages multiple readings, resulting in high noise rejection from ac line pickup.

The OMB-TEMPSCAN-1100 is designed to facilitate datalogging at fixed-time intervals. The unit can be configured to begin and end logging on a user-specified event, such as a TTL input, temperature level, IEEE GET command, as well as time of day, or upon completion of a specified number of readings. An internal 256 k data buffer can be upgraded to 8 megabytes, ideal for

Model OMB-TEMPSCAN-1100



OMB-EXP-11A
Optional Expansion Chassis,
\$1999

both high-speed and long-term datalogging. Many process control applications require occasional temperature monitoring until a limit condition occurs. Once an alarm is detected, the system often needs to accelerate temperature measurement and simultaneously provide closed-loop control signals until the process returns to steady-state conditions.

The OMB-TEMPSCAN-1100 provides 32 digital alarm outputs that actuate on user-specified alarm conditions, on a per channel basis. Once the limit condition is resolved, the alarm outputs return to steady-state. OMB-TEMPSCAN-1100 can update alarmed output channels in real-time, at the max 960 channels per second rate. It can also be configured to alert the host computer of active alarm conditions via an IEEE-488 SRQ.

The OMB-TEMPSCAN-1100 also provides separate pre-trigger and post-trigger scan intervals for quick reaction during alarm conditions. For example, the unit can be programmed to sample channels once per minute, and when a specified channel reaches a limit condition, to sample data once per second.

The OMB-TEMPSCAN-1100 scans groups of 16 consecutive channels during every ac line cycle

(i.e., channels 1-16 scanned during the first line cycle, 17-32 during the second line cycle, etc.). This results in max measurement rates of 960 channels per second (at 60 Hz, 800 channels per second at 50 Hz).

The OMB-TEMPSCAN-1100 IEEE-488 interface is well suited to laboratory applications that require real-time data transmission to the host for mass storage. Data transfer rates up to 300 kb per second are supported. The RS-232/422 interface supports baud rates from 300 to 9600, and can be used for process and environmental control.

The RS-232/422 interface suits it for applications that require the placement of instrumentation at remote distances from the controlling computer, such as process and environmental control. The unit provides switch selectable baud rates from 300 to 9600. Both its IEEE 488 and RS-232/422 interfaces support data retrieval in ASCII and, for high speed applications, in binary format.

The OMB-TEMPSCAN-1100 is designed with convenience in mind. It requires no external signal

conditioning, multiplexers, or custom cables saving the user both time and money. User-installable scanning modules provide all signal conditioning and amplification.

The scanning modules contain screw terminal sockets for quick and easy input connections. The modules slide into a metal, hielded enclosure within the OMB-TEMPSCAN-1100, keeping noise outside and maintaining a constant internal temperature.

The OMB-TEMPSCAN-1100 and its expansion chassis accept two versions of scanning modules, allowing users to create systems of up to 992 channels. These scanning modules include:

Remote/Modem Operation

The OMB-TEMPSCAN-1100 is ideal for applications that require the placement of instrumentation at some distance from the controlling computer.

The RS422 interface enables the OMB-TEMPSCAN-1100 to be located up to 1 Km from the computer.

For greater distances, Chartview is capable of controlling the OMB-TEMPSCAN-1100 via a Hayes compatible modem. To establish a modem link, a modem is required in the computer and an auto answer modem must be connected to the OMB-TEMPSCAN-1100.

Thermocouple Scanning Module:

OMB-TEMPTC-32B thermocouple scanning module contains 32 differential input channels, each of which may be configured for any thermocouple type or a millivolt input with ± 100 mV range. Measurements may be returned in units of $^{\circ}\text{C}$, $^{\circ}\text{F}$, K, R, or mV.

RTD Scanning Module:

The OMB-TEMPRTD-16B scanning module supports 16 channels of 3- or 4-wire RTDs. Measurements may be returned in units of $^{\circ}\text{C}$, $^{\circ}\text{F}$, K, or R.

Specifications

OMB-TEMPSCAN-1100

Number of Channels: Up to 32 differential thermocouple inputs, or up to 16 RTD inputs; accepts OMB-TEMPTC-32B or OMB-TEMPRTD-16B scanning modules

Scan Interval: Absolute time between channel scans (hh:mm:ss.s); min = 00:00:00.0; max = 99:59:59.9

Maximum Measurement Rate: 960 channels/sec (60 Hz)

Per Channel Scan Rate: The rate at which individual channel values are updated depends on the total number of channels scanned and the AC line frequency (50/60 Hz).

No. of Channels	Per Channel Scan Rate (Hz)	
	60 Hz	50 Hz
1-16	60	50
17-32	30	25
33-48	20	16.7
49-64	15	12.5
65-80	12	10
81-96	10	8.3
97-112	8.6	7.1
113-128	7.5	6.25
↓		
785-800	1.2	1.0
↓		
945-960	1.0	.83
961-976	.98	.82
977-992	.97	.81



OMB-TEMPSCAN-1100, \$1499, shown smaller than actual size

Programmable Triggering: Level (temperature or voltage), absolute time of day, alarm condition, IEEE GET, IEEE TALK, external TTL trigger

Level Trigger: Programmable value for any one channel

TTL Trigger: Programmable for rising or falling edges

Pre-Trigger Count: Programmable (< memory size - 1)

Post-Trigger Count: Programmable

Alarms & Digital I/O

Number of Digital Alarm Outputs: 32 bits, TTL-level compatible, will drive 5 TTL loads.

Number of Digital Inputs: 8 bits, TTL-level compatible

Connector: 50 pin D-connector; mating connector supplied

Data Storage and Format: 128K reading (256 Kbyte) standard; optional 500K reading (1 Mbyte), 2M reading (4 Mbyte), and 4M reading (8 Mbyte)

Data Formats: ASCII and binary; binary format returns a 16-bit compensated and linearized temperature value ($0.1^{\circ}\text{C}/\text{bit}$); user programmable for hi/lo byte or lo/hi byte

IEEE 488 Interface

Maximum Data Transfer Speed: 300 Kbytes/s

Connector: Standard IEEE 488 connector with metric studs

RS-232/422 Interface

Baud Rates: 300, 1200, 2400, 4800, and 9600

Data Bits: 8

Stop Bits: 1

Parity: Even, odd, none

Handshaking: RTS/CTS, XON/OFF

Connector: Male DB-9

General

Power: 105-125 or 210 to 250 Vac, 50/60 Hz; 20 VA max

Environment: 32 to 122°F (0 to 50°C); 0 to 95% RH (non-condensing) to 35°C ; linearly derate 3% RH/ $^{\circ}\text{C}$ from 35°C to 50°C

Dimensions:

1.75" H x 16.75" W x 12" D (45 x 425 x 305 mm)

Weight: 8 lb (3.62 kg)

OMB-EXP-10A

Expansion Chassis

Number of Channels: Up to 64 differential thermocouple inputs, or up to 32 RTD inputs; accepts any combination of two OMB-TEMPTC-32B or OMB-TEMPRTD-16B scanning modules

Power: 105-125 or 210 to 250 Vac, 50/60 Hz; 20 VA max

Dimensions:

1.75" H x 16.75" W x 12" D (45 x 425 x 305 mm)

Weight: 2.53 kg (5.5 lbs)

OMB-EXP-11A

Number of Slots: 10

Number of Channels: Up to 320 differential thermocouple inputs, or up to 160 RTD inputs; accepts any combination of 10 OMB-TEMPTC-32B or OMB-TEMPRTD-16B

Front Panel Indicators: LEDs for scanning, error, & power

Power: 105 to 125 or 210 to 250 Vac, 50/60 Hz; 20 VA max

Environment: 0 to 50°C; 0-95% RH non-condensing to 35°C; linearly derate 3% RH/°C from 35° to 50°C

Dimensions: 16.75" W x 12" D x 5.75" H (425 x 305 x 135 mm)

Weight: 14 lbs (6.36Kg)

**OMB-TEMPTC-32B
Thermocouple Scanning Module**

Number of Channels: 32 differential; programmable by channel for specific thermocouple type or a millivolt input

Input Types: J, K, T, E, R, S, B, N14 & N28, custom thermocouple, and millivolts

Input Connectors: Screw terminal

Thermocouple Wire: #16 AWG max, #24 AWG min, #20 AWG recommended for J, K, T., E & N #24 AWG recommended for R, S, & B

TEMPERATURE RANGES AND ACCURACY:

Type	Range	Accuracy*	Resolution**
J	-200 to 760°C	±0.5°C	±0.1°C
K	-100 to 1372°C	±0.5°C	±0.1°C
T	-100 to 400°C	±0.5°C	±0.1°C
E	-100 to 1000°C	±0.5°C	±0.1°C
N	-200 to 1300°C	±0.5°C	±0.1°C
R	0 to 1768°C	±1.0°C	±0.1°C
S	0 to 1768°C	±1.0°C	±0.1°C
B	35 to 1820°C	±1.0°C	±0.1°C
N14	0 to 1300°C	±0.5°C	±0.1°C
N28	-270 to 400°C	±0.5°C	±0.1°C

*18 to 28°C **Typical

Temperature Units: °C, °F, °K, °R

Input Impedance: 1M ohm typical

Maximum Allowable Input: ±35V peak

Channel to Digital Low Isolation: 500 V max

Channel to Channel Isolation: ±10 V peak

Digital Filtering: Averages 16 samples at 50/60Hz for line cycle noise rejection

Voltage Range/ Resolution: ±100 mV/ 3.05µV

Voltage Accuracy: ±0.02%

**OMB-TEMPRTD-16B
RTD Scanning Module**

Number of Inputs: 16 (3 or 4-wire)


Input Connectors: Screw terminal

TEMPERATURE RANGE AND ACCURACY:

Type	Range	Accuracy	Resolution
100 Ω Pt	-100 to 630°C	±0.2°C	0.1°C
α=0.00385	-270 to -100°C	±0.4°C	0.2°C

Excitation Current: <1 mA peak

OMB-TEMPSCAN-1100 data logging software provides effortless real-time scrolling and data capture to disk



**Software
CHARTVIEW SOFTWARE**

The OMB-TEMPSCAN-1100 includes ChartView, Windows-based setup and acquisition application. ChartView provides a graphical spreadsheet style user interface that lets you easily configure your hardware, acquisition, and display parameters. ChartView features a no programming approach that enables data collection and display within minutes.

ChartView provides a number of data display options including a real-time smooth scrolling trend display, digital meters, analog meters, and bar graph meters. The collected data is stored to disk in an ASCII format so it may be easily imported into other applications, such as Microsoft Excel, for post acquisition display and analysis. In addition, ChartView also provides a real-time link to Excel using Dynamic Data Exchange (DDE). The OMB-TEMPSCAN-1100 also includes PostView, a post acquisition graphics display program that integrates seamlessly into ChartView. Using PostView's intuitive on-screen controls, you can expand, contract and auto-scale waveforms as well as scroll in either direction. PostView also provides the table below summarizes the right summarizes the features of the ChartView software.


ChartView Software Feature Overview	
Feature	
Display Groups	64
Display Charts	16
Channels per Chart	up to 4
Overlapped Channels	✓
Auto-Rearm	✓
Alarm Logging	✓
Chart Setup Wizard	✓
Individual Channel Positioning	✓
Remote Operation	✓
Separate Pre- & Post-Scan Number	✓
Separate Pre- & Post-Scan Rate	✓
Alarm Channels	32
mX+b Scaling	✓
mX+b Scaling with Reference Channel	✓
Digital Inputs	✓
Digital/Analog Bar Graph Meters	✓
Engineering Units	✓
Label Channels	✓
Links to Excel	✓
PostView Included	✓
Scale Data to User Units	✓
Stand-Alone Operation	✓
Uniform and Scaled Grids	✓



Rear view of OMB-TEMPSCAN-1100, \$1499 and OMB-EXP-10A, \$799

Rear Panel Connections OMB-TEMPSCAN-1100

- 1 **IEEE-488 Connector:** Provides full IEEE-488 control from PCs, Macintosh computers, and SUN, HP and DEC workstations.
 - 2 **RS-232C/RS-422 Connector:** Serial port for operation at remote distances from computer. Supports 300 to 9600 baud using RTS/CTS or XON/XOFF handshaking.
 - 3 **DIP Switches:** select IEEE or RS-232/422 communications and respective parameters (IEEE address; RS-232 baud rate, parity and handshaking).
 - 4 **Trigger Input (BNC) Connector:** initiate and/or stop acquisition with TTL input signal.
 - 5 **TTL Output (BNC) Connector:** signal for each channel scan; used for synchronizing other equipment.
 - 6 **Alarm, Digital I/O Connector:** provides access to 32 TTL digital alarm outputs and 8 digital input lines.
 - 7 **Master/Slave Connector:** attach OMB-EXP-10A expansion chassis.
 - 8 **Shielded Enclosure:** scanning modules designed for constant temperature and reduce electrical noise interference.
 - 9 **Power:** 105 to 125 or 210 to 250 Vac, internally configurable.
 - 10 **Power Switch**
 - 11 **Master/Slave Expansion Cable**
- OMB-EXP-10A EXPANSION CHASSIS**
- 12 **DIP Switches:** select ID number for each OMB-EXP-10A expansion chassis.
 - 13 **Master/Slave Connector:** attach multiple OMB-EXP-10A modules to the OMB TEMPSCAN-1100A.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OMB-TEMPSCAN-1100	\$1499	High speed temperature measurement chassis; accepts one scanning module (module sold separately)
OMB-EXP-10A	799	Expansion chassis; includes OMB-TEMPSCAN-1100 to OMB-EXP-10A cable; accepts two scanning modules (modules sold separately)
OMB-EXP-11A	1999	Expansion chassis; includes OMB-TEMPSCAN-1100 to OMB-EXP-11A cable; accepts 10 scanning modules (modules sold separately)
OMB-TEMPTC-32B	499	32-channel thermocouple input scanning module
OMB-TEMPRTD-16B	499	16-channel RTD input scanning module
OMB-CA-47	51	6' cable, connects OMB-TEMPSCAN-1100 to 9 or 25 pin serial port

OMB-TEMPSCAN-1100 includes Chartview software, DB-50 digital I/O port mating connector, operator's manual and rack mount kit. OMB-EXP-10A and OMB-EXP-11A includes rack mount kit and master/slave interface cable.

Ordering Example: OMB-TEMPSCAN-1100 chassis, OMB-EXP-10A expansion chassis, OMB-TEMPTC-32B thermocouple input module, OMB-TEMPRTD-16B input module and OMB-CA-47 cable, \$1499 + 799 + 499 + 499 + 51 = \$3347.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters