

OEM-STYLE ACRYLIC ROTAMETERS

CAPACITIES: Water: 6.5 GPH to 20 GPM

Air: 2 SCFH to 40 SCFM

FL4000 Series
Starts at

\$56



Optional††

- ✓ 50, 75, 127, and 250 mm (1.97, 2.96, 5, and 9.85") Scale Lengths
- ✓ Floats are Rod-Guided in Most Models
- ✓ Metering Valves Available
- ✓ Rear Inserts Provided for Panel Mounting
- ✓ Direct-Reading Scales

FL4000 OEM-style rotameters are precisely machined from solid acrylic blocks. They are available in 50, 75, 127, and 250 mm (1.97, 2.96, 5, and 9.85") scale lengths and have accuracies between 2 and 6%. Designed for front-panel mounting, the rear ports extend through the panel for easy hookup. Mounting threads are also provided. Units are available with and without valves.

SPECIFICATIONS

Construction: Acrylic tube, 316 SS float and guide rod (no guide rod for FL4211 through FL4215 air meters), PVC end fittings (brass on FL4200 Series), EPR O-rings, optional brass valve

Max Pressure/Temperature:

Water Ranges:

125 psig @ 21°C (70°F);
54°C (130°F) at 0 psig

Air ranges:

100 psig @ 21°C (70°F);
38°C (100°F) @ 0 psig


Full Scale Accuracy/Repeatability:

FL4200: 6/2%

FL4300 and FL4400: 4/1%

FL4500: 3 1/2%

FL4600: 2 1/2%




FL4304, \$71,
shown actual size.



FL4212-V, with
optional valve, \$71,
shown actual size.

FL4503-V, \$107,
shown actual size.


Dimensional Drawing



(FULL OPEN)



(FULL OPEN)



REAR VIEW

Connection: FL4200: ¼ FNPT; FL4300 and FL-4500: ½ FNPT x ½ MNPT; FL4400: 1 MNPT; FL4600: ½ FNPT



Many fittings of various materials and styles are available. See pages T-36 to T-80 or visit omega.com

Dimensions: mm (in)

Dimensions	FL4200	FL4300	FL4400	FL4500	FL4600
A	102 (4.0)	168 (6.6)	225 (8.9)	210 (8¼)	362 (14¼)
B	25 (1.0)	32 (1.3)	44 (1.8)	32 (1¼)	44 (1¾)
C	32 (1.3)	35 (1.4)	46 (1.9)	35 (1⅝)	46 (1⅜)
D	105 (4.1)	173 (6.8)	232 (9.9)	213 (8⅝)	368 (14½)
E	13 (0.5)	25 (1.0)	32 (1.3)	25 (1)	19 (¾)
F	29 (1.1)	32 (1.3)	48 (1.9)	32 (1¼)	48 (1⅞)
G	76 (3.0)	127 (5.0)	165 (6.5)	164 (6⅞)	311 (12¼)
H	—	76 (3.0)	102 (4.0)	100 (3⅝)	222 (8¾)
L	17 (0.7)	25 (1.0)	35 (1.4)	25 (1)	32 (1¼)
J Mounting Thread Size*	†	¼ x 20	¼ x 20	¼ x 20	⅝ x 24

* Threaded stud.

† FL4200 has ⅝" hex lock nuts around ports; requires ¾" holes to be drilled through the panel.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Water					Air		
Model No.	Price	Range (Max)*	Pressure Drop, inH ₂ O**		Model No.	Price	Range (Max)*
			No Valve	Valve			
FL4201	\$56	7 GPH	1**	1.3**	FL4211	\$56	2.6 SCFH
FL4202	56	12 GPH	15**	17**	FL4212	56	5.0 SCFH
FL4203	56	22 GPH	35**	51**	FL4213	56	10.0 SCFH
FL4204	56	44 GPH	149**	200**	FL4214	56	20.0 SCFH
FL4205	56	60 GPH	100**	250**	FL4215	56	30.0 SCFH
FL4301	71	1 GPM	18**	26**	FL4216	56	60.0 SCFH
FL4302	71	2.0 GPM	70**	125**	FL4217	56	100.0 SCFH
FL4303	71	3.5 GPM	200**	290**	FL4218	56	180.0 SCFH
FL4304	71	5 GPM	290**	440**	FL4219	56	4.0 SCFM
FL4401	110	10 GPM	53	220	FL4411	110	40.0 SCFM
FL4402	110	15 GPM	132	330	FL4412	110	62.0 SCFM
FL4403	110	20 GPM	200	400	—	—	—
FL4501	87	1 GPM	18	33	FL4511	87	4.0 SCFM
FL4502	87	100 GPH	45	75	FL4512	87	6.8 SCFM
FL4503	87	2 GPM	70	155	FL4513	87	8.0 SCFM
FL4504	87	5 GPM	240	400	FL4514	87	20.0 SCFM
FL4601	162	2 GPM	5	21	FL4611	162	8.5 SCFM
FL4602	162	3.5 GPM	13	50	FL4612	162	14.5 SCFM
FL4603	162	5 GPM	20	95	FL4613	162	20.0 SCFM
FL4604	162	10 GPM	110	270	FL4614	162	40.0 SCFM

Comes with complete operator's manual.

* Minimum flow rate = 10% of maximum flow rate listed.

** For water ranges. For air ranges, contact the Flow Department. For units with brass valve, add suffix "-V" to model number and \$15 for FL4200s; \$16 for FL4300s; \$60 for FL4400s; \$20 for FL4500s; and \$32 for FL4600s.

†† For NIST calibration certificate, and "-NIST 5PT" to the model number for 5-point calibration, and \$250, or "-NIST 10PT" for 10-point calibration, and \$350.

Ordering Examples: FL4303-V, acrylic rotameter, 3.5 GPM flow rate, \$87.

FL-4613, acrylic rotameter, 40 SCFM max flow, \$162.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters