

LOW-FLOW MAGNETIC FLOWMETER

FMG201 Series
Starts at
\$1078



- ✓ Variety of Outputs
- ✓ Continuous Flow Signal
- ✓ Relay Alarm Outputs
- ✓ Rate and Total

The FMG201 Series comprises small, plastic-bodied electromagnetic flowmeters capable of measuring the pulsating flows from air and solenoid-driven metering pumps. They are designed for use with electrically conductive chemicals and fluids of varying viscosities. In addition to measuring and displaying flow rate and total flow, they have a variety of outputs. For continuous transmission of a flow signal, available outputs are 4 to 20 mA, 0 to 5V, and a frequency signal proportional to flow. Relay alarm outputs are for low and high flows with user-set flow levels.

Important Note: For proper operation, one or both of the ground lugs must be well connected with 10-24 UNC screws to a good earth ground.

SPECIFICATIONS

Accuracy:

±1% of Reading, +0.005 GPM (0.02 LPM): Above 10% FS

±3% of Reading, +0.005 GPM (0.02 LPM): Below 10% FS

Maximum Fluid Temperature: 85°C (185°F)



Each Unit Includes Sensing Element and Control Housing

Maximum Pressure: 10.3 bar (150 psi) @ 24°C (75°F)

Wetted Materials:

Body: PVDF

Electrodes: Platinum-coated titanium

Internal Seals: FKM

Housings (Primary Element): Fusion-coated aluminum

FMG200-DC: PVDF

Control/Display: Polycarbonate

Connection: 3/8" or 1/2" MNPT

Mounting Holes: 4 holes, 0.218" Dia.

DIMENSIONS

Housing: 125 H x 125 W x 74 mm D (4.93 x 4.93 x 2.92")

Flow Sensor: 112 H x 95 W x 89 mm D (4.4 x 3.75 x 3.5")

WARNING:
METER MAY BE DESTROYED BY TIGHTENING FITTINGS WITH A WRENCH. USE A WRENCH ONLY TO KEEP THE FITTINGS FROM ROTATING WHILE TIGHTENING THE MATING FITTINGS. (REF: INTERNAL SEAL IS MADE WITH AN O-RING)

FMG203-NPT, \$1518, shown smaller than actual size.

Cables (Controller to Sensor):

1.8 m (6') standard, 6 m (20') optional

Power: 115 Vac, 60 Hz

Display: Backlit LCD (2 lines of 16 characters)

Fuse (Included): 0.25 A, 5 x 20 mm

Minimum Conductivity: 20 µS

Outputs: 4 to 20 mA (24 Vdc required), 0 to 5V (both isolated); frequency to 9999 pulses per gallon; isolated 10 mH, 30 Vdc; high alarm, low alarm relay (6.25% hysteresis), isolated (100 mA, 110 Vac/Vdc)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	MNPT	Through Hole	Nominal Full Scale		Min for 1% Accuracy		Low-Flow Cutoff		Display
				LPM	GPM	LPM	GPM	LPM	GPM	
FMG201-NPT	\$1518	3/8"	1/4"	3.8	1	0.38	0.1	0.04	0.01	Yes
FMG210-NPT	1078	3/8"	1/4"	3.8	1	0.38	0.1	0.04	0.01	No
FMG202-NPT	1518	3/8"	3/8"	11	3	1.14	0.3	0.08	0.02	Yes
FMG220-NPT	1078	3/8"	3/8"	11	3	1.14	0.3	0.08	0.02	No
FMG203-NPT	1518	1/2"	1/2"	38	10	3.8	1	0.15	0.04	Yes
FMG230-NPT	1078	1/2"	1/2"	38	10	3.8	1	0.15	0.04	No

Comes complete with operator's manual, bracket and power cord.

For barb fittings, replace "-NPT" with "-BRB", no additional charge.

For units with 6 m (20') sensor cable, add "-20FT" to the model number and \$75 to price.

Ordering Examples: FMG201-NPT, 0.01 to 1 GPM magmeter with display, \$1518.

FMG220-NPT, 0.02 to 3 GPM magmeter without display, \$1078.

Recommended Reference Book: Magnetic Flowmeter Guide, FW-202, \$250. Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters