



ANEMOMETER WITH REAL TIME DATA LOGGER

HHF2005
Starts at

\$539



HHF2005, \$539,
shown smaller
actual size.



- ✓ Real Time Data Logger Records Year, Month, Date, Hour, Minute and Second—Up to 16,000 Records
- ✓ Heavy Duty Metal Van Gives Very Accurate Low and High Velocity Air Measurements
- ✓ Battery Powered Meter Includes Hard Carrying Case For Easy Portability
- ✓ Jumbo LCD With Multiple Displays Can be Adjusted For Brightness
- ✓ Adjustable Sampling Time and Data Hold Features
- ✓ Accepts Type J or K Thermocouple

The HHF2005 anemometer with real time data logger has multiple features and an RS232 computer interface that make it suitable to use in a variety of HVAC applications, such as environmental testing, flow hoods and wind speed measurements. What sets the HHF2005 apart from other anemometers is that it incorporates

a real-time data logger that can store up to 16,000 entries. The HHF2005 measures velocity and air temperature, and has an input probe socket that accepts a Type J or K thermocouple that can be used as a highly accurate thermometer. By entering the area into the instrument and measuring the velocity, the HHF2005 can even

determine the volume of air flow. The integrated thermistor provides fast and accurate readings—at low or high velocities. For added convenience, the HHF2005 is battery powered, has auto power off and low battery warning features. A hard carrying case is included to make portability simple.



Hard carrying case, operators manual, and 4 "AA" batteries included.

C

SPECIFICATIONS

Display Units: m/s, km/h, mile/h, knot, ft/min, CMM, CFM, °C, °F

Operating Temperature: 0 to 50°C (32 to 122°F)

Max Humidity: Less than 80% relative humidity (non-condensing)

Sampling Time: 2 sec to 8 hours, 59 min, 59 sec

Power Supply: 4 "AA" batteries (included)

Current: Approx 21.5 mA dc (27.5 mA dc with vane)

Weight: Approx 515 g (1.13 lb)

Dimensions:

Instrument: 203 x 76 x 38 mm (8.0 x 3.0 x 1.5")

Metal Vane: 72 mm (2.8") dia

LCD Display: 58 x 34 mm (2.3 x 1.3")

Measurement	Range	Resolution	Accuracy
m/s	0.4 to 30.0 m/s	0.1 m/s	±10% +1 lsd
km/hr	1.4 to 108.0 km/hr	0.1 km/hr	
mile/hr	0.9 to 67.0 mile/hr	0.1 mile/hr	
knot	0.8 to 58.3 knot	0.1 knots	
ft/min	80 to 5910 ft/min	1 ft/min	
Air temp (°C)	0 to 50°C	0.1°C	± 0.8°C
Air temp (°F)	32 to 122°F	0.1°F	± 1.5°F
Thermometer (Type J thermocouple)	-100.0 to 1100°C	0.1°C	± (0.2% + 0.5°C)
	-50.1 to -100°C		± (0.2% + 1°C)
	-58.0 to 2012°F	0.1°F	± (0.2% + 1°F)
-58.1 to -148°F	± (0.2% + 1.8°F)		
Thermometer (Type K thermocouple)	-50.0 to 1300°C	0.1°C	± (0.2% + 0.5°C)
	-50.1 to -100°C		± (0.2% + 1°C)
	-58.0 to 2372°F	0.1°F	± (0.2% + 1°F)
-58.1 to -148°F	± (0.2% + 1.8°F)		

Measurement	Range	Resolution	Area
CMM	0 to 54,000 CMM	0.001-1 CMM	0.001 to 30.0 m²
CFM	0 to 1,908,300 CFM	0.01-100 CFM	0.01 to 322.91 ft²

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HHF2005	\$539	Vane anemometer with data logger
HHF2005-RP	200	Replacement vane for HHF2005
SWCABLE	115	Data logging software for the HHF2005 series with cables
MN1500-4	3	4 "AA" replacement batteries

Comes complete with operator's manual, 4 "AA" batteries and hard carrying case.

Ordering Example: HHF2005, vane anemometer with data logger, \$539.

Recommended Reference Book: Heating, Ventilating and Air Conditioning, MS-1001, \$180.
Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters