

AIR VELOCITY METERS

ANEMOMETER, HYGROMETER, LIGHT METER, THERMOMETER

HHF80 Series
Starts at
\$89



- ✓ Simultaneous Readings of Air Velocity and Temperature or Humidity and Temperature
- ✓ Exclusive Photo Diode and Color Correction Filter Light Sensor, Spectrum Meets C.I.E. Photopic
- ✓ Standard Type K Thermocouple SMP Input Jack Suitable for All Types of K Probes
- ✓ Lux/Feet-Candle Selectable by Pressing Button on the Front Panel

The HHF81 anemometer can measure air flow, humidity, temperature and light. The built-in microprocessor circuit assures excellent performance and accuracy. The HHF81 can track the maximum and minimum values along with current readings. The HHF81 and HHF82 display the flowrate in your choice of knots, meters per second, kilometers per hour, miles per hour, feet per minute.

The HHF81 and HHF82 rely upon a low-friction ball bearing mounted wheel design to provide high accuracy at high and low air velocity. The impeller provides excellent accuracy (± 3 to 4%) and the ability to measure the slightest breeze (0.3 m/s). For temperature readings, the HHF81 has an internal thermistor or is compatible with any Type K thermocouple with SMP Male connector, accurate to $\pm 1^\circ\text{C} + 1\%$ of reading. The humidity sensor measures to 95% relative using a high precision thin-film capacitance sensor with fast response to humidity changes. The Light measurement utilizes an exclusive photo diode and color correction filter light sensor.

SPECIFICATIONS (COMMON)

Air Velocity

Measurement Range: 80 to 5910 ft/min, 0.4 to 30.0 m/s, 0.9 to 67.0 mph, 1.4 to 108.0 km/hr, 0.8 to 58.3 knots, 0.8 to 58.3 knots

Resolution: 1 ft/min, 0.1 m/s, 0.1 mph, 0.1 km/hr, 0.1 knots

Accuracy: ≤ 20 m/s: 3% FS, >20 m/s: 4% FS

Operational Temperature: 0 to 50°C (32 to 122°F)

Operational Humidity Max: 80% RH

Overrange Display: "----"

Battery: 9V (included)

Power Consumption: Approx. dc 6.2 mA

Weight: 160 g (0.4 lbs) with battery

Dimension: 156 x 60 x 33 mm (6.14 x 2.36 x 1.29")

SPECIFICATIONS (HHF81)

Temperature (Internal Thermistor)


Measurement Range: 0 to 50°C (32 to 122°F)

Resolution: $0.1^\circ\text{C}/^\circ\text{F}$

Accuracy: $\pm 1.2^\circ\text{C}$ ($\pm 2.5^\circ\text{F}$)

Temperature (External Type K)

Measurement Range: -100 to 1300°C (-148 to 2372°F)



HHF82, \$89, shown smaller than actual size.

HHF81, \$159, shown smaller than actual size.

KTSS-HH, \$29, thermocouple sold separately.

Resolution: $0.1^\circ\text{F}/^\circ\text{C}$

Accuracy: $\pm(1\% + 1^\circ\text{C})$ of rdg [$\pm(1\% + 2^\circ\text{F})$ of rdg]

Humidity

Measurement Range: 10 to 95%

Resolution: 0.1%

Accuracy: $< 70\%$ RH: $\pm 4\%$ of rdg, $\geq 70\%$ RH $\pm (4\% \text{ rdg} + 1.2\% \text{ RH})$

Light Lux

Measurement Range: 0 to 2200 Lux, 1800 to 20000 Lux, 0 to 204.0 Fc, 170 to 2000 Fc

Resolution: 1 Lux, 10 Lux, 0.1 Ft-cd, 1 Ft-cd

Accuracy: $\pm 5\%$ rdg ± 8 dgt

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HHF82	\$89	Air flow meter
HHF81	159	Anemometer, hygrometer, light meter and thermometer
KHSS-18E-RSC-12	34	Type K thermocouple—exposed element for air
KTSS-HH	29	Type K handle probe—grounded element for air or liquids
SC-HH11A	15	Soft carrying case
SMPW-K-M	1.75	Type K SMP male connector with write on window
MN1604	3	Replacement 9V battery
CAL-3-FLOW†	235	NIST traceable 4-point calibration certificate

Comes complete with operators manual and 9V battery.

Ordering Examples: HHF81, 5-digit air flow meter, SC-HH11A, soft carrying case and MN1604, replacement 9V battery, $\$159 + 15 + 3 = \177 .

HHF82, air flow meter, \$89.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters