

OMEGA-FLO® 2-WAY, ANTI-WATER HAMMER SOLENOID VALVES

1/2 TO 2 NPT

SV-600 Series Starts at
\$147



- ✓ Slow Closing, Anti-Waterhammer Design
- ✓ Process Temperatures to 90°C (194°F)
- ✓ Works for Gases or Liquids
- ✓ 120 Vac Standard (DC Optional)

SV-600 Series 2-way solenoid valves are internally piloted, with epoxy-encapsulated coils. Their brass bodies and Viton® seal material allow for high flow rates. A temperature range of -10 to 90°C (14 to 194°F) makes these valves ideal for neutral media such as compressed air, natural gas, water, hydraulic oil, and oils and fats with no additives (max viscosity of approximately 4 x 10⁻⁴ ft²/s). Electrical connection is by cable plug.

Specifications

Mounting Position: Any (preferably with the solenoid system upright)

Max Ambient Temp: 54°C (130°F)

Voltage Tolerance: ±10%

Power Consumption (in Warm State):

AC: 21 VA (inrush); 12 VA/8 W (hold)
DC: 8 W

Opening Time: 200 to 500 ms

Closing Time: 100 to 4000 ms

Options (No Additional Charge)

Ordering Suffix	Description
-24VDC	24 Vdc operation
-12VDC	12 Vdc operation
-240VAC	240 Vac operation
-BUNA	Buna-N seal

Options not available on all models.

Cycling Rate:


Approx.

10 to 50 cpm

Times measured at outlet A on energizing/de-energizing until attainment of pressure rise to 90%/pressure drop to 10% at a working pressure of 85 psi.

Duty Cycle: Continuous (100%)

FM Approvals: Non-incendiary for hazardous locations Class I Div. 2 Group A, B, C, D; Class II Div. 2 Group F, G; Class III Div. 1 and 2; Operating Temperature T4A



SV-601, \$147, shown smaller than actual size.

■ MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Normally Closed Valve

Model No.	Price	Port Connection (NPT)	Cv	Pressure Range (psi) ¹		Orifice Dia.
				AC	DC	
SV-601	\$147	1/2	4.7	7 to 230	7 to 140	1/2"
SV-602	168	3/4	5.8	7 to 230	7 to 140	3/4"
SV-603	272	1	12	7 to 230	7 to 140	1"
SV-604*	340	1 1/4	23	7 to 230	7 to 140	1 1/4"
SV-605	507	1 1/2	23	7 to 230	7 to 140	1 1/2"
SV-606	896	2	47	7 to 230	7 to 140	2"

Normally Open Valve

SV-611	\$274	1/2	4.7	7 to 170		1/2"
SV-612	337	3/4	5.8	7 to 170		3/4"
SV-613	352	1	12	7 to 170		1"
SV-614	401	1 1/4	23	7 to 170		1 1/4"
SV-615*	591	1 1/2	23	7 to 170		1 1/2"
SV-616*	839	2	47	7 to 170		2"

¹ Operation with less than a 7 psi pressure differential will yield unpredictable flow characteristics.

* SV-604, SV-615 and SV-616 are not UL listed.

Comes with complete operator's manual.

Ordering Examples: SV-603, normally closed valve, 1 NPT, 12 Cv rating, \$272.

SV-601, normally closed valve, 1 NPT, \$147.

Accessory

Model No.	Price	Description
FW-346	\$86	Reference Book: Control Valve Primer





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters