

OMEGAFLEX® NYLON 11 TUBING

TYNY Series
Starts at

\$12

100' Spool




By P/N†

Color Tubing

Order Suffix	Color
-BL	Blue
-BLK	Black
-GN	Green
-GY	Gray
-OR	Orange
-R	Red
-Y	Yellow

No additional charge. Standard color is neutral translucent white, no order suffix required.



This formulation for flexible premium tubing is the standard for both general industrial and automotive applications. Its broad temperature range -51 to 93°C (-60 to 200°F) continuously combines with light weight, dimensional stability, chemical resistance and flexibility.

SPECIFICATIONS

Hardness, Shore D: 64

Specific Gravity: 1.03

Tensile Strength PSI: Yield PSI (ASTMD-638): 3335

Elongation at Break: 570%

Min/Max Operating Temperature: -51 to 93°C (-60 to 200°F)

Color Tubing Availability

Note	Available Colors
1	-BL, -BLK, -GN, -GY, -OR, -R, -Y
2	-BLK, -R, -GN
3	-BL, -BLK
4	-BLK
5	-GN
6	Natural translucent white only

Note: Standard Color Natural Translucent White, no suffix required.

† Visit omega.com/rohs to determine RoHS compliance.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

1/8 to 1/2" OD Tubing

Model No.	Price	OD Nom. (in)	ID Nom. (in)	Wall Thickness Nom. (in)	Min. Bend Radius (in)	OD Tol. (in)	ID Tol. (mm)	Working Pressure psi @ 75°F	lbs/100 ft	Standard Coil Length (ft)
TYNY-18080-100 ⁶	\$12	1/8	0.08	0.023	0.7	+0.002-.0045	±0.004	250	1/2	100
TYNY-18080-500 ¹	62	1/8	0.08	0.023	0.7	+0.002-.0045	±0.004	250	1/2	500
TYNY-532106-100 ¹	19	5/32	0.106	0.025	0.94	+0.002-.0045	±0.004	250	3/4	100
TYNY-532106-500 ¹	94	5/32	0.106	0.025	0.94	+0.002-.0045	±0.004	250	3/4	500
TYNY-316118-100 ¹	21	3/16	0.118	0.035	1.1	+0.002-.0055	±0.004	250	1	100
TYNY-316118-500 ¹	103	3/16	0.118	0.035	1.1	+0.002-.0055	±0.004	250	1	500
TYNY-14180-100 ¹	30	1/4	0.18	0.035	1.5	+0.002-.0055	±0.004	250	1 1/4	100
TYNY-14180-500 ¹	150	1/4	0.18	0.035	1.5	+0.002-.0055	±0.004	250	1 1/4	500
TYNY-14170-100 ¹	44	1/4	0.17	0.04	1.5	+0.002-.0055	±0.004	300	1 1/2	100
TYNY-14170-500 ¹	220	1/4	0.17	0.04	1.5	+0.002-.0055	±0.004	300	1 1/2	500
TYNY-14126-100 ⁴	55	1/4	0.126	0.062	1.5	+0.002-.0055	±0.004	500	2 1/2	100
TYNY-14126-500 ⁴	275	1/4	0.126	0.062	1.5	+0.002-.0055	±0.004	500	2 1/2	500
TYNY-516233-100 ¹	50	5/16	0.233	0.04	1.85	+0.002-.0055	±0.004	250	1 3/4	100
TYNY-516233-500 ¹	216	5/16	0.233	0.04	1.85	+0.002-.0055	±0.004	250	1 3/4	500
TYNY-38275-100 ¹	60	3/8	0.275	0.05	2.25	+0.002-.0055	±0.004	250	2 3/4	100
TYNY-38275-500 ¹	299	3/8	0.275	0.05	2.25	+0.002-.0055	±0.004	250	2 3/4	500
TYNY-12375-100 ¹	109	1/2	0.375	0.062	3	+0.002-.0055	±0.004	250	4 3/4	100
TYNY-12375-500 ¹	545	1/2	0.375	0.062	3	+0.002-.0055	±0.004	250	4 3/4	500

Note: Specified minimum bend radius is for minimal tube flattening.

Ordering Example: TYNY-14180-100-GN, 100' of green tubing, 1/4" OD, 0.18" ID, 0.035" wall, \$30.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order Specify (Model Number)

4 to 14 mm OD Tubing, Metric Diameters

Model No.	Price	OD Nom. (mm)	ID Nom. (mm)	Wall Thickness Nom. (mm)	Bend Radius (mm)	Min. OD Tol. (mm)	ID Tol. (mm)	Max Working Pressure @ 75°F	lbs/100ft	Standard Coil Length (meters)
TYNY-427-25 ¹	\$19	4	2.7	0.65	24	+0.05-0.1	±0.1	18 BARS	1/2	50
TYNY-427-150 ¹	115	4	2.7	0.65	24	+0.05-0.1	±0.1	18 BARS	1/2	150
TYNY-42-25 ²	22	4	2	1	24	+0.05-0.1	±0.1	33 BARS	3/4	25
TYNY-42-150 ²	132	4	2	1	24	+0.05-0.1	±0.1	33 BARS	3/4	150
TYNY-533-25 ³	28	5	3.3	0.85	30	+0.05-0.1	±0.1	17 BARS	7/8	25
TYNY-533-150 ³	166	5	3.3	0.85	30	+0.05-0.1	±0.1	17 BARS	7/8	150
TYNY-64-25 ¹	33	6	4	1	36	+0.05-0.1	±0.1	21 BARS	1	25
TYNY-64-150 ¹	200	6	4	1	36	+0.05-0.1	±0.1	21 BARS	1	150
TYNY-86-25 ¹	46	8	6	1	48	+0.05-0.1	±0.1	14 BARS	1 1/2	25
TYNY-86-150 ¹	277	8	6	1	48	+0.05-0.1	±0.1	14 BARS	1 1/2	150
TYNY-855-25 ⁴	61	8	5.5	1.25	50	+0.05-0.1	±0.1	18 BARS	1 3/4	25
TYNY-855-150 ⁴	366	8	5.5	1.25	50	+0.05-0.1	±0.1	18 BARS	1 3/4	150
TYNY-108-25 ¹	59	10	8	1	60	+0.05-0.1	±0.1	10 BARS	3	25
TYNY-108-150 ¹	352	10	8	1	60	+0.05-0.1	±0.1	10 BARS	3	150
TYNY-1075-25 ⁴	63	10	7.5	1.25	70	+0.05-0.1	±0.1	14 BARS	3 1/4	25
TYNY-1075-150 ⁴	378	10	7.5	1.25	70	+0.05-0.1	±0.1	14 BARS	3 1/4	150
TYNY-1210-25 ¹	67	12	10	1	75	+0.05-0.1	±0.1	8 BARS	4 1/2	25
TYNY-1210-150 ¹	402	12	10	1	75	+0.05-0.1	±0.1	8 BARS	4 1/2	150
TYNY-129-25 ⁴	102	12	9	1.5	84	+0.05-0.1	±0.1	15 BARS	4 3/4	25
TYNY-129-150 ⁴	610	12	9	1.5	84	+0.05-0.1	±0.1	15 BARS	4 3/4	150
TYNY-1412-25 ²	102	14	12	1	98	+0.05-0.1	±0.1	6 BARS	5	25
TYNY-1411-25 ⁴	142	14	11	1.5	100	+0.05-0.1	±0.1	13 BARS	6	25

Note: Specified minimum bend radius is for minimal tube flattening.

Standard color is natural translucent white. Color options are available, see opposite page for ordering suffixes.

Ordering Example: TYNY-86-150-R, 150 m of red tubing, 8" OD, 6" ID, 1" wall, \$277.

T-X

T



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters