

HIGH WATT DENSITY CARTRIDGE HEATERS WITH INCOLOY® SHEATH 3/8" DIAMETER

CIR Series Starts at **\$35**



- Premium Quality
- Rugged Construction
- 120 and 240V Models Available
- Lengths from 1¼ to 24" (3 to 61 cm)

OMEGALUX® CIR series high watt density cartridge heaters are especially well suited for use in applications involving molds, dies, platens, hot plates, and sealing operations. They are available in lengths from 1¼ to 24" (3 to 61 cm).

SPECIFICATIONS

Sheath: Material, Incoloy; black oxide finish for efficient heat transfer; max. temp. 816°C (1500°F) welded, sealed tip
Leads: Type "F"; stranded, flexible manganese nickel wire insulated with

fiberglass, max. temp. 450°C (842°F), 14" standard length. Longer leads available.
Heater Wire: Premium grade nickel-chromium resistance wire for longer life, and consistent performance
Insulation: Specially formulated refractory insulation, rigidly controlled, densely compacted to improve thermal conductivity and dielectric strength
Internal Connections: Patented connector for high reliability and longer life. Vibration and shock resistant construction.
Voltage: 120V or 240 Vac, must be specified at time of order

3/8" Nominal Diameter CIR Series (Actual Dia. & Tolerance: 0.373" ±0.005")

MOST POPULAR MODELS HIGHLIGHTED!

To Order																	
Shth. in (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Shth. in (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Shth. in (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)
1¼ (3)	100	114	CIR-2013/120	\$35	.05(.2)	2½ (6)	250	107	CIR-20251/*	\$41	.10(.05)	5 (13)	750	142	CIR-2054/240	\$50	.20(.09)
1¼ (3)	125	143	CIR-20131/120	35	.05(.2)	2½ (6)	300	129	CIR-2029/*	41	.10(.05)	5 (13)	1000	190	CIR-2056/240	50	.20(.09)
1¼ (3)	150	171	CIR-2012/*	35	.05(.2)	2½ (6)	400	171	CIR-2026/*	41	.10(.05)	5½ (13)	200	44	CIR-2057/240	51	.21(.1)
1¼ (3)	200	228	CIR-2014/*	35	.05(.2)	2½ (6)	500	214	CIR-20252/*	41	.10(.05)	5½ (14)	600	102	CIR-2058/240	53	.22(.1)
1½ (4)	50	43	CIR-2018/120	36	.06(.3)	2½ (6)	250	91	CIR-20253/120	43	.11(.05)	5½ (14)	1000	171	CIR-2059/240	53	.24(.1)
1½ (4)	85	73	CIR-2016/120	36	.06(.3)	2½ (6)	300	109	CIR-20254/240	43	.11(.05)	6 (15)	200	31	CIR-2064/120	56	.24(.1)
1½ (4)	100	85	CIR-20151/*	36	.06(.3)	3 (8)	100	34	CIR-2032/*	44	.12(.05)	6 (15)	250	39	CIR-2061/*	56	.24(.1)
1½ (4)	130	111	CIR-20152/240	36	.06(.3)	3 (8)	150	51	CIR-2033/*	44	.12(.05)	6 (15)	400	62	CIR-2065/*	56	.24(.1)
1½ (4)	150	129	CIR-2019/*	36	.06(.3)	3 (8)	200	68	CIR-2031/*	44	.12(.05)	6 (15)	500	78	CIR-2060/*	56	.24(.1)
1½ (4)	200	171	CIR-2015/*	36	.06(.3)	3 (8)	250	85	CIR-2034/*	44	.12(.05)	6 (15)	600	93	CIR-2066/*	56	.24(.1)
1½ (4)	250	214	CIR-20191/*	36	.06(.3)	3 (8)	300	103	CIR-20301/*	44	.12(.05)	6 (15)	750	117	CIR-2062/240	56	.24(.1)
1¾ (4)	125	85	CIR-2017/120	37	.06(.3)	3 (8)	400	137	CIR-20302/*	44	.12(.05)	6 (15)	1000	155	CIR-2063/240	56	.24(.1)
1¾ (4)	175	120	CIR-20171/120	37	.06(.3)	3 (8)	500	171	CIR-2030/*	44	.12(.05)	6½ (17)	600	85	CIR-2067/240	60	.26(.1)
1¾ (4)	250	170	CIR-20172/*	37	.06(.3)	3 (8)	600	205	CIR-2036/240	44	.12(.05)	6½ (17)	1000	143	CIR-2068/240	60	.26(.1)
1¾ (5)	200	128	CIR-20173/120	38	.06(.3)	3½ (9)	250	71	CIR-2037/*	46	.14(.06)	7 (18)	250	33	CIR-2070/*	63	.28(.1)
2 (5)	50	29	CIR-20201/120	39	.07(.3)	3½ (9)	300	86	CIR-2038/*	46	.14(.06)	7 (18)	600	79	CIR-2076/*	63	.28(.1)
2 (5)	75	42	CIR-20209/120	39	.07(.3)	3½ (9)	500	142	CIR-2035/*	49	.14(.06)	7 (18)	1000	131	CIR-2079/240	63	.28(.1)
2 (5)	100	57	CIR-20202/*	39	.07(.3)	3½ (9)	150	37	CIR-2039/120	48	.15(.07)	7½ (19)	600	73	CIR-2075/240	66	.30(.1)
2 (5)	150	85	CIR-2021/*	39	.07(.3)	3½ (9)	500	128	CIR-20303/240	48	.15(.07)	7½ (19)	1000	122	CIR-2077/240	66	.30(.1)
2 (5)	200	114	CIR-20203/*	39	.07(.3)	4 (10)	125	30	CIR-2045/*	49	.16(.07)	8 (20)	300	34	CIR-2081/*	69	.32(.1)
2 (5)	250	142	CIR-2020/*	39	.07(.3)	4 (10)	150	37	CIR-2041/*	49	.16(.07)	8 (20)	400	45	CIR-2082/120	69	.32(.1)
2 (5)	300	171	CIR-20204/*	39	.07(.3)	4 (10)	175	44	CIR-2046/120	49	.16(.07)	8 (20)	500	57	CIR-2085/*	69	.32(.1)
2 (5)	350	199	CIR-20205/*	39	.07(.3)	4 (10)	200	51	CIR-2044/240	66	.16(.07)	8 (20)	600	68	CIR-2086/*	69	.32(.1)
2 (5)	400	228	CIR-20206/*	39	.07(.3)	4 (10)	250	61	CIR-2042/*	49	.16(.07)	8 (20)	700	80	CIR-2080/*	69	.32(.1)
2 (5)	500	262	CIR-20207/*	39	.07(.3)	4 (10)	300	73	CIR-2040/*	49	.16(.07)	8 (20)	1000	115	CIR-2089/240	69	.32(.1)
2½ (6)	75	37	CIR-20225/120	39	.08(.4)	4 (10)	400	102	CIR-2047/*	49	.16(.07)	9½ (24)	600	57	CIR-2090/240	79	.38(.2)
2½ (6)	100	49	CIR-20221/*	40	.08(.4)	4 (10)	450	110	CIR-2048/240	49	.16(.07)	9½ (24)	1000	97	CIR-2091/240	79	.38(.2)
2½ (6)	125	61	CIR-2023/*	40	.08(.4)	4 (10)	500	122	CIR-2043/*	49	.16(.07)	10 (25)	400	36	CIR-2102/120	82	.40(.2)
2½ (6)	150	73	CIR-20222/*	40	.08(.4)	4 (10)	550	133	CIR-2049/120	49	.16(.07)	10 (25)	600	54	CIR-2100/*	82	.40(.2)
2½ (6)	175	86	CIR-20226/120	40	.08(.4)	4½ (11)	300	64	CIR-20401/*	47	.18(.08)	10 (25)	1000	90	CIR-2101/240	82	.40(.2)
2½ (6)	200	98	CIR-20223/*	40	.08(.4)	4½ (11)	500	106	CIR-20402/*	47	.18(.08)	12 (30)	500	30	CIR-2122/120	95	.48(.2)
2½ (6)	250	122	CIR-2022/*	40	.08(.4)	4½ (11)	300	58	CIR-20403/240	49	.19(.09)	12 (30)	600	45	CIR-2123/*	95	.48(.2)
2½ (6)	300	147	CIR-20224/*	40	.08(.4)	4½ (11)	500	97	CIR-20404/240	49	.19(.09)	12 (30)	900	67	CIR-2120/*	95	.48(.2)
2½ (6)	350	172	CIR-20227/*	40	.08(.4)	5 (13)	150	29	CIR-2055/*	50	.20(.09)	12 (30)	1000	74	CIR-2121/240	95	.48(.2)
2¾ (6)	75	34	CIR-2025/120	41	.09(.4)	5 (13)	200	88	CIR-2051/*	50	.20(.09)	15 (38)	1100	65	CIR-2150/240	115	.80(.4)
2¾ (6)	165	75	CIR-2024/*	41	.09(.4)	5 (13)	300	57	CIR-2052/*	50	.20(.09)	20 (51)	1300	57	CIR-2200/240	147	.80(.4)
2½ (6)	100	43	CIR-2027/240	41	.10(.05)	5 (13)	400	76	CIR-2050/*	50	.20(.09)	24(61)	1500	55	CIR-2240/240	173	.90(.4)
2½ (6)	200	86	CIR-2028/*	41	.10(.05)	5 (13)	500	95	CIR-2053/*	50	.20(.09)						

*Designate voltage, insert "120" for 120 Vac or "240" for 240 Vac. Those model numbers containing 120 or 240 are only available in that voltage.

†Consult Sales.

Note: 3/8" (1cm) diameter CIR series cartridge heaters use 17 AWG stranded lead wire.

Ordering Example: CIR-2054/240, 5", high watt density cartridge heater, \$50.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters