


FLEXIBLE SILICONE RUBBER FIBERGLASS INSULATED HEATERS

- ✓ Lightweight Thin, Flexible
- ✓ Available in 2.5, 5 and 10 W/in²
- ✓ -56 to 232°C (-70 to 450°F) Operating Temperature
- ✓ Etched Foil and Wire Wound Design
- ✓ Round or Rectangular Shapes
- ✓ Available in 115 or 230** Vac
- ✓ Optional Pressure Sensitive Adhesive (PSA)[†]

SRF Series Starts at
\$26



OMEGALUX[®] silicone rubber fiberglass insulated flexible heaters can improve heat transfer and speed warm-ups where controlled heating is required in confined areas. Two circuit designs are available: etched foil or wire wound. Heaters with etched foil designed elements are available where the length or width dimension is less than 305 mm (12"). All other heaters where both the length and

the width dimensions exceed 305 mm (12") use the wire-wound element design. Effect of power density: gentle warming is best done with 2.5 W/in². A good all purpose unit is the 5 W/in². Rapid warm-up and high temperature are

achieved with the 10 W/in²; however, temperature must be controlled as the safe maximum operating temperature limit of 232°C (450°F) may be exceeded.

Round Silicone Rubber Heaters

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)							
Diameter cm (in)	Total Wattage for Watt Density			Without PSA Model No.	Price	With PSA Model No.	Price
	2.5 W/in ²	5 W/in ²	10 W/in ²				
7.6 (3)	17.5	35	70	SRFR-3/*	\$26	SRFR-3/*-P	\$28
10 (4)	31.4	62.8	125.6	SRFR-4/*	32	SRFR-4/*-P	35
13 (5)	49.0	98.15	196.3	SRFR-5/*	39	SRFR-5/*-P	42
15 (6)	70.67	141.3	282.7	SRFR-6/*	40	SRFR-6/*-P	44
18 (7)	96.2	192.4	384.8	SRFR-7/*	44	SRFR-7/*-P	48
20 (8)	125.65	251.3	502.6	SRFR-8/*	48	SRFR-8/*-P	53
23 (9)	157.9	315.8	631.7	SRFR-9/*	53	SRFR-9/*-P	59
25 (10)	196.25	392.5	785	SRFR-10/*	59	SRFR-10/*-P	65
28 (11)	237.45	474.9	949.8	SRFR-11/*	65	SRFR-11/*-P	72
30 (12)	376.8	753.6	1507.2	SRFR-12/*	72	SRFR-12/*-P	79

Comes with complete operator's manual

* Insert watt density: 2 for 2.5 W/in², 5 for 5 W/in² or 10 for 10 W/in².

** Most sizes available in 230V. Contact Engineering.

† Heaters with pressure sensitive adhesive: max operating temperature is 149°C (300°F).

Ordering Examples: SRFR-3/10, 7.6 cm (3") diameter heater with a watt density of 10 W/in² and 70 watts of total power, \$26.

SFRG-208/10

SRFR-11/10, 28 cm (11") diameter heater with a 10 W/in², 949 watts \$72.

CAUTION AND WARNING!
 Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.

Rectangular Silicone Rubber Heaters

 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)								
Width, cm (")	Length, cm (")	Total Wattage for Watt Density			Without PSA Model No.	Price	With PSA Model No.	Price
		2.5 W/in ²	5 W/in ²	10 W/in ²				
2.5 (1)	2.5 (1)	–	–	10	SRFG-101/10	\$21	SRFG-101/10-P	\$23
2.5 (1)	5 (2)	5	10	–	SRFG-102/*	22	SRFG-102/*-P	24
2.5 (1)	7.6 (3)	7.5	15	30	SRFG-103/*	22	SRFG-103/*-P	25
2.5 (1)	10 (4)	10	20	40	SRFG-104/*	23	SRFG-104/*-P	26
2.5 (1)	13 (5)	12.5	25	50	SRFG-105/*	24	SRFG-105/*-P	27
2.5 (1)	15 (6)	15	30	60	SRFG-106/*	25	SRFG-106/*-P	27
2.5 (1)	18 (7)	17.5	35	70	SRFG-107/*	26	SRFG-107/*-P	29
2.5 (1)	20 (8)	20	40	80	SRFG-108/*	18	SRFG-108/*-P	20
2.5 (1)	23 (9)	22.5	45	90	SRFG-109/*	19	SRFG-109/*-P	20
2.5 (1)	25 (10)	25	50	100	SRFG-110/*	19	SRFG-110/*-P	21
2.5 (1)	28 (11)	27.5	55	110	SRFG-111/*	20	SRFG-111/*-P	22
2.5 (1)	30 (12)	30	60	120	SRFG-112/*	20	SRFG-112/*-P	22
2.5 (1)	46 (18)	45	90	180	SRFG-118/*	24	SRFG-118/*-P	26
2.5 (1)	61 (24)	60	120	240	SRFG-124/*	28	SRFG-124/*-P	30
2.5 (1)	76 (30)	75	150	300	SRFG-130/*	29	SRFG-130/*-P	32
2.5 (1)	91 (36)	90	180	360	SRFG-136/*	35	SRFG-136/*-P	38
2.5 (1)	107 (42)	105	210	420	SRFG-142/*	38	SRFG-142/*-P	42
2.5 (1)	122 (48)	120	240	480	SRFG-148/*	42	SRFG-148/*-P	46
5 (2)	5 (2)	10	20	40	SRFG-202/*	22	SRFG-202/*-P	24
5 (2)	7.6 (3)	15	30	60	SRFG-203/*	23	SRFG-203/*-P	25
5 (2)	10 (4)	20	40	80	SRFG-204/*	24	SRFG-204/*-P	26
5 (2)	13 (5)	25	50	100	SRFG-205/*	20	SRFG-205/*-P	22
5 (2)	15 (6)	30	60	120	SRFG-206/*	22	SRFG-206/*-P	23
5 (2)	18 (7)	35	70	140	SRFG-207/*	21	SRFG-207/*-P	24
5 (2)	20 (8)	40	80	160	SRFG-208/*	23	SRFG-208/*-P	25
5 (2)	23 (9)	45	90	180	SRFG-209/*	24	SRFG-209/*-P	26
5 (2)	25 (10)	50	100	200	SRFG-210/*	25	SRFG-210/*-P	27
5 (2)	28 (11)	55	110	220	SRFG-211/*	25	SRFG-211/*-P	28
5 (2)	30 (12)	60	120	240	SRFG-212/*	26	SRFG-212/*-P	29
5 (2)	46 (18)	90	180	360	SRFG-218/*	32	SRFG-218/*-P	35
5 (2)	61 (24)	120	240	480	SRFG-224/*	37	SRFG-224/*-P	40
5 (2)	76 (30)	150	300	600	SRFG-230/*	42	SRFG-230/*-P	45
5 (2)	91 (36)	180	360	720	SRFG-236/*	48	SRFG-236/*-P	52
5 (2)	107 (42)	210	420	840	SRFG-242/*	52	SRFG-242/*-P	58
5 (2)	122 (48)	240	480	960	SRFG-248/*	58	SRFG-248/*-P	64
7.6 (3)	7.6 (3)	22.5	45	90	SRFG-303/*	23	SRFG-303/*-P	26
7.6 (3)	10 (4)	30	60	120	SRFG-304/*	25	SRFG-304/*-P	27
7.6 (3)	13 (5)	37.5	75	150	SRFG-305/*	26	SRFG-305/*-P	28
7.6 (3)	15 (6)	45	90	180	SRFG-306/*	27	SRFG-306/*-P	30
7.6 (3)	18 (7)	52.5	105	210	SRFG-307/*	28	SRFG-307/*-P	31
7.6 (3)	20 (8)	60	120	240	SRFG-308/*	29	SRFG-308/*-P	32
7.6 (3)	23 (9)	67.5	135	270	SRFG-309/*	31	SRFG-309/*-P	34
7.6 (3)	25 (10)	75	150	300	SRFG-310/*	32	SRFG-310/*-P	35
7.6 (3)	28 (11)	82.5	165	330	SRFG-311/*	33	SRFG-311/*-P	36
7.6 (3)	30 (12)	90	180	360	SRFG-312/*	34	SRFG-312/*-P	38

Comes complete with operator's manual

* Insert watt density: 2 for 2.5 W/in², 5 for 5 W/in² or 10 for 10W/in².

** Most sizes available in 230V. Consult heater sales and engineering.

Ordering Examples: SRFG-208/5-P, 5 x 20 cm (2 x 8") heater with a watt density of 5 W/in², total rated wattage output of 80 watts, with optional pressure sensitive adhesive, \$25.

SRFG-208/10, 10 W/in², 160 watts, \$23.

Note: Heaters are available in only the watt densities where total wattage is shown. Heaters with pressure sensitive adhesive: max operating temperature is 149°C (300°F).

FLEXIBLE HEATERS

Rectangular Silicone Rubber Heaters

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)								
Width, cm (")	Length, cm (")	Total Wattage for Watt Density			Without PSA Model No.	Price	With PSA Model No.	Price
		2.5 W/in ²	5 W/in ²	10 W/in ²				
7.6 (3)	46 (18)	135	270	540	SRFG-318/*	\$42	SRFG-318/*-P	\$46
7.6 (3)	61 (24)	180	360	720	SRFG-324/*	49	SRFG-324/*-P	54
7.6 (3)	76 (30)	225	450	900	SRFG-330/*	56	SRFG-330/*-P	62
7.6 (3)	91 (36)	270	540	1080	SRFG-336/*	63	SRFG-336/*-P	70
7.6 (3)	107 (42)	315	630	1260	SRFG-342/*	71	SRFG-342/*-P	78
7.6 (3)	122 (48)	360	720	1440	SRFG-348/*	78	SRFG-348/*-P	86
10 (4)	10 (4)	40	80	160	SRFG-404/*	29	SRFG-404/*-P	32
10 (4)	13 (5)	50	100	200	SRFG-405/*	31	SRFG-405/*-P	34
10 (4)	15 (6)	60	120	240	SRFG-406/*	32	SRFG-406/*-P	35
10 (4)	18 (7)	70	140	280	SRFG-407/*	34	SRFG-407/*-P	37
10 (4)	20 (8)	80	160	320	SRFG-408/*	35	SRFG-408/*-P	39
10 (4)	23 (9)	90	180	360	SRFG-409/*	37	SRFG-409/*-P	41
10 (4)	25 (10)	100	200	400	SRFG-410/*	38	SRFG-410/*-P	42
10 (4)	28 (11)	110	220	440	SRFG-411/*	40	SRFG-411/*-P	44
10 (4)	30 (12)	120	240	480	SRFG-412/*	41	SRFG-412/*-P	46
10 (4)	46 (18)	180	360	720	SRFG-418/*	51	SRFG-418/*-P	56
10 (4)	61 (24)	240	480	960	SRFG-424/*	60	SRFG-424/*-P	66
10 (4)	76 (30)	300	600	1200	SRFG-430/*	69	SRFG-430/*-P	76
10 (4)	91 (36)	360	720	1440	SRFG-436/*	78	SRFG-436/*-P	86
10 (4)	107 (42)	420	840	1680	SRFG-442/*	88	SRFG-442/*-P	96
10 (4)	122 (48)	480	960	—	SRFG-448/*	97	SRFG-448/*-P	106
13 (5)	13 (5)	62.5	125	250	SRFG-505/*	35	SRFG-505/*-P	39
13 (5)	15 (6)	75	150	300	SRFG-506/*	37	SRFG-506/*-P	41
13 (5)	18 (7)	87.5	175	350	SRFG-507/*	39	SRFG-507/*-P	42
13 (5)	20 (8)	100	200	400	SRFG-508/*	40	SRFG-508/*-P	44
13 (5)	23 (9)	112.5	225	450	SRFG-509/*	42	SRFG-509/*-P	46
13 (5)	25 (10)	125	250	500	SRFG-510/*	44	SRFG-510/*-P	48
13 (5)	28 (11)	137.5	275	550	SRFG-511/*	46	SRFG-511/*-P	50
13 (5)	30 (12)	150	300	600	SRFG-512/*	48	SRFG-512/*-P	52
15 (6)	15 (6)	90	180	360	SRFG-606/*	38	SRFG-606/*-P	42
15 (6)	18 (7)	105	210	420	SRFG-607/*	40	SRFG-607/*-P	44
15 (6)	20 (8)	120	240	480	SRFG-608/*	40	SRFG-608/*-P	44
15 (6)	23 (9)	135	270	540	SRFG-609/*	42	SRFG-609/*-P	46
15 (6)	25 (10)	150	300	600	SRFG-610/*	43	SRFG-610/*-P	47
15 (6)	28 (11)	165	330	660	SRFG-611/*	44	SRFG-611/*-P	48
15 (6)	30 (12)	180	360	720	SRFG-612/*	46	SRFG-612/*-P	51
15 (6)	46 (18)	270	540	1080	SRFG-618/*	56	SRFG-618/*-P	61
15 (6)	61 (24)	360	720	1440	SRFG-624/*	66	SRFG-624/*-P	92
15 (6)	76 (30)	450	900	—	SRFG-630/*	76	SRFG-630/*-P	83
15 (6)	91 (36)	540	1080	—	SRFG-636/*	85	SRFG-636/*-P	94
15 (6)	107 (42)	630	1260	—	SRFG-642/*	91	SRFG-642/*-P	100
15 (6)	122 (48)	720	1440	—	SRFG-648/*	105	SRFG-648/*-P	115
18 (7)	18 (7)	122.5	245	490	SRFG-707/*	40	SRFG-707/*-P	44
18 (7)	20 (8)	140	280	560	SRFG-708/*	42	SRFG-708/*-P	46
18 (7)	23 (9)	157.5	315	630	SRFG-709/*	44	SRFG-709/*-P	48

Comes complete with operator's manual. * Insert watt density: 2 for 2.5 W/in², 5 for 5 W/in² or 10 for 10W/in².

** Most sizes available in 230V. Consult heater sales and engineering.

Ordering Examples: SRFG-404/5-P, 10 x 10 cm (4 x 4") heater with a watt density of 5 W/in², total rated wattage output of 80 watts, with optional pressure sensitive adhesive, \$32.

SRFG-318/5, 5 W/in², 270 watts, \$42.

Note: Heaters are available in only the watt densities where total wattage is shown.

Heaters with pressure sensitive adhesive: max operating temperature is 149°C (300°F).

Rectangular Silicone Rubber Heaters

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)								
Width, cm (")	Length, cm (")	Total Wattage for Watt Density			Without PSA Model No.	Price	With PSA Model No.	Price
		2.5 W/in ²	5 W/in ²	10 W/in ²				
18 (7)	25 (10)	175	350	700	SRFG-710/*	\$46	SRFG-710/*-P	\$50
18 (7)	28 (11)	192.5	385	770	SRFG-711/*	47	SRFG-711/*-P	52
18 (7)	30 (12)	210	420	840	SRFG-712/*	47	SRFG-712/*-P	54
20 (8)	20 (8)	160	320	640	SRFG-808/*	44	SRFG-808/*-P	48
20 (8)	23 (9)	180	360	720	SRFG-809/*	46	SRFG-809/*-P	51
20 (8)	25 (10)	200	400	800	SRFG-810/*	48	SRFG-810/*-P	53
20 (8)	28 (11)	220	440	880	SRFG-811/*	50	SRFG-811/*-P	55
20 (8)	30 (12)	240	480	960	SRFG-812/*	53	SRFG-812/*-P	58
20 (8)	46 (18)	360	720	1440	SRFG-818/*	66	SRFG-818/*-P	72
20 (8)	61 (24)	480	960	—	SRFG-824/*	79	SRFG-824/*-P	86
20 (8)	76 (30)	600	1200	—	SRFG-830/*	92	SRFG-830/*-P	101
20 (8)	91 (36)	720	1440	—	SRFG-836/*	105	SRFG-836/*-P	115
20 (8)	107 (42)	840	1680	—	SRFG-842/*	118	SRFG-842/*-P	129
20 (8)	122 (48)	960	1920	—	SRFG-848/*	131	SRFG-848/*-P	144
23 (9)	23 (9)	202.5	405	810	SRFG-909/*	49	SRFG-909/*-P	53
23 (9)	25 (10)	225	450	900	SRFG-910/*	51	SRFG-910/*-P	56
23 (9)	28 (11)	247.5	495	990	SRFG-911/*	53	SRFG-911/*-P	59
23 (9)	30 (12)	270	540	1080	SRFG-912/*	56	SRFG-912/*-P	61
25 (10)	25 (10)	250	500	1000	SRFG-1010/*	52	SRFG-1010/*-P	59
25 (10)	28 (11)	275	550	1100	SRFG-1011/*	58	SRFG-1011/*-P	64
25 (10)	30 (12)	300	600	1200	SRFG-1012/*	59	SRFG-1012/*-P	65
25 (10)	46 (18)	450	900	—	SRFG-1018/*	75	SRFG-1018/*-P	82
25 (10)	61 (24)	600	1200	—	SRFG-1024/*	92	SRFG-1024/*-P	101
25 (10)	76 (30)	750	1500	—	SRFG-1030/*	108	SRFG-1030/*-P	118
25 (10)	91 (36)	900	1800	—	SRFG-1036/*	124	SRFG-1036/*-P	136
25 (10)	122 (48)	1200	—	—	SRFG-1048/*	157	SRFG-1048/*-P	172
28 (11)	28 (11)	302.5	605	1210	SRFG-1111/*	59	SRFG-1111/*-P	65
28 (11)	30 (12)	330	660	1320	SRFG-1112/*	62	SRFG-1112/*-P	69
30 (12)	30 (12)	360	720	—	SRFG-1212/*	71	SRFG-1212/*-P	74
30 (12)	46 (18)	540	1080	—	SRFG-1218/*	85	SRFG-1218/*-P	88
30 (12)	61 (24)	720	1440	—	SRFG-1224/*	105	SRFG-1224/*-P	115
30 (12)	76 (30)	900	—	—	SRFG-1230/*	124	SRFG-1230/*-P	136
30 (12)	91 (36)	1080	—	—	SRFG-1236/*	144	SRFG-1236/*-P	158
30 (12)	107 (42)	1260	—	—	SRFG-1242/*	163	SRFG-1242/*-P	180
30 (12)	122 (48)	1440	—	—	SRFG-1248/*	183	SRFG-1248/*-P	201

Comes complete with operator's manual.

* Insert watt density: 2 for 2.5 W/in², 5 for 5 W/in² or 10 for 10W/in².

** Most sizes available in 230V. Consult heater sales and engineering.

Ordering Example: SRFG-712/5-P, 18 x 30 cm (7 x 12") heater with a watt density of 5 W/in², total rated wattage output of 420 watts, with optional pressure sensitive adhesive, \$54.

Note: Heaters are available in only the watt densities where total wattage is shown. Heaters with pressure sensitive adhesive: max operating temperature is 149°C (300°F).

Recommended Reference Book:
Process Design Principles,
PE-1320, \$34.
See Section Y for Additional Books.



APPLICATIONS

- ✓ Freeze Protection
- ✓ Low Temperature Ovens
- ✓ Heat Tracing Systems
- ✓ Viscosity Control
- ✓ Dehumidification of Motors and Control Devices

SPECIFICATIONS

Wattage: 5 to 1440 Watts
Power: 115 or 230** Vac
Watt Density: 2.5, 5 and 10 W/in²
Lead Wire:
 305 mm (12") PFA insulated
Thickness: 0.045 to 0.0700",
 except at lead wire exit

Dielectric Strength: 1250 Vac
Maximum Temperature: heaters without pressure sensitive adhesive, 232°C (450°F); heaters with pressure sensitive adhesive, 149°C (300°F)
Minimum Temperature: -56°C (-70°F)



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters