


# ECONOMICAL DIGITAL TRANSDUCER INDICATORS FOR STRAIN GAGE OR PROCESS INPUTS

## DP302 Series

Starts at  
**\$195**



DP3002-S digital indicator, \$320, shown actual size, with LCGD-250 load cell, \$490, see page F-27.

- ✓ AC Power Standard; DC Power Optional
- ✓ Models Available for Millivolts, Voltage, or Current Output Type Transducers
- ✓ Easily Scaled to Display Readings in Engineering Units
- ✓ 3½ or 4½ Digit Models Available

The DP302 and DP3002 low-cost digital panel meters are designed for applications in which only indication is required. The DP302 models have a 3½ digit display that can read ±1999 counts. The DP3002 models have a 4½ digit display and can read ±19999 counts. Both models can easily be scaled to display engineering units.

### SPECIFICATIONS

**Accuracy:**  
**DP302:** ±0.05% of span + 1 count  
**DP3002:** ±0.01 % of span + 2 counts

**Operating Temp:** 0 to 60°C (32 to 140°F)

**Span Temp Coefficient:** ±0.01% of span/°C

**Zero Temp Coefficient:**  
**DP302:** ±0.1 count/°C  
**DP3002:** ±0.5 count/°C

**Storage Temperature:** -40 to 85°C (-40 to 185°F)

**Humidity:** 95% RH to 40°C (104°F) (non-condensing)

**CMRR:** 120 dB from DC to 60 Hz

**Common Mode Voltage:** 1500 Vp per HV test, 354 Vp per IEC spacing

**NMRR:** 56 dB at 50/60 Hz

**Display Type:** 7-segment, red LED

**Display Digits:**  
**DP302:** 3½ (±1999 counts)  
**DP3002:** 4½ (±19999 counts)

**Digit Height:** 14.2 mm (0.56")  
**Conversion Rate:** 2.5/s

### POWER REQUIREMENTS

**AC Models:** 115 Vac ±15%, 230 Vac ±15% (optional)  
**Frequency Range:** 47 to 400 Hz  
**DC Models:** 9 to 32 Vdc (300V isolation)  
**Power Consumption:** 2.4 W (3.7 W with excitation)  
**Excitation:** Adjustable 10 to 24 Vdc @ 30 mA ("E" and "S" models only)

### MECHANICAL SPECIFICATIONS

**Bezel:** 96 W x 48 H x 5.1 mm D (3.78 x 1.89 x 0.20")  
**Depth Behind Bezel:** 104 mm (4.09")  
**Panel Cutout:** 92 W x 45 mm H (3.62 x 1.77")  
**Weight:** 425 g (15 oz)

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

MODEL NO.	DIGITS	PRICE	INPUT RANGES*	EXCITATION
DP302-P	3½	\$195	4 to 20 mA, 1 to 5 Vdc, 0 to 10 Vdc	None
DP302-E	3½	255	4 to 20 mA, 1 to 5 Vdc, 0 to 10 Vdc	10 to 24 Vdc
DP302-S	3½	285	±20 mVdc, 200 mVdc, 2 Vdc	10 to 24 Vdc
DP3002-P	4½	280	4 to 20 mA, 1 to 5 Vdc, 0 to 10 Vdc	None
DP3002-E	4½	295	4 to 20 mA, 1 to 5 Vdc, 0 to 10 Vdc	10 to 24 Vdc
DP3002-S	4½	320	±20 mVdc, 200 mVdc, 2 Vdc	10 to 24 Vdc

\* Input ranges selected by internal jumpers.

For 230 Vac power, add suffix "-230", no extra charge. For 9 to 32 Vdc power, add suffix "-DC" and add \$120 to price.

**Ordering Example:** DP3002-P, 4½ digit display process panel meter, \$280.

Recommended Reference Book:  
 Applied Structural and Mechanical Vibrations,  
**CE-1910, \$180.**  
 Visit [omega.com/bobi](http://omega.com/bobi)  
 for Additional Books





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters