

VACUUM GAUGES ELECTRONIC AND DIGITAL

DVG-60
\$135




- ✓ Reads From 5000 Down to 50 Microns
- ✓ Cleanable Thermistor Sensor for Repeated Accuracy
- ✓ Single Switch Operation
- ✓ Low-Battery Indicator
- ✓ Color-Coded LED Display Shows Vacuum Range
- ✓ Built-In Hanger/Stand
- ✓ Furnished with Vinyl Protective Case

The OMEGA DVG-60 is a durable, self-contained, battery-powered electronic vacuum gauge that displays the level of vacuum on an LED color-coded readout.

The 10 level color-coded LEDs display the vacuum level from 5000 down to 50 microns.

SPECIFICATIONS

Range: 10 segments to 50 microns
Connections: Standard 1/4" male flare fitting
Power: 9V alkaline battery (included)
Dimensions: 140 H x 44.5 W x 38 mm D (5.5 x 1.75 x 1.5")
Case: Polycarbonate
Carrying Case: Included



DVG-60, \$135, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	RANGE
DVG-60	\$135	5000 to 50 microns

Comes complete with operator's manual, carrying case, and 9V battery.
Ordering Example: DVG-60, electronic vacuum gauge, \$135.

DVG-64
\$175



- ✓ 12,000 to 0 Microns
- ✓ Reads Vacuum in 7 Units of Measure
- ✓ Auto Shut-Off
- ✓ Built-In Hanger
- ✓ Cleanable Sensor

The OMEGA DVG-64 digital vacuum gauge delivers high precision at a low price. It can accurately read vacuum from 12,000 microns down to 0, over a wide temperature range of 2 to 52°C (35 to 125°F). The vacuum can be displayed in user-selectable units.

SPECIFICATIONS

Display: Updated every 1/2 second; 1 micron resolution below 200 microns
Sensor Type: Thermistor
Connector Type: Standard 1/4" male flare fitting
Vacuum Range: 0 to 12,000 microns (0 to 1600 Pa) with vacuum increasing/decreasing indicator when above 12,000 microns
Scale: Microns, psi, inHg, mbar, Pa, torr, millitorr
Operating Temperature Range: 2 to 52°C (35 to 125°F)
Overpressure: 300 psi max (20 bar)
Accuracy: ±10% (0 to 1000 microns)
Power Source: 9V alkaline battery (included)
Continuous Usage: Over 35 hr
Auto Shut-Off: After 10 min when vacuum reading is above 12,000 microns
Weight: 0.2 kg (6.7 oz)
Dimensions: 140 H x 76 W x 32 mm D (5.5 x 3 x 1.25")



DVG-64, \$175, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	RANGE
DVG-64	\$175	12,000 microns to 0

Comes complete with operator's manual and 9V battery.
Ordering Example: DVG-64, digital vacuum gauge, \$175.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters