

SANITARY CURRENT OUTPUT PRESSURE TRANSDUCER PROVEN THIN-FILM TECHNOLOGY

PX792 Series
Ranges from Vacuum to 1000 psi
(69 bar)
4 to 20 mA Output

Starts at
\$420



- ✓ All Stainless Steel Construction
- ✓ NEMA 4X (IP65) Enclosure
- ✓ Dairy, Food Processing, Pharmaceutical, Biotech Applications
- ✓ High Reliability

The PX790 Series transducers use proven thin-film technology and precision machining and electro-polishing to meet 3A standards.

SPECIFICATIONS

Excitation: 10 to 36 Vdc unregulated reverse voltage protected

Output: 4 to 20 mA 2-wire

Zero Balance: ±1% FS
 $V_{min} = 10 V + (0.022A) \times R_L$

Linearity: ±0.4% BFSL

Hysteresis: +0.2%

Repeatability: ±0.07%

Stability: ±1% FS/year

Durability: 100M cycles

Operating Temperature:
-29 to 82°C (-20 to 180°F)

Compensated Temperature:
-1 to 54°C (30 to 130°F)

Thermal Effects:

Zero: ±0.04% FS/°F

Span: ±0.04% FS/°F

Proof Pressure: 200% range

Burst Pressure: 800% range

Gage Type: Stainless steel diaphragm, diffused silicon sensor

Vibration: <±0.1% FS effect for 20 g, 0 to 2000 Hz in any axis


Shock: Less than ±0.05% FS effect for 100 g, 20 ms shock in any axis

Position Effect: <0.1% FS

Response Time: 5 ms

Wetted Parts: 316L stainless steel electro-polished


Exploded view showing PX792 transducer, Tri-Grip™ clamp gasket and T-fitting.



CAUTION AND WARNING!
Sensitive Diaphragm
Do Not Touch!
Remove Protective Cap
Just Before Installation.

PX792-100G5V, with 2" Tri-Grip™ flange, \$420, shown actual size.

Connections
Red +
Black -



MODEL	A	B	C	D
1½" Tri-Grip™	20.3 (0.8)	119.4 (4.7)	22.9 (0.9)	51 (2.0)
2" Tri-Grip™	20.3 (0.8)	119.4 (4.7)	22.9 (0.9)	63.5 (2.5)



Fill Fluid: USP grade 99.5% glycerin

Pressure Port: Tri-Grip™ (Tri-Clamp® compatible) style, 2" standard, 1½" optional

Case: 300 Series SS

Electrical Connection: 24 AWG, 91.4 cm (36") PVC, shielded, vented

Weight: 383 g (13.5 oz)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

RANGE		MODEL NO.	MODEL NO.	PRICE	COMPATIBLE METERS**
psig	bar	1½" FTG*	2" FTG*		
Vac to 30	Vac to 2.1	PX791-V30GI	PX792-V30GI	\$455	DP41-E, DP302-E, DP460-E
Vac to 60	Vac to 4.1	PX791-V60GI	PX792-V60GI	455	DP41-E, DP302-E, DP460-E
Vac to 100	Vac to 6.9	PX791-V100GI	PX792-V100GI	455	DP41-E, DP3002-E, DP460-E
0 to 30	0 to 2.1	PX791-30GI	PX792-30GI	435	DP41-E, DP3002-E, DP460-E
0 to 60	0 to 4.1	PX791-60GI	PX792-60GI	420	DP41-E, DP302-E, DP460-E
0 to 100	0 to 6.9	PX791-100GI	PX792-100GI	420	DP41-E, DP302-E, DP460-E
0 to 200	0 to 13.8	PX791-200GI	PX792-200GI	420	DP41-E, DP302-E, DP460-E
0 to 300	0 to 20.7	PX791-300GI	PX792-300GI	420	DP41-E, DP3002-E, DP460-E
0 to 500	0 to 34.5	PX791-500GI	PX792-500GI	420	DP41-E, DP3002-E, DP460-E
0 to 750	0 to 51.7	PX791-750GI	PX792-750GI	420	DP41-E, DP3002-E, DP460-E
0 to 1000	0 to 68.9	PX791-1KGI	PX792-1KGI	420	DP41-E, DP3002-E, DP460-E

Comes complete with operator's manual.

* To order with 1½" fitting, change model number to PX791 (no extra charge).

** See section D for compatible meters.

Ordering Example: PX792-V100GI, 50.8 mm (2") fitting, range from vacuum to 100 psig and 4 to 20 mA output at the full scale level, \$455.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters