

3 mV/V OUTPUT CANISTER LOAD CELLS STAINLESS STEEL

LC1102/LC1112 Series

Tension/Compression
Calibrated in Tension†

LC1102 (Cable Style)

LC1112 (Connector Style)

0-50 lb to 0-100,000 lb

0-23 kg to 0-45,372 kg

1 Newton = 0.2248 lb

1 daNewton = 10 Newtons


1 lb = 454 g

1 t = 1000 kg = 2204 lb

† Ranges ≥ 100,000 lb calibrated
in compression.

Models
Available with
Built-In Amplifiers!
See Page F-87.

LC1102-5K, \$1150,
shown smaller than
actual size, see next
page for dimensions.



- ✓ FM and CSA Approved Intrinsically Safe
- ✓ Optional FM and CSA Approved for Hazardous Locations (Single Bridge Models Only)
- ✓ 5-Point Calibration Included
- ✓ Dual-Bridge Models Available
- ✓ High Accuracy

Starts at
\$995



Standard

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY		CABLE STYLE	CONNECTOR STYLE	PRICE	COMPATIBLE METERS**	LOAD BUTTON		ROD END	
lb	kg					MODEL	PRICE	MODEL	PRICE
50	23	LC1102-50	LC1112-50	\$995	DP41-B, DP41-S, DP25B-S	LBC-038	\$40	REC-038M	\$20
100	45	LC1102-100	LC1112-100	995	DP41-B, DP41-S, DP25B-S	LBC-038	40	REC-038M	20
300	136	LC1102-300	LC1112-300	995	DP41-B, DP41-S, DP25B-S	LBC-038	40	REC-038M	20
500	227	LC1102-500	LC1112-500	995	DP41-B, DP41-S, DP25B-S	LBC-012	40	REC-012M	35
1000	455	LC1102-1K	LC1112-1K	995	DP41-B, DP41-S, DP25B-S	LBC-012	40	REC-012M	35
2000	909	LC1102-2K	LC1112-2K	995	DP41-B, DP41-S, DP25B-S	LBC-012	40	REC-012M	35
5000	2269	LC1102-5K	LC1112-5K	1150	DP41-B, DP41-S, DP25B-S	LBC-100	55	REC-100M	95
10,000	4537	LC1102-10K	LC1112-10K	1150	DP41-B, DP41-S, DP25B-S	LBC-100	55	REC-100M	95
15,000	6806	LC1102-15K	LC1112-15K	1150	DP41-B, DP41-S, DP25B-S*	LBC-100	55	REC-100M	95
20,000	9074	LC1102-20K	LC1112-20K	1300	DP41-B, DP41-S, DP25B-S*	LBC-112	70	REC-112M	150
25,000	11,343	LC1102-25K	LC1112-25K	1300	DP41-B, DP41-S, DP25B-S*	LBC-112	70	REC-112M	150
50,000	22,686	LC1102-50K	LC1112-50K	†	DP41-B, DP41-S, DP25B-S*	LBC-200-12	114		
100,000	45,372	LC1102-100K	LC1112-100K	†	DP41-B, DP41-S, DP25B-S*	LBC-300-8	125		

Comes with 5-point NIST-traceable calibration. † Special quote. * 4-digit meter, counts by 10. ** See section D for compatible meters.

To order an FM Hazardous Location model (not available on Dual Bridge Models), add suffix "-FM" to model number and \$150 to price.

To order a dual bridge version, add suffix "-DUAL" to model number. See next page for pricing.

To order unit with integral connector, specify LC1112, no extra charge. PT06F10-6S, mating connector (sold separately), \$26.50.

Ordering Examples: LC1102-100K, 100,000 lb capacity load cell, \$2800.

LC1112-5K, 5000 lb capacity load cell with integral connector, \$1150.

PT06F10-6S, mating connector (sold separately), \$26.50.

LC1102-500-FM, 500 lb capacity FM Hazardous Location rated load cell, \$995 + 150 = \$1145.

LC1102-100-DUAL, dual-output 100 lb capacity load cell, \$995 + 250 = \$1245.


ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
PT06F10-6S	\$26.50	Mating connector for LC1112 series load cells

HIGH-OUTPUT UNIVERSAL CANISTER LOAD CELLS



LC1102-100, \$995, shown smaller than actual size.



SPECIFICATIONS

Output: 3 mV/V $\pm 0.25\%$ FSO
Excitation: 10 Vdc (15V max)
Accuracy Class: $\pm 0.05\%$ FSO
Linearity: $\pm 0.05\%$ FSO
Hysteresis: $\pm 0.02\%$ FSO
Repeatability: $\pm 0.02\%$ FSO
Zero Balance: $\pm 1.0\%$ FSO
Operating Temp Range: -24 to 79°C (-30 to 175°F)
Compensated Temp Range: 16 to 71°C (60 to 160°F)
Thermal Effects:
 Zero: $\pm 0.003\%$ FSO/°C
 Span: $\pm 0.014\%$ rdg/°C
Protection Class: IP67
Safe Overload: 150% of capacity
Ultimate Overload: 300% of capacity
Bridge Resistance: 350 Ω
Full Scale Deflection: 0.08 to 0.13 mm (0.003 to 0.005") typ.
Construction: Stainless steel


Electrical: 4.5 m (15') 4-conductor shielded color-coded cable

Agency Approvals:
 FM/CSA Intrinsically Safe:
 IS/I.II.III/1/CDEFG (standard)

POPULAR OPTIONS

	Price
0 to 5 Vdc Output	"5V" \$175
Overload Stops:	"-OL" Consult Factory
Dual Bridge:	
≤2000 kg	"-DUAL" 250
>2000 kg	"-DUAL" 350
Extended Temperature Range:	
-45 to 93°C (-50 to 200°F)	"-TC1" 50
-45 to 177°C (-50 to 350°F)	"-TC2" 225
Watertight Cable Exit:	"-WTC" 125
Additional Cable Length:	6.50/ft

Note: 100,000 lb capacity load cells are supplied with 2 eyebolts for easy handling.



Dimensions: mm (in)

CAPACITY		A	B	D	E	G	T
50 to 300 lb	23 to 136 kg	89 (3.5)	114 (4.50)	22 (0.87)	6.4 (0.25)	76 (3.00)	3/8-24 UNF x 3/16 DP
500 to 3000 lb	227 to 1361 kg	89 (3.5)	116 (4.56)	38 (1.5)	6.4 (0.25)	32 (1.25)	1/2-20 UNF x 1/2 DP
5000 to 15,000 lb	2269 to 6806 kg	89 (3.5)	151 (5.94)	33 (1.3)	9.7 (0.38)	71 (1.81)	1-14 UNS x 1 1/4 DP
20,000 to 30,000 lb	9074 to 13,612 kg	114 (4.5)	216 (8.5)	58 (2.3)	13 (0.50)	197 (2.81)	1 1/2 UNF x 2.0 DP
50,000 lb	22,686 kg	168 (6.63)	291 (11.44)	71 (2.8)	16 (0.62)	81 (3.19)	2-12 UN x 2% DP
100,000 lb	13,612 kg	219 (8.63)	451 (17.75)	102 (4.0)	29 (1.13)	125 (4.94)	3-8 UN x 4 1/2 DP



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters