

Glass Wire-Wound Pt RTD Elements




Class B (IEC751), Alpha = 0.00385

Glass wire-wound platinum RTD elements are made by winding a platinum wire onto a glass core and then fusing the exterior with glass. They are suitable for low or very high temperatures and are tolerant of thermal shocks.

They offer good vibration resistance (depending on mounting method) and can be immersed (with exception of GX) directly into liquid media.

 **MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)


Dimensions in millimeters (1 mm = 0.03937")	Nominal Resistance (ohms)	Temperature Range, °C (°F)	Model No.	Price	Self-Heating Error in C°/mW Flowing Air V = 1 m/sec	Response Time in Seconds			
						Flowing Water V = 0.4 m/sec		Moving Air V = 1 m/sec	
						50% Response	90% Response	50% Response	90% Response
	1 x 100	0 to 600 (32 to 1110)	1PT100G3045	\$94	0.04	0.7	2.0	12.0	38.0
	1 x 100	0 to 600 (32 to 1110)	1PT100G1730	80	0.11	0.7	2.0	8.0	28.0
	1 x 100	0 to 600 (32 to 1110)	1PT100G1050	128	0.12	0.8	3.0	11.0	34.0








Ordering Examples: 1PT100G1730, 1 x 100 Ω, 0.11 glass wire-wound Pt RTD element, \$80.

1PT100G1050, 100 Ω, 5 D x 10 mm L glass wire-wound RTD, \$128.

The glass wire-wound platinum RTD "GO" Series has a platinum band wound into a solid glass core and homogeneously fused with the exterior glass.

The "GX" Series has one or two platinum bands wound onto a glass tube and protected from the environment by a layer of glaze.



Dimensions in millimeters (1 mm = 0.03937")	Nominal Resistance (ohms)	Temperature Range, °C (°F)	Model No.	Price	Self-Heating Error in C°/mW Flowing Air V = 1 m/sec	Response Time in Seconds			
						Flowing Water V = 0.4 m/sec		Moving Air V = 1 m/sec	
						50% Response	90% Response	50% Response	90% Response
	1 x 100	-220 to 400 (-365 to 750)	1PT100GX0518	\$65	0.36	0.2	0.8	8.0	30.0
	1 x 100	-220 to 400 (-365 to 750)	1PT100GX1013	55	0.39	0.2	0.5	4.0	12.0
	1 x 100	-220 to 400 (-365 to 750)	1PT100GX1510	51	0.36	0.2	0.4	2.0	7.0
	2 x 100	-220 to 400 (-365 to 750)	*2PT100GX1528	98	0.20	0.3	1.0	12.0	45.0
	1 x 100	-220 to 400 (-365 to 750)	1PT100GO1020	52	0.26	0.14	0.35	7.0	21.0
	1 x 100	-220 to 400 (-365 to 750)	1PT100GO1327	65	0.11	0.40	1.30	13.0	25.0
	1 x 100	-220 to 400 (-365 to 750)	1PT100GO1545	50	0.09	0.80	2.40	16.0	40.0

* Dual element.

Ordering Examples: 1PT100GX0518, 1 x 100 Ω glass wire-wound Pt RTD element, \$65.

2PT100GX1528, 2 x 100Ω glass wire-wound element, \$98.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters