

Documenting Multifunction Calibrator

Portable, High Accuracy

CL310
\$2695



- ✓ Highest Accuracy in Class to 0.015% of Reading
- ✓ Measure and Simulate T/Cs (13 Types), RTDs (13 Types), Ω , Current, Voltage, Frequency and Pressure; Source Pulse Trains
- ✓ Pressure Module Communication Port Compatible with OMEGA® Pressure Modules
- ✓ Direct Entry of Custom RTD Coefficients (R0, A, B, C)
- ✓ All Simulate Modes Can be Programmed with Dedicated Setpoints to Speed Calibration and Linearity Tests
- ✓ Store Up to 21 Data Points Per Instrument, and Up to 50 Instruments in Non-Volatile Memory
- ✓ Test for Pass/Fail Criteria
- ✓ Capture Both as Found and as Left Data
- ✓ Software is Included
- ✓ Protective Rubber Boot Standard

The CL310 documenting multi-function calibrator delivers a feature set unmatched in high accuracy, hand-held calibrators in its price range. The CL310 delivers functions and accuracy associated with fixed installation, laboratory instruments, and has everything needed for virtually any calibration task. What makes this versatile calibrator best in class is the ability to fully document any calibration easily while performing the normal job. Software is included. Some functions will require a Microsoft Excel-compatibility.

CL310 can also measure and source thermocouples, RTDs, current, voltage, frequency, and it can source pulse trains. It has a communications port for pressure modules and an isolated mA/V readback circuit. Arrow keys, direct numeric keypad entry, and three software-driven function buttons combine with a large, backlit, menu-driven graphics display to provide a highly intuitive yet powerful interface. A built-in 250 Ω resistor for Hart® compatibility; compatibility with smart transmitters and PLCs, full fuseless protection, and a serial communications port for control using ASCII commands are additional features that make the CL310 indispensable for calibration tasks. This product is battery operated.



CL310, \$2695, shown with protective rubber boot (included).

Measuring Pressure

With a PCL-PMA pressure module adaptor, the CL310 will work with all OMEGA® PCL-PM pressure modules. (For information on these see specifications under PCL1200 visit omega.com/pcl1200).

Specifications (23 \pm 5°C unless otherwise noted)

Voltage:

Source: 0.000 to 20.000 Vdc

Read:

Isolated: 0.000 to 30.000 Vdc

Non-Isolated: 0.000 to 20.000 Vdc

Thermocouple mV:

Read/Source: -10.000 to 75.000 mV

Current (mA):

Source: 0.000 to 24.000 mA

Read:

Isolated: 0.000 to 24.000 mA

Non-Isolated: 0.000 to 24.000 mA

Frequency (1 to 20V Selectable Amplitude):

CPM Source/Read: 2.0 to 600.0 cpm

Hz Source/Read: 1.0 to 1000.0 Hz

kHz Source/Read: 1.0 to 10.00 kHz

Pulse (Source Only 1 to 20V; Selectable Amplitude):

Pulses: 1 to 30,000; 2 cpm to 10 kHz

Ohms:

Source: 5.0 to 4000.0 Ω

Read: 0.00 to 4000.0 Ω

Thermocouple Range Read and Source:

Type J: -200.0 to 1200.0°C (-328 to 2192°F)

Type K: -200.0 to 1370.0°C (-328 to 2498°F)

Type T: -200.0 to 400.0°C (-328 to 752°F)

Type E: -200.0 to 950.0°C (-328 to 1742°F)

Type R: -20.0 to 1750.0°C (-4 to 3182°F)

Type S: -20.0 to 1750.0°C (-4 to 3182°F)

Type B: 600.0 to 1800.0°C (1112 to 3272°F)

Type C: 0 to 2316.0°C (32 to 4201°F)

Type XK: -200.0 to 800.0°C (-328 to 1472°F)

Type BP: 0 to 2500.0°C (32 to 4532°F)

Type L: -200.0 to 900.0°C (-328 to 1652°F)

Type U: -200.0 to 400.0°C (-328 to 752°F)

Type N: -200.0 to 1300.0°C (-328 to 2372°F)

RTD Range Read and Source:

Ni120 (672): -80.0 to 260.0°C (-112 to 500°F)

Pt100 (385): -200.0 to 800.0°C (-328 to 1472°F)

Pt100 (3926): -200.0 to 630.0°C (-328 to 1166°F)

Pt100 (3916): -200.0 to 630.0°C (-328 to 1166°F)

Pt200 (385): -200.0 to 630.0°C (-328 to 1166°F)

Pt500 (385): -200.0 to 630.0°C (-328 to 1166°F)

Pt1000 (385): -200.0 to 630.0°C (-328 to 1166°F)

Cu10: -100.0 to 260.0°C (-148 to 500°F)

YSI400: 15.00 to 50.00°C (59 to 122°F)

Cu50: -180.0 to 200.0°C (-292 to 392°F)

Cu100: -180.0 to 200.0°C (-292 to 392°F)

Pt385-10: -200.0 to 800.0°C (-328 to 1472°F)

Pt385-50: -200.0 to 800.0°C (-328 to 1472°F)

Accuracy

Voltage: ±0.015% of reading, ±2 mV

Thermocouple: mV ±0.02% of reading, ±10 μV

Thermocouple Errors (Typical at 100°C)

(In °C; Add 0.2 for Cold-Junction Compensation Error)

Type J: 0.2°C (0.4°F) Type K: 0.3°C (0.5°F)

Type T: 0.2°C (0.4°F) Type B: 1.2°C (2.2°F)

Type S: 1.2°C (2.2°F) Type XK: 0.2°C (0.4°F)

Type C: 0.6°C (1.6°F) Type L: 0.2°C (0.4°F)

Type BP: 0.9°C (34°F) Type N: 0.4°C (0.7°F)

Type U: 0.25°C (0.5°F)

RTD Read/Source:

Ni120 (672): 0.06°C (0.11°F) Pt100 (385): 0.13°C (0.23°F)

Pt100 (3926): 0.13°C (0.23°F) Pt100 (3916): 0.13°C (0.23°F)

Pt200 (385): 0.45°C (0.81°F) Pt500 (385): 0.21°C (0.38°F)

Pt1000 (385): 0.14°C (0.75°F) Cu10: 0.82°C (1.48°F)

YSI400: 0.05°C (0.09°F) Cu50: 0.20°C (0.36°F)

Cu100: 0.13°C (0.23°F) Pt385-10: 0.84°C (2.16°F)

Pt385-50: 0.21°C (0.38°F)

Read/Source:

Current (mA): ±0.015% of reading, ±2 μA/±0.015% of reading, ±2 μA

CPM: ±0.05% of reading, ±0.1

Hz: ±0.05% of reading, ±0.1 Hz

kHz: 1 to 10 kHz/±0.250% of reading

Ohms (Works with All Pulsed Transmitters Down to 5 ms):

5 to 400 Ohms Range: ±0.015% of reading ±0.03 Ω/

±0.015% of reading ±0.1 Ω

400 to 1500 Ohms Range: ±0.015% of reading ±0.3 Ω

1500 to 4000 Ohms Range: ±0.015% of reading ±0.3 Ω

**Environmental**

Operating Temperature: -10 to 50°C (14 to 122°F)

Storage Temperature: -20 to 70°C (-4 to 158°F)

Stability: ±0.005% of reading/°C (outside of 23°C ±5°C)

Power Requirement: 6 Vdc

Batteries: 4 "AA" alkaline (included) or optional rechargeable

Mechanical

Dimensions: 220.9 H x 106.6 W x 58.4 mm D (8.7 x 4.2 x 2.3")

Weight: 863 g (30.5 oz)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!**To Order (Specify Model Number)**

Model No.	Price	Description
CL310	\$2695	Documenting multifunction calibrator

Accessories

Model No.	Price	Description
PCL-PMA	\$310	Pressure module adaptor
DPG4000-C32	30	RS232 cable with miniature plug
PCL422-TL	17	1.2 m (48") stackable test leads
CL20-KIT-2	90	Thermocouple test lead kit
PCL-ACA	45	AC adaptor/charger 120 Vac

Comes complete with instruction manual, test leads, protective rubber boot, nylon carrying case, RS232 cable, USB adaptor cable, Type K thermocouple, Type K cable, NIST calibration certificate, software CD and 4 "AA" alkaline batteries.

Ordering Examples: CL310, high accuracy multifunction calibrator, and CL20-KIT-2, thermocouple test lead kit, \$2695 + 90 = **\$2785.**

CL310, high accuracy multifunction calibrator, and PLC-ACA AC adaptor, \$2695 + 45 = **\$2740.** OCW-1, OMEGACARESM extends standard 1-year warranty to a total of 2 years (**\$150**) \$2740 + 150 = **\$2890.**

Recommended Reference Book: Instrumentation Fundamentals for Process Control, ME-1805, \$155. Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters