

MILLIAMP LOOP CALIBRATORS

CL530 Series

Starts at
\$725



Standard

- ✓ Sources, Measures, Simulates, and Reads All 4 to 20 mA Process Loop Functions
- ✓ Large, High-Contrast Display with Bar Graph
- ✓ Checks 4 and 20 mA Span Limits
- ✓ One-Handed Operation
- ✓ Automatic Stepping and Ramping
- ✓ Hart® Compatible
- ✓ Displays mA or %
- ✓ 0.012% Rdg Accuracy
- ✓ Rugged Carrying Case

The CL530 builds on OMEGA's 30 years of calibration experience. The user can check, calibrate, and troubleshoot 4 to 20 mA process control loops with this easy-to-use instrument.

The CL532 has all the features of the CL530, plus it will read up to 30 Vdc and source up to 24 Vdc.

SPECIFICATIONS

Accuracy: $\pm 0.012\%$ rdg + 0.004 mA

Temperature Effect: ± 50 ppm/ $^{\circ}$ C

Operating Temperature Range: -20 to 60 $^{\circ}$ C (-5 to 140 $^{\circ}$ F)

Storage Temperature Range: -30 to 60 $^{\circ}$ C (-22 to 140 $^{\circ}$ F)

Relative Humidity Range: 10% \leq RH \leq 90% [0 to 35 $^{\circ}$ C (32 to 95 $^{\circ}$ F)], non-condensing; 10% \leq RH \leq 70% [35 to 60 $^{\circ}$ C (95 to 140 $^{\circ}$ F)], non-condensing

Overvoltage Protection: 120 Vrms for 30 seconds, 240 Vrms for 15 seconds

Overload Protection: 24 mA nominal

Battery: 9V, alkaline (included)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Battery Life:

Source Mode: ≥ 18 hours at 12 mA (Hart® disabled)

Power Measure: 10 hours, read, 2 W limit sim.

Read Vdc: > 40 hours

Loop Drive Ability: 1200 Ω at 20 mA for life of battery

Loop Burden: $< 2V$ at 20 mA

Loop Supply Limits (2 W Limit Sim.): 2 to 60 Vdc

Connection: Alligator test leads attached, 610 mm (24") long

Dimensions: 84 W x 180 H x 56 mm D (3.3 x 7.1 x 2.2")

Weight: 326 g (11.5 oz)

Source Current: Source 0 to 24 mA or -25 to 125% into $\leq 1200 \Omega$; a flashing HIGH Ω indicator appears if improperly connected

2-Wire Transmitter Simulate:

Adjust loop current from 0 to 24 mA or -25 to 125% when powered by an external supply; LOW SUPPLY flashes to indicate a misconnection

Power Measure: Power the loop and read 0 to 24 mA or -25 to 125%; CURRENT LIMITED flashes at > 24 mA, protecting devices in the loop

Read Current: Read 0 to 24 mA or -25 to 125%; CURRENT LIMITED flashes at > 24 mA, protecting devices in the loop

Read DC Voltage: Read 0 to 60 Vdc with 2x overrange ability and flashing OVERRANGE indicator

CL530, \$725, shown smaller than actual size. Test leads, wrist strap and 9V battery included.



EZ-Check Switch: Gives instant access to 4 and 20 mA or other user-set span limits; in read modes, the EZ-Check switch provides a max/min log of reading

EZ-Step Button: Allows one-handed stepping up and down the span in 6 different step sizes

EZ-Dial Knob: Adjusts output by 0.001 mA (0.01%); push and turn for 100x faster adjustment—by 0.100 mA (1.00%)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
CL530	\$725	Milliamp loop calibrator
CL532	995	Milliamp/voltage calibrator

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
CL530-ADAPTOR	\$65	110 AC adaptor
CL530-ADAPTOR-220	65	220 AC adaptor
SC-530	65	Rugged carrying case

The CL530 and CL532 comes complete with test leads, operator's manual, 9V alkaline battery and NIST calibration certificate.

Ordering Example: CL530, milliamp loop calibrator, \$725. OCV-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years, \$130, \$725 + 130 = \$855.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters