

¼ DIN Economical 6-Zone PID Temperature Controllers

Panel punches
available, visit
[omega.com/
panelpunches](http://omega.com/panelpunches)

CN616 Series
\$620
All Models



- ✓ 6-Loop PID Controller
- ✓ Autotune or Manual Tuning
- ✓ Heat or Cool Control
- ✓ 20-Segment Ramp/Soak Profile Per Zone
- ✓ Password Protected
- ✓ User Programmable
- ✓ RS232 Digital Communications Standard
- ✓ Front Panel Calibration
- ✓ High, Low or High/Low Alarm, Latching or Non-Latching
- ✓ Programmable Thermocouple Types J, K, T, R, S, E, B, or C
- ✓ ¼ DIN Aluminum Case



CN616TC1, \$620, shown smaller than actual size.



The CN616 Series is a highly versatile 6-loop microprocessor-based controller designed for easy front panel or remote setup and operation. Each of 6 zones is sequentially scanned, and active zones are displayed. Individual zones can be locked for monitoring. Each instrument is programmable to meet operator needs for: thermocouple type, temperature units; high, low or high/low alarm configured as latching or non-latching; and autotune with manual trim or manual PID setting. The zone display scan time and ramp/soak can be set by the operator. Parameters and setpoints are retained when power is turned off. Password protection is provided to prevent accidental changes to

calibration, PID setting and ramp/soak profile. If power loss occurs, the controller retains all the latest parameters and returns to "RUN" mode.

All CN616 controllers have RS232 3-wire serial communications. The RS232 program is capable of monitoring up to 10 daisy-chained units.

Line voltage is 120 Vac or 240 Vac selectable by external jumper assembly. Connections are made to the back of the instrument through easy-to-use screw terminal plugs.

The CN616 Series implements a security password to protect settings. The password can be enabled or disabled on the front panel and changed via RS232. Calibration is performed via the front panel and is separately password protected. Higher level

passwords are available.

The instrument is housed in a ¼ DIN aluminum box which does not have to be removed for mounting. The unit mounts in a ¼ DIN panel cutout and is secured by slide brackets. The device is controlled via 6 DC pulse outputs (1 for each zone).

A single output relay is provided to indicate an alarm condition on any zone. The instrument shows an alarm condition by flashing the main temperature display while indicating the zone in alarm with a flashing zone number display. When set to non-latching, the alarm automatically resets when the condition changes. The alarm must be manually reset in the latching setting.

The controller functions in 2 modes— "RUN", the basic operating mode, and "FUNCTION SELECT", the password protected settings selection and control mode.

Specifications

Number of Loops: 6

Accuracy: ±0.1% of max range

Resolution: ±1°C or °F

Temperature Units: °C or °F

Thermocouple Input:

Selectable J, K, E, T, S, R, B or C

PID: Autotune or manual

Password Protection: Calibration and PID changes

Profiling: Ramp/soak,
20 segments/loop

Loop Configuration: Heat or cool

Control Output: 6 DC pulse outputs
(1 per zone); designed to drive
3 to 32 Vdc input solid-state relays

Control Output Voltage:

5 Vdc at 10 mA per loop

Alarms Rating: 5 A @ 120 Vac

Alarms Selectable: High, low, or
high/low; latching or non-latching single
relay for 6 loops

Zone in Alarm: Flashing

Latch Reset: Manual

RS232 Communications: Single-drop
daisy-chain up to 10 controllers

Baud Rate: 4800

Data Bits: 8

Parity: N

Stop: 1

Protocols:

ASCII line computer interface

Communication Software: Windows
compatible, written in Visual Basic


Terminals: Headers for plug-in wiring

Enclosure: ¼ DIN aluminum,
152 mm (6") L



Power Loss: Controller retains
the last setting

Display: 14 mm (0.56") LED, 4-digit

*OMEGACARESM extended warranty program
is available for models shown on this page.
Ask your sales representative for full details
when placing an order. OMEGACARESM
covers parts, labor, and equivalent loaners.*



CN606 Series companion scanner,
\$590, also available. See page M-85.



Software Configuration Screen

Input Types and Ranges

Thermocouple Input Type	Standard Range CN616 (TC1)	Extended Range CN616 (TC2)
B Pt/30% Rh-Pt/6% Rh	0 to 1800°C 32 to 3300°F	—
C W/5% Re-W/26% Re	0 to 2300°C 32 to 4200°F	—
E CHROME SM -Constantan	0 to 550°C 32 to 1000°F	0 to 900°C 32 to 1652°F
J Iron-Constantan	0 to 700°C 32 to 1300°F	—
K CHROME SM -ALOMEGA SM	0 to 1000°C 32 to 1800°F	0 to 1800°C 32 to 2282°F
R Pt/13% Rh-Pt	0 to 1750°C 32 to 3200°F	—
S Pt/10% Rh-Pt	0 to 1750°C 32 to 3200°F	—
T Copper-Constantan	0 to 400°C 32 to 750°F	—

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CN616TC1	\$620	6-zone thermocouple input controller
CN616TC2	620	6-zone thermocouple input controller with extended range
DPP-6	575	¼ DIN panel punch

Comes complete with software and operator's manual.

Ordering Example: CN616TC1, 6-loop temperature controller with 20-segment ramp and soak on each loop and RS232 communications, \$620.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$155), \$620 + 155 = \$775.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters