

1- or 2-Channel Circular Recorder/Controllers

CT8100
Starts at
\$1272



- ✓ 305 mm (12") Chart
- ✓ 1- or 2-Pen Versions
- ✓ Programmable Inputs:
Thermocouple, RTD,
DC Current or Voltage
- ✓ Control Outputs
- ✓ 4-Digit, 14 mm (0.56") High
Display per Pen



CT8110, \$1514,
shown smaller
than actual size.

The CT8000 Series circular chart recorder/controllers measure, display, and control up to 2 process variables. Choose from a variety of programmable inputs. All recorder, control, and alarm functions are easily configured via the front keypad. The user can choose 1 of 2 alarm settings for each pen. RS485 communications and NEMA 4X (IP66) are also available. Control outputs include SSR driver, 4 to 20 mA, and relays. With the 4 to 20 mA option, the user can retransmit the process value.

Specifications

Inputs

Input Types/Range:

Thermocouple: J, K, T, R, S, E, B, N, C

RTD: 100 Ω Platinum, 0.00385 $\Omega/\Omega/^\circ\text{C}$

DC Current: 0 to 20 mA, 4 to 20 mA.
external shunt resistor, 2.5 Ω or 250 Ω
(not included)

DC Voltage: 0 to 25 mV, 0 to 50 mV,
10 to 50 mV, 0 to 5 V, 1 to 5 V

Impedance: >100 M Ω for T/C and mV
inputs; 100 k Ω for 5 V inputs; 2.5 Ω or
250 Ω for mA inputs

RTD Excitation Current:

330 μA , typical

Input Scan Rate: 1 scan per second

Input Correction:

Offset adjustment -999 to 999 units

Remote Setpoint: 0 to 5 V, 1 to 5 V

Sensor Fault Detection:

Sensor break on all T/Cs,
RTDs, 1 V, 1 to 5 V, 4 to 20 mA, and
millivolt inputs. No sensor break can
be detected for zero-based volt and milliamp
ranges. Display goes to
"SnSr" and pen goes up-scale if a
sensor break is detected.

Display goes to "Hi" 5% above span;
display goes to "Lo" 5% below scan.

Transmitter Power Supplies:

One isolated 50 mA @ 24 Vdc
supply available

Input Performance

Performance Under

Reference Conditions:

Measurement Error:

Type J, K, T, E, N, C T/Cs and RTDs:
 $\pm 0.25\%$ of span ± 1 degree.

Type R, S, B, C T/Cs: $\pm 0.25\%$ of span
@ 25 $^\circ\text{C}$ (77 $^\circ\text{F}$) mVdc and Vdc; $\pm 0.25\%$
of scaled span plus 1 least-significant digit

Cold-Junction

Compensation Error:

$\pm 0.2^\circ\text{C}$ (0.36 $^\circ\text{F}$) @ 25 $^\circ\text{C}$ (77 $^\circ\text{F}$)

Cold-Junction

Compensation Rejection:

0.04 $^\circ\text{C}$ (0.07 $^\circ\text{F}$) deviation
from 25 $^\circ\text{C}$ (77 $^\circ\text{F}$)

Linearization Error:

T/Cs: $\pm 0.25^\circ\text{C}$ (0.45 $^\circ\text{F}$) typical,
 $\pm 0.5^\circ\text{C}$ (0.9 $^\circ\text{F}$) worst case

RTDs: $\pm 0.1^\circ\text{C}$ (0.18 $^\circ\text{F}$) typical,
 $\pm 0.3^\circ\text{C}$ (54 $^\circ\text{F}$) worst case

Ambient Temperature Error:

$\pm 0.01\%$ of span per $^\circ\text{C}$ (1.8 $^\circ\text{F}$)
deviation from 25 $^\circ\text{C}$ (77 $^\circ\text{F}$)

Common-Mode Rejection:

90 dB minimum; 24 Vac maximum for
RTD input; 115 Vac maximum all others

Normal-Mode Rejection:

85 dB minimum @ 60 Hz or greater
isolation:

RTD inputs 24 Vac; all other inputs
115 Vac; inputs share a common
signal ground

Reference Conditions

Ambient Temperature: 25 $^\circ\text{C}$ (77 $^\circ\text{F}$)

Relative Humidity: 60 to 70%

Recording

Pen Type: Disposable fiber tip

Pen Color: Pen 1—red; pen 2—green

Chart Size: 305 mm (12")

Chart Drive: Stepper motor

Chart Rotation: User configurable:

0.1 to 999 hours in 0.1-hour increments
Chart Span: Bottom and top of span,
-9999 to 9999 units

Filtering: 1 to 20 scans averaging
(affects display and recording)

Recording Performance

Chart Resolution Accuracy:

0.5% of chart span reference accuracy

Resolution: 0.15% of chart span

Deadband: 0.3% of chart span

Response Time:

20 seconds for full scale travel

Chart Rotation Accuracy:

$\pm 0.5\%$ of rotation time, assuming all
backlash removed

Operator Interface

Display: 4-digit, 0.56" (14 mm) high,
red, 7-segment, LED display

Resolution:

T/C and RTD: 0.1 and 1 $^\circ$

mV, V and mA: 0.001, 0.01, 0.1 and 1 unit

Status Indicators:

Recorders: ALRM1 and ALRM2; red LEDs.

Controllers: MAN, OUT1, OUT2, ALRM;
yellow and red LEDs

Keypad: 3 keys for programming and unit
operation; 1 or 2 auto/manual keys on
controllers

Display Modes:

Recorders: Process value(s)

Controllers: Process value(s) or
deviation(s), with or without setpoint
sequentially

Alarms

Number: Up to 2 process alarms for each of 2 inputs

Type:

Recorder: Process high or low.

Controllers: Process, deviation, or band

Hysteresis: Fully adjustable, 0 to 300 units, straddles alarm point

Security: Alarm setpoint changes can be prohibited

Sensor Fault Action: Alarms work normally in "HI" and "LO" conditions; alarm relays are de-energized in a "SnSr" sensor break condition

ON/OFF Outputs

On/Off Outputs:

Assignable to alarm or control outputs

Relays: SPDT; contacts rated 5 A resistive @ 115 Vac, 2.5 A resistive @ 230 Vac, 1/2 hp at 230 Vac (single phase), 250 VA @ 115/230 Vac

Solid State Relay Driver:

Open-collector output; can provide 40 mA at 3 Vdc or 20 mA at 4 Vdc; short circuit current is limited to 100 mA

Current Output

Drivers: Assignable to process value or setpoint retransmission or control outputs

Output Span:

0 to 20 mA or 4 to 20 mA, nominal

Resolution: 0.02% of 20 mA;

12 bits over a 0 to 25.6 mA span

Accuracy: ±0.1% to 20 mA

span reference accuracy

Compliance: 650 Ω load

Power Requirements

Line Voltage: 115/230 Vac, ±10%,

50/60 Hz (230 Vac is optional)

Power Consumption: 25 VA max

Construction

Enclosure: Gasketed cover, case and windows; structural foam case and cover with plastic or glass window area; door lock available

NEMA Rating: NEMA 3 (IP54) standard

Conduit Openings: 4 openings standard, 2 additional as required

Mounting:

Panel or wall, or optional pipe mounting

Overall Dimensions:

358.65 W x 425.96 H x 196.85 mm D (14.12 x 16.77 x 7.75")

Panel Cutout: 322.58 W x 322.58 mm H (12.7 x 12.7")

Panel Depth: 133.35 mm (5.25")

Panel Protrusion: 63.5 mm (2.5")

Weight: 9 kg (20 lb) max

Environmental and Operating Conditions

Operating Temperature:

0 to 55°C (32 to 131°F)

Storage Temperature:

-40 to 65°C (-4 to 149°F)

Humidity:

10 to 90% RH, non-condensing

Digital Communications

Communications Port: RS485 serial

communications, half-duplex

Bit Rate: 9600, 4800, 2400,

1200, 600, 300 baud

Configuration:

Monitor: Read only.

Normal: Read and write

Address: User configurable;

0 to 99 for each pen

General Reference Data

Data Backup:

Battery-backed SRAM for all data

Battery Backup:

5 years minimum life, 10 years typically

Approvals and Compliance

Safety: UL approved for USA: UL 1092,

UL 916 and QUXY, pending, UL certified for

Canada: CSA Spec 142, pending

Thermocouple Ranges

Sensor Type	Sensor Specs	Code	Reference Range °C	Reference Range °F
TC	Iron-constantan	J	0 to 760	0 to 1400
	CHROMEGA®-ALOMEGA®	K	0 to 1360	0 to 2500
	Copper-constantan	T	-200 to 400	-330 to 750
	Platinum 13% rhodium-platinum	R	200 to 1650	400 to 3000
	Platinum 10% rhodium-platinum	S	200 to 1650	400 to 3000
	CHROMEGA®-constantan	E	0 to 750	0 to 1400
	Platinum 30% rhodium-platinum 6% rhodium	B	200 to 1800	400 to 3300
	OMEGA-P®-OMEGA-N® (nicosil-nisil)	N	0 to 1300	0 to 2370
	Tungsten 5% rhenium-tungsten 26% rhenium Pt100	C	200 to 2300	390 to 4170
RTD	100 Ω 0.00.385	Pt100	-140 to 400	-220 to 750

 **MOST POPULAR MODELS HIGHLIGHTED!**

Remember to Order Extra Paper and Pens!

To Order (Specify Model Number)

Model No.	Price	Description
CT8100	\$1272	1-pen circular recorder
CT8101	1321	1-pen circular recorder with 1 relay
CT8100-MA1	1395	1-pen circular recorder with one 4 to 20 mA output
CT8110	1514	2-pen circular recorder
CT8112	1722	2-pen circular recorder with 2 relays
CT8201	1588	1-pen circular recorder/controller with 1 relay
CT8202	1637	1-pen circular recorder/controller with 2 relays
CT8200-D1	1583	1-pen circular recorder/controller with 1 SSR driver
CT8200-MA1	1669	1-pen circular recorder/controller with one 4 to 20 mA output
CT8222	2211	2-pen circular recorder/controller with 2 relays
CT8220-D2	2201	2-pen circular recorder/controller with 2 SSR drivers
CT8220-MA2	2329	2-pen circular recorder/controller with two 4 to 20 mA outputs

Comes complete with package of charts, 1 pen per channel and operator's manual.

For RS485 communications, add suffix "-RST" to model number and add \$200

to price. For 230 Vac option, add suffix "-230V" to model number and add \$65 to price.

For glass window NEMA 4X, add suffix "-4X" to model number and add \$150 to price.

For transmitter power supply, add "-XPS" to model number and add \$125 to price.

Ordering Examples: CT8100, 1-pen circular recorder, CT8000C-0-100/24, 100 sheets of chart paper, \$1272 + 21 = \$1293. CT8112, 2-pen circular recorder with 2 relays, \$1722.

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OCW-1 OMEGACARESM extends standard 2-year warranty to a total of 3 years (\$130).

Accessories

Model No.	Price	Description
CT7000-GREEN	\$25	Green pens, pkg. of 5
CT7000-RED	25	Red pens, pkg. of 5
CT8000C-0-100/24	21	Circular paper, 100 qty. 24-hour
CT8000C-0-100/7	21	Circular paper, 100 qty. 7-day
CT8000C-0-300/24	21	Circular paper, 100 qty. 24-hour
CT8000C-0-300/7	21	Circular paper, 100 qty. 7-day
CT8000C-0-500/24	21	Circular paper, 100 qty. 24-hour
CT8000C-0-800/24	21	Circular paper, 100 qty. 24-hour
CT8000C-0-1000/24	21	Circular paper, 100 qty. 24-hour
MS-1301	125	Reference Book: Assembly Automation and Product Design

Other ranges available; consult factory for details.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters