


Heater Hookup Wire

Technical Data

Additional Heater Hook-Up Wire Available. Visit omega.com/heatwire



Current Carrying Capacity Base Temperature at 40°C (104°F) (Values tabulated are in Amperes)						
Wire Gage, AWG	Conductor Type					
	200°C (390°F)	250°C (480°F)	250°C (480°F)	250°C (480°F)	450°C (840°F)	450°C (840°F)
	tc, npc	npc-7%	A-nickel	npi	npc-27%	A-nickel
24	7.2	8.0	4.0	3.3	9.0	4.3
22	9.6	10.8	5.0	4.4	12.0	5.6
20	14.0	15.0	7.0	6.0	18.0	8.0
18	18.0	20.0	9.4	8.0	23.0	11.0
16	24.0	26.0	12.0	11.0	30.0	14.0
14	36.0	39.0	18.0	16.0	45.0	21.0
12	45.0	49.0	23.0	20.0	56.0	26.0
10	60.0	66.0	31.0	27.0	75.0	35.0
8	83.0	91.0			104.0	49.0
6	110.0	121.0			138.0	65.0

The use of this table for establishing ampacity ratings is an inexact procedure. This table should only be used as a starting point when establishing ratings for any given situation. Values may be lesser or greater than those given in the table because of the influence of installation method, environment, number of conductors, conductor composition and size, ambient temperatures, insulation types, etc. It is recommended that design engineers desiring accurate ampacity data closely study the 1990 National Electrical Code Handbook Article 310-15-310-84. Additional information can be derived from AIEE, paper number 57-660, "The calculation of the temperature rise and load capability of cable systems" by J. H. Neher and M. H. McGrath. This paper was presented to the AIEE general meeting in Montreal, Quebec, Canada on June 24-28, 1956 and was published in the "AIEE transactions," part 3 (power apparatus and systems), Volume 76, October, 1957, pp. 752-772.

Conductor Types:

- tc = tinned copper
- npc = nickel plated copper
- npi = nickel plated iron
- A-nickel = Type "A" 100% nickel

Temperature Correction Factors For ambient temperatures other than 40°C (100°F), multiply the ampacities shown above by the appropriate factor shown below				
Ambient Temperature		Wire Temperature Rating		
°C	°F	200°C (390°F)	250°C (480°F)	450°C (840°F)
41 to 50	106 to 122	0.97	0.98	0.99
51 to 60	124 to 140	0.94	0.95	0.99
61 to 70	142 to 158	0.90	0.93	0.96
71 to 80	160 to 176	0.87	0.90	0.95
81 to 90	177 to 194	0.83	0.87	0.93
91 to 100	195 to 212	0.72	0.85	0.92
101 to 120	213 to 248	0.71	0.79	0.89
121 to 140	249 to 284	0.61	0.71	0.86
141 to 160	285 to 320	0.50	0.65	0.84
161 to 180	321 to 356	0.35	0.58	0.81
181 to 200	357 to 392	-	0.49	0.78
201 to 225	393 to 437	-	0.35	0.74
226 to 250	439 to 482	-	-	0.69
251 to 275	483 to 527	-	-	0.65
276 to 300	528 to 572	-	-	0.60
301 to 325	573 to 617	-	-	0.55
326 to 350	618 to 662	-	-	0.49
351 to 375	663 to 707	-	-	0.42
376 to 400	708 to 752	-	-	0.34

Example: The current carrying capacity (ampacity) rating of a 16 AWG 200°C npc conductor at 40°C is 24.0 A.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters