


# Utility Thermocouple Handle Probes 304 SS or Inconel® Sheath



Available as  
See page A-43 to A-48.




Shown smaller than actual size

## Handle Is Permanently Molded to Probe Sheath, Includes Cable and Miniature Connector

0.3 m (1') Retractable Cable Expands to 1.5 m (5')

Starts at  
**\$33**

- ✓ Molded Handle Rated to 220°C (425°F)
- ✓ Retractable Cable with Superior Memory Expands to 1.5 m (5')
- ✓ Subminiature Connector for Use with Handheld Thermometers
- ✓ 300, 450 and 600 mm (12, 18 and 24") Lengths Standard— Custom Lengths Available
- ✓ Companion RTD Probe, Type PR-16 (see Section C)
- ✓ 304, 310, 316, 321 SS, Inconel and Super OMEGA CLAD® XL Sheaths




**MOST POPULAR MODELS HIGHLIGHTED!**

Thermocouple Alloy	Sheath Dia. mm (in.)	Model No. 300mm (12") Length	Price		Model No. 450mm (18") Length	Price		Model No. 600mm (24") Length	Price		Price/Add'l 300m (Ft.)
			G/E*	U*		G/E*	U*		G/E*	U*	
Iron-Constantan Inconel Sheath <b>J</b>	1.5 (1/16)	JHIN-116(*)-RSC-12	\$33	\$40	JHIN-116(*)-RSC-18	\$33.80	\$40.80	JHIN-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	JHIN-18(*)-RSC-12	34	41	JHIN-18(*)-RSC-18	35.60	42.60	JHIN-18(*)-RSC-24	37.15	44.15	3.15
	4.5 (3/16)	JHIN-316(*)-RSC-12	36	39	JHIN-316(*)-RSC-18	38.20	41.20	JHIN-316(*)-RSC-24	40.35	43.35	4.35
	6.0 (1/4)	JHIN-14(*)-RSC-12	38	41	JHIN-14(*)-RSC-18	41.80	44.80	JHIN-14(*)-RSC-24	45.50	48.50	7.50
Iron-Constantan 304 SS Sheath <b>J</b>	1.5 (1/16)	JHSS-116(*)-RSC-12	\$33	\$40	JHSS-116(*)-RSC-18	\$33.80	\$40.80	JHSS-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	JHSS-18(*)-RSC-12	34	41	JHSS-18(*)-RSC-18	34.90	41.90	JHSS-18(*)-RSC-24	35.85	42.85	1.85
	4.5 (3/16)	JHSS-316(*)-RSC-12	36	39	JHSS-316(*)-RSC-18	37.60	40.60	JHSS-316(*)-RSC-24	39.15	42.15	3.15
	6.0 (1/4)	JHSS-14(*)-RSC-12	38	41	JHSS-14(*)-RSC-18	40.50	43.50	JHSS-14(*)-RSC-24	43.00	46.00	5.00
CHROMEGA®-ALOMEGA®** Inconel Sheath <b>K</b>	1.5 (1/16)	KHIN-116(*)-RSC-12	\$33	\$40	KHIN-116(*)-RSC-18	\$33.80	\$40.80	KHIN-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	KHIN-18(*)-RSC-12	34	41	KHIN-18(*)-RSC-18	35.60	42.60	KHIN-18(*)-RSC-24	37.15	44.15	3.15
	4.5 (3/16)	KHIN-316(*)-RSC-12	36	39	KHIN-316(*)-RSC-18	38.20	41.20	KHIN-316(*)-RSC-24	40.35	43.35	4.35
	6.0 (1/4)	KHIN-14(*)-RSC-12	38	41	KHIN-14(*)-RSC-18	41.80	44.80	KHIN-14(*)-RSC-24	45.50	48.50	7.50
CHROMEGA®-ALOMEGA®** 304 SS Sheath <b>K</b>	1.5 (1/16)	KHSS-116(*)-RSC-12	\$33	\$40	KHSS-116(*)-RSC-18	\$33.80	\$40.80	KHSS-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	KHSS-18(*)-RSC-12	34	41	KHSS-18(*)-RSC-18	34.90	41.90	KHSS-18(*)-RSC-24	35.85	42.85	1.85
	4.5 (3/16)	KHSS-316(*)-RSC-12	36	39	KHSS-316(*)-RSC-18	37.60	40.60	KHSS-316(*)-RSC-24	39.15	42.15	3.15
	6.0 (1/4)	KHSS-14(*)-RSC-12	38	41	KHSS-14(*)-RSC-18	40.50	43.50	KHSS-14(*)-RSC-24	43.00	46.00	5.00
CHROMEGA®-Constantan Inconel Sheath <b>E</b>	1.5 (1/16)	EHIN-116(*)-RSC-12	\$33	\$40	EHIN-116(*)-RSC-18	\$33.90	\$40.90	EHIN-116(*)-RSC-24	\$34.85	\$41.85	\$1.85
	3.0 (1/8)	EHIN-18(*)-RSC-12	34	41	EHIN-18(*)-RSC-18	35.90	42.90	EHIN-18(*)-RSC-24	37.75	44.75	3.75
	4.5 (3/16)	EHIN-316(*)-RSC-12	36	39	EHIN-316(*)-RSC-18	38.50	41.50	EHIN-316(*)-RSC-24	41.00	44.00	5.00
	6.0 (1/4)	EHIN-14(*)-RSC-12	38	41	EHIN-14(*)-RSC-18	41.80	44.80	EHIN-14(*)-RSC-24	45.50	48.50	7.50
CHROMEGA®-Constantan 304 SS Sheath <b>E</b>	1.5 (1/16)	EHSS-116(*)-RSC-12	\$33	\$40	EHSS-116(*)-RSC-18	\$33.80	\$40.80	EHSS-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	EHSS-18(*)-RSC-12	34	41	EHSS-18(*)-RSC-18	35.30	42.30	EHSS-18(*)-RSC-24	36.50	43.50	2.50
	4.5 (3/16)	EHSS-316(*)-RSC-12	36	39	EHSS-316(*)-RSC-18	37.60	40.60	EHSS-316(*)-RSC-24	39.15	42.15	3.15
	6.0 (1/4)	EHSS-14(*)-RSC-12	38	41	EHSS-14(*)-RSC-18	40.50	43.50	EHSS-14(*)-RSC-24	43.00	46.00	5.00
Copper-Constantan Inconel Sheath <b>T</b>	1.5 (1/16)	THIN-116(*)-RSC-12	\$33	\$40	THIN-116(*)-RSC-18	\$33.90	\$40.90	THIN-116(*)-RSC-24	\$34.85	\$41.85	\$1.85
	3.0 (1/8)	THIN-18(*)-RSC-12	34	41	THIN-18(*)-RSC-18	35.90	42.90	THIN-18(*)-RSC-24	37.75	44.75	3.75
	4.5 (3/16)	THIN-316(*)-RSC-12	36	39	THIN-316(*)-RSC-18	38.50	41.50	THIN-316(*)-RSC-24	41.00	44.00	5.00
	6.0 (1/4)	THIN-14(*)-RSC-12	38	41	THIN-14(*)-RSC-18	41.80	44.80	THIN-14(*)-RSC-24	45.50	48.50	7.50
Copper-Constantan 304 SS Sheath <b>T</b>	1.5 (1/16)	THSS-116(*)-RSC-12	\$33	\$40	THSS-116(*)-RSC-18	\$33.80	\$40.80	THSS-116(*)-RSC-24	\$34.55	\$41.55	\$1.55
	3.0 (1/8)	THSS-18(*)-RSC-12	34	41	THSS-18(*)-RSC-18	35.30	42.30	THSS-18(*)-RSC-24	36.50	43.50	2.50
	4.5 (3/16)	THSS-316(*)-RSC-12	36	39	THSS-316(*)-RSC-18	37.60	40.60	THSS-316(*)-RSC-24	39.15	42.15	3.15
	6.0 (1/4)	THSS-14(*)-RSC-12	38	41	THSS-14(*)-RSC-18	40.50	43.50	THSS-14(*)-RSC-24	43.00	46.00	5.00

\* Specify junction type: **E** (Exposed), **G** (Grounded), **U** (Ungrounded) or **S** (Surface). **Note:** PFA Coating is available, with a handle that is not molded in place. Order standard part number with a suffix "-PFA". Price: add \$20 to 300 mm (12") probes, \$25 to 450 mm (18") probes and \$30 to 600 mm (24") probes. 200°C (400°F) max.

\*\* For highest temperature and stability rating, change "SS" or "IN" to "XL" and add \$3 to price.

**Ordering Examples:** KHSS-18G-RSC-12, Type K, 3.0 mm (1/8") grounded junction, 300 mm (12") long, 304 stainless steel sheath, \$34  
For additional lengths, consult sales. To Order 310, 316, or 321 stainless steel sheath, change the "SS" in the model number to "310SS, 316SS, or 321SS"; no additional charge. KHXL-14G-RSC-12, Super OMEGA CLAD® XL Type K, 6 mm (1/4") grounded junction, 300 mm (12") long, 321 stainless steel sheath, \$38 + 3 = \$41.



### Retractable Cord

0.3 m (1') retractable cable expands to 1.5 m (5') Standard miniature connector mates with all handheld thermometers for convenient hook-up.

Thermocouple Probes with Built-In USB Available, See Page A-86

Discount Schedule	
1-10 Units	Net
11-24 Units	10%
25-49 Units	20%
50 and Up	Consult Sales

## Economical Off-the-Shelf Special Tip Probes


\* Temperature ratings are dependent on thermocouple type, sheath diameter and environment.

**Recommended Handheld Meter**  
**HMM290**  
**\$245**

- ✓ Large Backlit Display
- ✓ Built-In IR Pyrometer

Please see pages J-19 through J-22 for more information on the SUPERMETER®!

Probe not included.



### Air Probe

Exposed element allows airflow for fast measurement. Rated to 870°C (1600°F). Available with 4.5 mm (3/16") diameter and exposed junction only. To order, add suffix "-AP" to model number, and add \$25 to price.

**Ordering Example:** KHSS-316E-RSC-12-AP, 300 mm (12") long handle probe, Type K, 4.5 mm (3/16") O.D., 304 SS sheath, exposed junction, air probe tip, \$36 + 25 = \$61.



### Penetration Probe (Very Popular)

Conical tip, for insertion into soft and semi-frozen material. Rated 1150°C (2100°F). Available with 4.5 mm (3/16") or 6 mm (1/4") diameter and grounded junction only. To order, add suffix "-NP" to model number, and add \$10 to price.

**Ordering Example:** KHSS-316G-RSC-12-NP, 300 mm (12") long handle probe, Type K, 4.5 mm (3/16") O.D., 304 SS sheath, grounded junction, conical probe tip, \$36 + 10 = \$46.

**PATENTED**  
 Covered by U.S. and International patents and pending applications.

### SHEATH MATERIALS

Probes made from OMEGACLAD® wire are available with either 304 SS, 310 SS, 316 SS, 321 SS and Super XL or Inconel® 600 Sheathing. While all may be used in a variety of applications, the differences between them can help determine which should be used in a particular application. 304 SS is rated to 900°C (1650°F) and 321 SS is rated to 870°C (1600°F), while Inconel is rated to 1150°C (2100°F). Both materials are rated "Very Good" in oxidizing, vacuum and inert atmospheres, and rated "Good" in Hydrogen atmospheres. 304 SS and 321 SS are recommended for general chemical applications, food applications, oil refinery use and steam lines. 321 SS is the same as 304 except for the addition of titanium as a stabilizer. The titanium helps prevent weld decay at temperatures above 650°C (1200°F). Inconel 600 is preferred in gas furnaces, lead bath, and bath mixtures containing cyanide. Inconel should not be used in salt baths contaminated by sulphur.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters