

Thermocouple Wire Stripper For Metal-Sheathed or OMEGACLAD® Wire



- ✓ Larger Chip Ports for Continuous Self-Cleaning
- ✓ Power Tool Adaptor Standard
- ✓ Expanded Range of Sizes

Sheath Diameter vs. Rotational Speed

0.25 to 0.79 mm (0.010 to 0.032") hand, 1 to 3.17 mm (0.040 to 0.125") hand to 300 rpm, 4.75 to 6.25 mm (0.185 to 0.250") 150 to 300 rpm
Where the stripping action is being conducted on semi-production or production quantities, the power adapted tool is recommended.

EASY TO USE

Method 1 (sizes 1 mm (0.040") and larger)

1. Secure the sheath in a vice, collet, or other holding fixture.
2. Locate the tool over the end of the sheath and apply a slight pressure on the tool while turning it by hand or machine, rotating in a clockwise direction, as though sharpening a pencil.
3. After the cut has started, the tool will self-feed until it runs against the holding fixture.
4. Slip the tool off over the exposed wires.

Method 2 (sizes 0.79 mm (0.032") and smaller)

1. Firmly grip the sheath a small distance from the end (about 0.25 mm (1/4")) with a pair of flat jaw pliers or any other holder which will firmly grip without crushing the sheath.
2. Grab the adaptor by hand, feed the sheath into the opening and slowly rotate the stripper while applying slight pressure, as though sharpening a pencil.
3. The tool will self-feed until it runs against the holding fixture.
4. Slip the tool off over the exposed wire.

Strippers for Both Metric and Standard Wire

 MOST POPULAR MODELS HIGHLIGHTED!

Nominal Sheath OD		Tool Tolerance Inches	Weight g (oz)	Model Number	Price	Replacement Tool Bit		Power Adaptor	
Inches	Metric					Model Number	Price	Size	Price
0.020	0.50 mm	0.019 to 0.021	28 (1)	PST020A	\$100	TB125	\$14	S	\$17
0.025	0.60 mm	0.024 to 0.026	28 (1)	PST025A	100	TB125	14	S	17
0.032	0.79 mm	0.031 to 0.034	28 (1)	PST032A	100	TB125	14	S	17
0.040	1.00 mm	0.040 to 0.044	71 (2½)	PST040A	100	TB188	14	M	17
1/16	1.50 mm	0.060 to 0.064	71 (2½)	PST062A	100	TB188	14	M	17
1/16	1.57 mm	0.063 to 0.067	71 (2½)	PST065A	100	TB188	14	M	17
0.080	2.00 mm	0.077 to 0.083	71 (2½)	PST20MMA	100	TB188	14	M	17
3/32	2.38 mm	0.090 to 0.094	71 (2½)	PST090A	100	TB188	14	M	17
0.118	3.00 mm	0.115 to 0.121	128 (4½)	PST30MMA	100	TB250	14	M	17
1/8	3.17 mm	0.122 to 0.128	128 (4½)	PST125A	100	TB250	14	M	17
0.177	4.50 mm	0.174 to 0.180	227 (8)	PST45MMA	120	TB250	14	L	30
3/16	4.75 mm	0.185 to 0.190	227 (8)	PST187A	120	TB250	14	L	30
0.236	6.00 mm	0.233 to 0.239	227 (8)	PST60MMA	120	TB250	14	L	30
1/4	6.25 mm	0.247 to 0.253	227 (8)	PST250A	120	TB250	14	L	30

To order additional power adaptors, specify POWER ADAPTOR (*), where (*) indicates S, M or L. Find power adaptor size in table above.

Ordering Examples: POWER ADAPTOR L for PST250A stripper and TB250, replacement tool bit for PST250A stripper, \$30 + 14 = \$44.
POWER ADAPTOR M for PST062A stripper and TB188, replacement tool bit for PST062A stripper, \$17 + 14 = \$31.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters