

Series 260S

Standard Threaded Well for 1/4" Diameter Elements



Application:

Standard length, 1/4" stem, bimetal thermometers; #20-gage thermocouple elements; unarmored liquid-in-glass test thermometers. Other temperature-sensing elements having 0.252" maximum diameter.

Connection Size:

1/2, 3/4 and 1 NPT are standard. Other thread sizes are available upon request.

Protective Coatings for Thermowells:

- Resist Corrosion
- For Chemical Baths
- Color-Coded Sensors for Process Control

- Available in PFA, Epoxy and other materials
- Consult Sales Department for complete information


Materials:

Brass (ASTM B-16); Carbon Steel (C-1018); Stainless Steel A.I.S.I. 304 & A.I.S.I. 316; Monel. Wells are also available in special materials; prices on request.

Cap and Chain Options:

For Brass cap, add \$4 to price and add suffix "CC (Brass)" to the end of the model number when you order. For 304 SS cap, add \$7 to the price and add suffix "CC (304SS)" to the end of the model number.

Series 260S—General Use



Metric Models Available!
See Pages B-37 and B-38

† NPSM internal pipe thread will accept both NPT and NPS male threads.

MOST POPULAR MODELS HIGHLIGHTED!



Shown close to actual size.

To Order (Specify Model Number)

Ext Thread P	Model Number	Materials and Prices				Stem Length A	Insert. Length U	Shank Dia. Q
		Stainless Steel 304	Stainless Steel 316	Carbon Steel	Brass			
1/2 NPT	1/2-260S-U21/2-*	\$26.50	\$36.00	\$20.00	\$20.00	4	2 1/2	—
	1/2-260S-U41/2-*	34.50	47.00	30.00	30.00	6	4 1/2	5/8
	1/2-260S-U71/2-*	51.50	69.00	44.00	44.00	9	7 1/2	5/8
	1/2-260S-U101/2-*	62.50	84.50	57.50	57.50	12	10 1/2	5/8
	1/2-260S-U131/2-*	90.00	121.00	74.50	74.50	15	13 1/2	5/8
	1/2-260S-U161/2-*	107.50	144.50	89.00	89.00	18	16 1/2	5/8
	1/2-260S-U221/2-*	170.00	200.00	118.50	118.50	24	22 1/2	5/8
3/4 NPT	3/4-260S-U21/2-*	\$26.50	\$36.00	\$20.00	\$20.00	4	2 1/2	—
	3/4-260S-U41/2-*	34.50	47.00	30.00	30.00	6	4 1/2	3/4
	3/4-260S-U71/2-*	51.50	69.00	44.00	44.00	9	7 1/2	3/4
	3/4-260S-U101/2-*	62.50	84.50	57.50	57.50	12	10 1/2	3/4
	3/4-260S-U131/2-*	90.00	121.00	74.50	74.50	15	13 1/2	3/4
	3/4-260S-U161/2-*	107.50	144.50	89.00	89.00	18	16 1/2	3/4
	3/4-260S-U221/2-*	170.00	200.00	118.50	118.50	24	22 1/2	3/4
1 NPT	1-260S-U21/2-*	\$38.00	\$46.00	\$31.00	\$31.00	4	2 1/2	—
	1-260S-U41/2-*	47.50	64.00	37.00	37.00	6	4 1/2	7/8
	1-260S-U71/2-*	62.50	84.50	48.50	48.50	9	7 1/2	7/8
	1-260S-U101/2-*	78.00	104.00	64.50	64.50	12	10 1/2	7/8
	1-260S-U131/2-*	107.90	144.95	85.50	85.50	15	13 1/2	7/8
	1-260S-U161/2-*	126.00	170.00	100.00	100.00	18	16 1/2	7/8
	1-260S-U221/2-*	185.50	213.00	133.00	133.00	24	22 1/2	7/8

* Specify material type "304SS" for 304 Stainless Steel, "316SS" for 316 Stainless Steel, "CS" for Carbon Steel or "BRASS" for brass. PFA coating available, see page B-16.

Ordering Example: 3/4-260S-U71/2-304SS, 304 stainless steel thermowell with 3/4 NPT external thread, 0.260" internal diameter, 7 1/2" insertion length and a 9" stem length, \$51.50.

For Assistance in Choosing Head and Well Assemblies, See Guide on Page B-5.

These wells are compatible with OMEGA® NB1, NB2, (page B-8); PR-12, PR14, and NPT-style probes, (page C-95); as well as DialTemp™ Thermometers (page E-11).

Pressure-Temperature rating—lb per square inch

Material	Temperature — °F						
	70°	200°	400°	600°	800°	1000°	1200°
Brass	5000	4200	1000	—	—	—	—
Carbon Steel	5200	5000	4800	4600	3500	1500	—
A.I.S.I.-304	7000	6200	5600	5400	5200	4500	1650
A.I.S.I.-316	7000	7000	6400	6200	6100	5100	2500
Monel	6500	6000	5400	5300	5200	1500	—

Increase Response Rate!
Use OT-201 Conductive Silicon Paste;
see page B-40.

Discount Schedule	
1-10.....Net	25-100.....20%
11-24.....10%	101 and up....Consult Sales

Discounts apply to similar thermowells.

See Page B-19 For Maximum Fluid Velocity.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters