

Reference Guide

- Properties of the sheath material
- Diameter and construction of thermocouple assembly

Temperature Range

OMEGA CLAD® is a three-part system composed of compacted MgO insulation, thermocouple wire and metal sheath. Four factors determine the useful service temperature for OMEGA CLAD® assemblies.

- Range for the thermocouple wire (see table of error)
- Maximum service temperature of insulation. In the case of MgO, this is in excess of 1650°C (3000°F)

Sheath Material Specifications

Material	Melting Point (°C/°F)	Continuous Maximum Temp. (°C/°F)	Tensile (PSI) Strength	
			@ 93°C (200°F)	@ 537°C (1000°F)
304 SS	1405/2560	900/1650	68,000	15,000
310 SS	1405/2560	1150/2100	75,000	27,500
316 SS	1370/2500	925/1700	75,000	23,000
321 SS	1400/2550	870/1600	70,000	17,000
Hastelloy X	1260/2300	1200/2200	55,100	35,500
Inconel*	1400/2550	1150/2100	39,000	5,000
SUPER XL	1400/2550	1204/2200	70,000	17,000

* Oxidizing, Vacuum or Inert atmosphere only

Conductor Size Equivalents

Gage No.	AWG		SWG		GAGE No.	AWG		SWG	
	inches	mm	inches	mm		inches	mm	inches	mm
0	0.3249	8.25	0.324	8.23	23	0.0226	0.574	0.024	0.610
1	0.2893	7.35	0.300	7.62	24	0.0201	0.511	0.022	0.559
2	0.2576	6.54	0.276	7.01	25	0.0179	0.455	0.020	0.508
3	0.2294	5.83	0.252	6.40	26	0.0159	0.404	0.0180	0.457
4	0.2043	5.19	0.232	5.89	27	0.0142	0.361	0.0164	0.417
5	0.1819	4.62	0.212	5.38	28	0.0126	0.320	0.0148	0.376
6	0.1620	4.11	0.192	4.88	29	0.0113	0.287	0.0136	0.345
7	0.1443	3.67	0.176	4.47	30	0.0100	0.254	0.0124	0.315
8	0.1285	3.26	0.160	4.06	31	0.0089	0.226	0.0116	0.295
9	0.1144	2.91	0.144	3.66	32	0.0080	0.203	0.0108	0.274
10	0.1019	2.59	0.128	3.25	33	0.0071	0.180	0.0100	0.254
11	0.0907	2.30	0.116	2.95	34	0.0063	0.160	0.0092	0.234
12	0.0808	2.05	0.104	2.64	35	0.0056	0.142	0.0084	0.213
13	0.0720	1.83	0.092	2.34	36	0.0050	0.127	0.0076	0.193
14	0.0641	1.63	0.080	2.03	37	0.0045	0.114	0.0068	0.173
15	0.0571	1.45	0.072	1.83	38	0.0040	0.102	0.0060	0.152
16	0.0508	1.29	0.064	1.63	39	0.0035	0.089	0.0052	0.132
17	0.0453	1.15	0.056	1.42	40	0.0031	0.079	0.0048	0.122
18	0.0403	1.02	0.048	1.22	41	0.0028	0.071	0.0044	0.112
19	0.0359	0.912	0.040	1.02	42	0.0025	0.064	0.0040	0.102
20	0.0320	0.813	0.036	0.914	43	0.0022	0.056	0.0036	0.091
21	0.0285	0.724	0.032	0.813	44	0.0020	0.051	0.0032	0.081
22	0.0253	0.643	0.028	0.711	45	0.0018	0.046	0.0028	0.071


AWG = American Wire Gage
SWG = (British) Standard Wire Gage

To convert from AWG to SWG: Determine wire diameter in inches (mm) from appropriate AWG.
To convert 30 AWG to SWG, determine that 30 AWG is 0.0100", which is equivalent to 33 SWG

Upper Temperature Limit in °C (°F) of OMEGA CLAD® Vs. Sheath Diameter

Sheath T/C Dia.	0.020" 0.5 mm	0.032" 0.8 mm	0.040" 1.0 mm	0.062" 1.6 mm	0.093" 2.4 mm	0.125" 3.2 mm	0.188" 4.8 mm	0.250" 6.3 mm
J	260 (500)	260 (500)	260 (500)	440 (825)	480 (900)	520 (970)	620 (1150)	720 (1300)
K & N	700 (1290)	700 (1290)	700 (1290)	920 (1690)	1000 (1830)	1070 (1960)	1150 (2100)	1150 (2100)
E	300 (570)	300 (570)	300 (570)	510 (950)	580 (1075)	650 (1200)	730 (1350)	820 (1510)
T	260 (500)	260 (500)	260 (500)	260 (500)	260 (500)	315 (600)	370 (700)	370 (700)

Bends Easily!




Upper Temperature Limit in °C (°F) of Protected Bare Wire Thermocouples Vs. Wire Diameter

T/C Type	Wire Size						
	8 AWG 0.128"	14 AWG 0.064"	20 AWG 0.032"	24 AWG 0.020"	28 AWG 0.013"	30 AWG 0.010"	36 AWG 0.005"
J	760 (1400)	590 (1100)	480 (900)	370 (700)	370 (700)	320 (600)	315 (590)
K	1260 (2300)	1090 (2000)	980 (1800)	870 (1600)	870 (1600)	760 (1400)	590 (1100)
E	870 (1600)	650 (1200)	540 (1000)	430 (800)	430 (800)	370 (700)	320 (600)
T	370 (700)	370 (700)	260 (500)	200 (400)	200 (400)	150 (300)	
RX/SX	200 (400)	200 (400)	200 (400)	200 (400)	200 (400)	150 (300)	
N	1260 (2300)	1090 (2000)	980 (1800)	980 (1800)	980 (1800)	870 (1600)	
CX	472 (800)	472 (800)	472 (800)	472 (800)	472 (800)	400 (752)	

Common Thermocouple Junctions



Twisted Shielded Wire





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters